

Description

The F2913 is a high isolation, low insertion loss, 50Ω SP2T absorptive RF switch designed for a multitude of wireless and RF applications. This device covers a broad frequency range of 50MHz to 6000MHz. In addition to providing low insertion loss, the F2913 also delivers high linearity and high isolation performance while providing a 50Ω termination at all RF ports.

The F2913 uses a single positive supply voltage of +2.7V to +5.5V and supports three states using either +1.8V or +3.3V control logic.

Competitive Advantage

- Low insertion loss
- High isolation
- Excellent linearity
- Fast switching time
- High termination power handling
- Extended temperature range

Typical Applications


- Base Station 2G, 3G, 4G, 5G
- Portable Wireless
- Repeaters and E911 Systems
- Digital Pre-Distortion
- Point-to-Point Infrastructure
- Public Safety Infrastructure
- WIMAX Receivers and Transmitters
- Military Systems, JTRS Radios
- RFID Handheld and Portable Readers
- Test / ATE Equipment

Features

- Low insertion loss: 0.79dB at 2GHz
- High isolation:
 - 71dB at 1GHz
 - 65dB at 2GHz
 - 58dB at 4GHz
- High IIP3: +65dBm at 2.6GHz
- Supply voltage: +2.7V to +5.5V
- 1.8V and 3.3V compatible control logic
- Operating temperature: -40°C to +110°C
- 4 × 4 mm 20-VFQFPN package

Block Diagram


Figure 1. Block Diagram





Pin Assignments

Figure 2. Pin Assignments for 4mm x 4mm x 0.95mm 20-QFN - Top View



Pin Descriptions

Table 1. Pin Descriptions

Pin	Name	Function
1, 15, 18	GND	This pin is internally connected to the exposed paddle. Connect this pin to ground as close as possible to the pin.
2, 4, 5, 6, 7, 9, 10, 11, 12, 14, 19	GND	Connect this pin directly to ground as close as possible to the pin with thru vias.
3	RF1	RF1 Port. If this pin is not 0V DC, then an external coupling capacitor must be used.
8	RFC	RF Common Port. If this pin is not 0V DC, then an external coupling capacitor must be used.
13	RF2	RF2 Port. If this pin is not 0V DC, then an external coupling capacitor must be used.
16	C2	Logic control pin. See Table 7 for proper logic setting.
17	C1	Logic control pin. See Table 7 for proper logic setting.
20	V_{DD}	Power supply. Bypass to GND with capacitors shown in the Figure 30 as close as possible to the pin.
	EP	Exposed Pad. This is internally connected to GND. Solder this exposed pad to a PCB pad that uses multiple ground vias to provide heat transfer out of the device into the PCB ground planes. These multiple ground vias are also required to achieve the specified RF performance.



Absolute Maximum Ratings

Stresses beyond those listed below may cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Table 2. Absolute Maximum Ratings

Paramet	Symbol	Minimum	Maximum	Unit		
V _{DD} to GND	V_{DD}	-0.5	+6.0	V		
C1, C2 to GND		V _{LOGIC}	-0.3	Lower of (V _{DD} + 0.3, 3.9)	V	
RF1, RF2, RFC to GND		V _{RF}	-0.3	0.3	V	
Maximum Input CW Power,	Insertion loss states	Pabscw		33	<u>.</u>	
$Z_S = Z_L = 50\Omega$, $T_{EP} = 25$ °C, $V_{DD} = 5.5V$ (any port) [a]	Terminated states	P _{ABSCW_TERM}		27	dBm	
Maximum Input Peak Power,	Insertion loss states	P _{ABSPK}		36	-ID	
$Z_S = Z_L = 50\Omega$, $T_{EP} = 25$ °C, $V_{DD} = 5.5V$ (any port) [a, b]	Terminated states	P _{ABSPK_TERM}		30	dBm	
Junction Temperature		T _{JMAX}		140	°C	
Storage Temperature Range		T _{ST}	-65	150	°C	
Lead Temperature (soldering, 10s)	TLEAD		260	°C		
Electrostatic Discharge – HBM (JEDEC/ESDA JS-001-2012)	V _{ESDHBM}		2500 (Class 2)	V		
Electrostatic Discharge – CDM (JEDEC 22-C101F)	V _{ESDCDM}		1000 (Class C2)	V		

a. $T_{EP} = T_{emperature}$ of the exposed paddle.

b. 5% duty cycle of a 4.6ms period.





Recommended Operating Conditions

Table 3. Recommended Operating Conditions

Parameter	Symbol	Condition	Minimum	Typical	Maximum	Unit
Supply Voltage	V_{DD}		2.7	3.3	5.5	V
Operating Temperature Range	T_{EP}	Exposed Paddle	-40		+110	°C
RF Frequency Range	f_{RF}		50		6000	MHz
Maximum Operating Input Power	P _{MAX}	$Z_S = Z_L = 50\Omega$			See Figure 3	dBm
Port Impedance (RFC, RF1, RF2)	Z_{RF}			50		Ω

Figure 3. Maximum RF Input Operating Power vs. RF Frequency ($Z_S = Z_L = 50\Omega$)





Electrical Characteristics

Table 4. Electrical Characteristics

See the F2913 Typical Application Circuit. Specifications apply when operated with $V_{DD} = +3.3V$, $T_{EP} = +25$ °C, $Z_S = Z_L = 50\Omega$, RF signals applied at RF1 or RF2 and measured at RFC, and Evaluation Board trace and connector losses are de-embedded, unless otherwise noted.

Parameter	Symbol	Condition	Min	Тур	Max	Unit	
Logic Input High	V _{IH}	C1, C2 pins	1.17 ^[b]		Lower of (V _{DD} , 3.6)	V	
Logic Input Low	VIL	C1, C2 pins	-0.3		0.6	V	
Logic Current	I _{IH} , I _{IL}		- 1 [a]		+1	μΑ	
DC Current (V _{DD})	I _{DD}			90	170	μA	
		$50MHz \le f_{RF} \le 400MHz$		0.77	0.97		
		$400MHz < f_{RF} \le 1GHz$ [c]		0.79	1.00		
		1GHz < f _{RF} ≤ 2GHz		0.79	1.00		
Insertion Loss RF1 to RFC or RF2 to RFC	IL	2GHz < f _{RF} ≤ 3GHz		0.88	1.10	dB	
IN TONICOIN ZONIC		3GHz < f _{RF} ≤ 4GHz		1.03	1.40		
		4GHz < f _{RF} ≤ 5GHz		1.15	1.50		
		5GHz < f _{RF} ≤ 6GHz		1.25	1.65		
	ISO1	$50MHz \le f_{RF} \le 400MHz$	74	79		dB	
		$400MHz < f_{RF} \le 1GHz$	66	71			
Isolation		$1GHz < f_{RF} \le 2GHz$	60	65			
(RFC to RF1, RF2)		$2GHz < f_{RF} \le 3GHz$	57	62			
(one path on)		$3GHz < f_{RF} \le 4GHz$	53	58			
		$4GHz < f_{RF} \le 5GHz$	50	54			
		5GHz < f _{RF} ≤ 6GHz	46	51			
		$50MHz \le f_{RF} \le 400MHz$	80	85			
		$400MHz < f_{RF} \le 1GHz$	75	80			
Isolation		1GHz < f _{RF} ≤ 2GHz	67	72			
(RF1 to RF2, RF2 to RF1)	ISO2	2GHz < f _{RF} ≤ 3GHz	62	67		dB	
(one path on)		$3GHz < f_{RF} \le 4GHz$	57	62			
		$4GHz < f_{RF} \le 5GHz$	53	58			
		5GHz < f _{RF} ≤ 6GHz	51	56			
Return Loss RF1, RF2 [d]	RL1	$50MHz \le f_{RF} \le 4GHz$		20		dB	
Insertion Loss State	INLI	4GHz < f _{RF} ≤ 6GHz		18.7		นม	
Return Loss RFC [d]	RL2	50MHz ≤ f _{RF} ≤ 4GHz		18.0		dB	
Insertion Loss State	ΝLZ	$4GHz < f_{RF} \le 6GHz$		15.2		ub	

- a. Items in min/max columns in **bold italics** are guaranteed by test.
- b. Items in min/max columns that are not bold italics are guaranteed by design characterization.
- c. Maximum spec guaranteed by test at 1GHz and by design characterization over the whole frequency range.
- d. Return loss includes mismatch effects of Evaluation Kit PCB and RF connectors.

Electrical Characteristics

Table 5. Electrical Characteristics

See F2913 Typical Application Circuit. Specifications apply when operated with $V_{DD} = +3.3V$, $T_{EP} = +25$ °C, $Z_S = Z_L = 50\Omega$, RF signals applied at RF1 or RF2 and measured at RFC, Evaluation Board trace and connector losses are de-embedded, unless otherwise noted.

Parameter	Symbol	Condition	Min	Тур	Max	Unit	
Return Loss RF1, RF2 [c]	RL3	$50MHz \le f_{RF} \le 4GHz$		20.3		dB	
Terminated State, All Off State	KL3	4GHz < f _{RF} ≤ 6GHz		19.3		uв	
Return Loss RFC [c]	RL4	$50MHz \le f_{RF} \le 4GHz$		17.5		dB	
All Off State	KL4	4GHz < f _{RF} ≤ 6GHz		15.3		uв	
Input IP2 (RF1, RF2 to RFC)		$\begin{split} f_1 &= 2.55 GHz \\ f_2 &= 2.65 GHz \\ P_{IN} &= +20 dBm/tone \\ Measure 5.2 GHz product \end{split}$		115		dBm	
Input IP3 (RF1, RF2 to RFC)		$f_1 = 2.55 GHz$ $f_2 = 2.65 GHz$ $P_{IN} = +13 dBm/tone$ Measure 2.75 GHz product	60 [ь]	65		dBm	
		$f_{RF} = 50MHz$	35	37		dBm	
Innut 1dD Compression [d]	IP1dB	$f_{RF} = 100MHz$	35	37			
Input 1dB Compression [d]	IPTUB	$f_{RF} = 2400MHz$	34	36			
		$f_{RF} = 6000MHz$	34	36			
Spurious Output (No RF Applied) [e]	P _{SPUR}	All unused ports terminated RBW = 100Hz		-127	-120	dBm	
Insertion Loss Flatness	IL _{FLAT}	Any 400MHz range		0.1	0.2	dB	
Group Delay	GD			0.05		ns	
		50% control to 90% RF		155	230		
Cuitobing Time [f]	CM	50% control to 10% RF		142	200] no	
Switching Time [f]	SW _{TIME}	50% control to 99% RF		234	300	ns	
		50% control to 1% RF		205	265		
Switching Rate	SWrate				25	kHz	

- a. Items in min/max columns in **bold italics** are guaranteed by test.
- b. Items in min/max columns that are not bold italics are guaranteed by design characterization.
- c. Return loss includes mismatch effects of Evaluation Kit PCB and RF connectors.
- d. The input 1 dB compression point is a linearity figure of merit. Refer to Figure 3 for the maximum RF operating input power levels.
- e. Spurious due to on-chip negative voltage generator. Typical generator fundamental frequency is 2.2MHz.
- f. Measured at $f_{RF} = 1GHz$.



Thermal Characteristics

Table 6. Package Thermal Characteristics

Parameter	Symbol	Value	Unit
Junction to Ambient Thermal Resistance	θЈА	60.2	°C/W
Junction to Case Thermal Resistance (Case is defined as the exposed paddle)	ӨЈС_ВОТ	9.5	°C/W
Moisture Sensitivity Rating (Per J-STD-020)		MSL1	

Typical Operating Conditions (TOCs)

Unless otherwise noted:

- $V_{DD} = +3.3V$
- $T_{EP} = 25$ °C. All temperatures are referenced to the exposed paddle.
- $Z_S = Z_L = 50\Omega$
- f_{RF} = 1GHz
- Small signal tests done at 0dBm input power.
- +13dBm per tone for IIP3 measurements.
- RF1 or RF2 are the driven ports.
- Evaluation Kit traces and connector losses are de-embedded for the insertion loss and isolation plots. All other plots include the loss and effects of the PCB.



Typical Performance Characteristics (1)

Figure 4. RFC to RF1 Insertion Loss vs. Freq. over Temperature and Voltage




Figure 6. RFC to RF1 Isolation vs. Freq. over Temp. and Voltage (RF2 On State)




Figure 8. RF1 to RF2 Isolation vs. Freq. over Temp. and Voltage (RF1 On State)




Figure 5. RFC to RF2 Insertion Loss vs. Freq. over Temperature and Voltage




Figure 7. RFC to RF2 Isolation vs. Freq. over Temp. and Voltage (RF1 On State]





Figure 9. RF2 to RF1 Isolation vs. Freq. over Temp. and Voltage (RF2 On State)



Typical Performance Characteristics (2)

Figure 10. RFC to RF1 Isolation vs. Freq. over Temp. and Voltage (All Off State)




Figure 12. RF1 to RF2 Isolation vs. Freq. over Temp. and Voltage (All Off State)




Figure 14. Evaluation Board Thru Line Match over Temperature




Figure 11. RFC to RF2 Isolation vs. Freq. over Temp. and Voltage (All Off State)





Figure 13. Evaluation Board Thru Line Loss over Temperature





Typical Performance Characteristics (3)

Figure 15. RF1 Return Loss vs. Frequency over Temp. and Voltage (RF1 On State)




Figure 17. RF2 Return Loss vs. Frequency over Temp. and Voltage (RF2 On State)




Figure 19. RFC Return Loss vs. Frequency over Temp. and Voltage (RF1 On State)




Figure 16. RF1 Return Loss vs. Frequency over Temp. and Voltage (RF2 On State)




Figure 18. RF2 Return Loss vs. Frequency over Temp. and Voltage (RF1 On State)





Figure 20. RFC Return Loss vs. Frequency over Temp. and Voltage (RF2 On State)



Typical Performance Characteristics (4)

Figure 21. RF1 Return Loss vs. Frequency over Temp. and Voltage (All Off State)




Figure 23. RFC Return Loss vs. Frequency over Temp. and Voltage (All Off State)




Figure 25. RF2 Input IP3 vs. Frequency over Temp. and Voltage (RF2 On State)




Figure 22. RF2 Return Loss vs. Frequency over Temp. and Voltage (All Off State)




Figure 24. RF1 Input IP3 vs. Frequency over Temp. and Voltage (RF1 On State)





Figure 26. Input P1dB vs. Frequency over Temp. and Voltage (On States)





Control Mode

Table 7. Switch Control Truth Table

C1	C2	RFC – RF1	RFC – RF2
LOW	LOW	OFF	OFF
LOW	HIGH	OFF	ON
HIGH	LOW	ON	OFF
HIGH	HIGH	N/A	N/A

Application Information

Default Start-up

The C1 and C2 control pins include no internal pull-down resistors to logic LOW or pull-up resistors to logic HIGH.


Power Supplies

A common V_{DD} power supply should be used for all pins requiring DC power. All supply pins should be bypassed with external capacitors to minimize noise and fast transients. Supply noise can degrade the noise figure, and fast transients can trigger ESD clamps and cause them to fail. Supply voltage change or transients should have a slew rate slower than 1V / 20 μ s. In addition, all control pins should remain at 0V (\pm 0.3V) while the supply voltage ramps up or while it returns to zero.

Control Pin Interface

If a clean control signal for pins 16 and 17 cannot be guaranteed due to overshoot, undershoot, or ringing, etc., the following circuit at the input of the control pins is recommended.

Figure 27. Control Pin Signal Integrity Improvement Circuit



Evaluation Kit Picture

Figure 28. Top View





Figure 29. Bottom View





Evaluation Kit / Applications Circuit

Figure 30. Electrical Schematic




Table 8. Bill of Material (BOM)

Part Reference	QTY	Description	Manufacturer Part #	Manufacturer
C1	1	0.1µF ±10%, 16V X7R Ceramic Capacitor (0402)	GRM155R71C104KA88D	Murata
C2 – C9	0	Not Installed (0402)		
R1 – R3	3	0Ω ±1%, 1/10W, Resistor (0402)	ERJ-2RKF1000X	Panasonic
J1 – J5	5	SMA Edge Mount	142-0761-881	Cinch Connectivity
J6	1	8x2 Vertical Pin Strip Header	961216-6404-AR	Amphenol FCI
U1	1	SP2T Switch 4mm x 4mm QFN	F2913NLGK	IDT
	1	Printed Circuit Board	F2913 PCB	IDT

Evaluation Kit (EVKit) Operation

External Supply Setup

- 1. Set up a V_{DD} power supply in the range of +2.7V to +5.5V with the power supply output disabled.
- 2. Connect the disabled V_{DD} supply connection to J6 pins 1, 3, 13, or 15 and GND to J6 pins 2, 4, 6, 8, 10, 12, 14, or 16.

Logic Control Setup

- 1. With the logic control lines disabled, set the HIGH and LOW logic levels to satisfy the levels stated in the electrical specifications table.
- 2. Connect the disabled logic control to J6 VCTRL1 (pins 5 or 7) and VCTRL2 (pins 9 or 11).
- 3. See Table 7 for the logic truth table. Note that C1 in the table corresponds to VCTRL1 on the EVKIT and C2 corresponds to VCTRL2.

Turn On Procedure

- 1. Set up the supplies and EVKIT as noted in the External Supply Setup and Logic Control Setup sections above.
- 2. Enable the V_{DD} supply.
- 3. Enable the logic control signals.
- 4. Set the logic settings to achieve the desired Table 7 configuration. Note that external control logic should not be applied without V_{DD} being present.

Turn Off Procedure

- 1. Set the logic control pins to 0V.
- Disable the V_{DD} supply.



Package Outline Drawings

The package outline drawings are located at the end of this document and are accessible from the Renesas website (see Ordering Information for POD links). The package information is the most current data available and is subject to change without revision of this document.

Marking Diagram



IDTF29 13NLGK ZE705AHG Lines 1 and 2 – Part number Line 3 "ZE" – Die version Line 3 "705" – Production period, last digit of year plus workweek Line 3 "AHG" – Production process

Ordering Information

Part Number	Package	MSL Rating	Shipping Packaging	Temperature Range
F2913NLGK	4 × 4 × 0.95 mm <u>20-VFQFPN</u>	MSL1	Cut Tape	-40°C to +110°C
F2913NLGK8	4 × 4 × 0.95 mm <u>20-VFQFPN</u>	MSL1	Reel	-40°C to +110°C
F2913EVBI	Evaluation Board			


Revision History


Date	Description
February 8, 2023	Updated POD links.
January 31, 2019	Updated package for correct drawing number
September 29, 2017	Initial release






Package Code:NLG20P1 20-VFQFPN 4.0 x 4.0 x 0.9 mm Body, 0.5mm Pitch PSC-4170-01, Revision: 02, Date Created: Oct 4, 2022







RECOMMENDED LAND PATTERN (PCB Top View, NSMD Design)

NOTES:

- 1. JEDEC compatible.
- 2. All dimensions are in mm and angles are in degrees.
- 3. Use ±0.05 mm for the non-toleranced dimensions.
- 4. Numbers in () are for references only.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use o any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/