


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **2072350150**  
**Status:** **Active**  
**Overview:** LTE Cellular Antennas  
**Description:** 824MHz-2170MHz Cellular Flexible Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 2072350100-AS (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2072350100-PK (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2072350100-PS (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Antennas
Series	<a href="#">207235</a>
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	<a href="#">734120110</a> Microcoaxial RF, 50 Ohm
Overview	<a href="#">LTE Cellular Antennas</a>
Product Name	Cellular Flexible Antenna
Protocol	Cellular
Type	Cellular Antenna
UPC	191128895927

**Physical**

Cable Length	150.00mm
Length	40.40mm
Mounting Style	Adhesive
Net Weight	0.791/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.40mm

**Electrical**

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	2170
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	0 @ 824 MHz, 3.8 @ 1710 MHz
Return Loss - S11 (dB)	< -5, < -8
Total Efficiency	>31% @ 824 MHz, >60% @ 1710 MHz

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2072350100-AS
Packaging Specification	2072350100-PK
Product Specification	2072350100-PS
Sales Drawing	2072350100-SD

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[207235](#) Series