

EM3908 Series EuroMag Terminal Blocks

High Current; Two-Tier; 5.08 Centers; Modular

SPECIFICATIONS

Rating: 25A, 300V

Center Spacing: 0.20" (5.08mm)

Wire Range: #10-24 AWG

Housing Material: UL rated 94V0 Thermoplastic

Contact Material: Brass Tin-Plated

Cage Material: Brass, Nickel-Plated

Screw Size: M2.6 Zinc-Plated Steel

Operating Temperature: 105°C (221°F) max., -40°C (-40°F) min.

Torque Rating: 6.0 lb-in.

Recommended PCB Hole Diameters: 0.055" (1.40mm)

Construction: Modular design features dovetails for interlocking to achieve longer lengths


Agency Information: cULus File E62622; CE Certified



EM390808

EM390804

Dimensions - mm (in)



| Poles | L (mm) | Poles | L (mm) |
|-------|--------|-------|--------|
| 2 | 10.16 | 14 | 71.12 |
| 3 | 15.24 | 15 | 76.20 |
| 4 | 20.32 | 16 | 81.28 |
| 5 | 25.40 | 17 | 86.36 |
| 6 | 30.48 | 18 | 91.44 |
| 7 | 35.56 | 19 | 96.52 |
| 8 | 40.64 | 20 | 101.60 |
| 9 | 45.72 | 21 | 106.68 |
| 10 | 50.80 | 22 | 111.76 |
| 11 | 55.88 | 23 | 116.84 |
| 12 | 60.96 | 24 | 121.92 |
| 13 | 66.04 | | |

To convert to inches, divide by 25.4

Part Numbering System

Series

of Poles

EM3908

□□

02 to 24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[EM390821](#) [EM390822](#) [EM390819](#) [EM390820](#) [EM390823](#) [EM390824](#) [EM390803](#) [EM390807](#) [EM390802](#)
[EM390810](#) [EM390812](#) [EM390818](#) [EM390805](#) [EM390811](#) [EM390806](#) [EM390808](#) [EM390813](#) [EM390814](#)
[EM390809](#) [EM390815](#) [EM390816](#) [EM390817](#) [EM390804](#)