



650 kHz/1.2 MHz, 18.5 V STEP-UP DC-DC CONVERTER

FEATURES


- 2.3 V to 6 V Input Voltage Range
- 18.5 V Boost Converter With 2.0 A Switch Current
- 650 kHz/1.2 MHz Selectable Switching Frequency
- Adjustable Soft-Start
- Thermal Shutdown
- Undervoltage Lockout
- 8-Pin MSOP Package
- 8-Pin TSSOP Package

APPLICATIONS

- Handheld Devices
- GPS Receiver
- Digital Still Camera
- Portable Applications
- DSL Modem
- PCMCIA Card
- TFT LCD Bias Supply

DESCRIPTION

The TPS61085 is a high frequency, high efficiency DC to DC converter with an integrated 2.0 A, 0.13 Ω power switch capable of providing an output voltage up to 18.5 V. The selectable frequency of 650 kHz and 1.2 MHz allows the use of small external inductors and capacitors and provides fast transient response. The external compensation allows optimizing the application for specific conditions. A capacitor connected to the soft-start pin minimizes inrush current at startup.





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.





SLVS859-JUNE 2008 www.ti.com

These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ORDERING INFORMATION(1)(2)

T _A	ORDERING	PACKAGE	PACKAGE MARKING
–40 to 85°C	TPS61085DGK	MSOP-8 (DGK)	PMKI
–40 to 85°C	TPS61085PW	TSSOP-8 (PW)	61085

- (1) The DGK and PW packages are available taped and reeled.
- (2) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.

ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted)(1)

	VALUE	UNIT
Input voltage range IN ⁽²⁾	-0.3 to 7	V
Voltage range on pins EN, FB, SS, FREQ, COMP	-0.3 to 7	V
Voltage on pin SW	20	V
ESD rating HBM	2	kV
ESD rating MM	200	V
ESD rating CDM	500	V
Continuous power dissipation	See Dissipation Rating Table	
Operating junction temperature range	-40 to 150	°C
Storage temperature range	-65 to 150	°C
Lead temperature (soldering, 10 sec)	260	°C

⁽¹⁾ Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability

(2) All voltage values are with respect to network ground terminal.

DISSIPATION RATINGS(1)(2)

PACKAGE	$R_{\theta JA}$	T _A ≤ 25°C POWER RATING	T _A = 70°C POWER RATING	T _A = 85°C POWER RATING
MSOP	181°C/W	552 mW	303 mW	221 mW
TSSOP	160°C/W	625 mW	343 mW	250 mW

- (1) $P_D = (T_J T_A)/R_{\theta JA}$
- (2) R_{0,JA} given for High-K PCB board.

RECOMMENDED OPERATING CONDITIONS

		MIN	TYP MAX	UNIT
V _{IN}	Input voltage range	2.3	6	V
Vs	Boost output voltage range	V _{IN} + 0.5	18.5	V
T _A	Operating free-air temperature	-40	85	°C
T_J	Operating junction temperature	-40	125	°C

Product Folder Link(s): TPS61085

ELECTRICAL CHARACTERISTICS


 V_{IN} = 3.3 V, EN = IN, V_{S} = 12 V, T_{A} = -40°C to 85°C, typical values are at T_{A} = 25°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
SUPPLY							
V _{IN}	Input voltage range		2.3		6	V	
IQ	Operating quiescent current into IN	Device not switching, V _{FB} = 1.3 V		70	100	μΑ	
I _{SDVIN}	Shutdown current into IN	EN = GND			1	μΑ	
UVLO	Undervoltage lockout threshold	V _{IN} falling			2.2	V	
		V _{IN} rising			2.3	V	
T _{SD}	Thermal shutdown	Temperature rising		150		°C	
T _{SD(HYS)}	Thermal shutdown hysteresis			14		°C	
LOGIC SIG	NALS EN, FREQ						
V _{IH}	High level input voltage	V _{IN} = 2.3 V to 6 V	2			V	
V _{IL}	Low level input voltage	V _{IN} = 2.3 V to 6 V			0.5	V	
I _{lkg}	Input leakage current	EN = FREQ = GND			0.1	μΑ	
BOOST CO	NVERTER		•		'		
V _S	Boost output voltage		V _{IN} + 0.5		18.5	V	
V_{FB}	Feedback regulation voltage		1.230	1.238	1.246	V	
gm	Transconductance error amplifier			107		μA/V	
I _{FB}	Feedback input bias current	V _{FB} = 1.238 V			0.1	μΑ	
R _{DS(on)}	N-channel MOSFET on-resistance	$V_{IN} = V_{GS} = 5 \text{ V}, I_{SW} = \text{current limit}$		0.13	0.20	Ω	
, ,		$V_{IN} = V_{GS} = 3.3V$, $I_{SW} = current limit$		0.15	0.24		
I _{lkg}	SW leakage current	EN = GND, V _{SW} = 6V			10	μA	
I _{LIM}	N-Channel MOSFET current limit		2.0	2.6	3.2	Α	
I _{SS}	Soft-start current	V _{SS} = 1.238 V	7	10	13	μΑ	
f _{osc}	Oscillator frequency	FREQ = high	0.9	1.2	1.5	MHz	
		FREQ = low	480	650	820	kHz	
	Line regulation	V _{IN} = 2.3 V to 6 V, I _{OUT} = 10 mA		0.0002		%/V	
	Load regulation	V _{IN} = 3.3 V, I _{OUT} = 1 mA to 400 mA		0.11		%/A	



PIN ASSIGNMENT

DGK, PW PACKAGES (TOP VIEW)



8-PIN 4.9mm x 3mm x 1.1mm MSOP (DGK) 8-PIN 6.4mm x 3mm x 1.2mm TSSOP (PW)

TERMINAL FUNCTIONS

TERMI	TERMINAL		DESCRIPTION			
NAME	NO.	I/O	DESCRIPTION			
COMP	1	I/O	Compensation pin			
FB	2	I	eedback pin			
EN	3	I	Shutdown control input. Connect this pin to logic high level to enable the device			
PGND	4		Power ground			
SW	5		Switch pin			
IN	6		Input supply pin			
FREQ	7	I	Frequency select pin. The power switch operates at 650 kHz if FREQ is connected to GND and at 1.2 MHz if FREQ is connected to IN			
SS	8		Soft-start control pin. Connect a capacitor to this pin if soft-start needed. Open = no soft-start			

TYPICAL CHARACTERISTICS

TABLE OF GRAPHS

			FIGURE
η	Efficiency	vs Load current, V _S = 12 V, V _{IN} = 3.3V	Figure 1
η	Efficiency	vs Load current, V _S = 9 V, V _{IN} = 3.3 V	Figure 2
	PWM switching - discontinuous conduction		Figure 3
	PWM switching - continuous conduction		Figure 4
	Load transient response	at High frequency	Figure 5
	Load transient response	at Low frequency	Figure 6
	Soft-start		Figure 7
	Supply current	vs Supply voltage	Figure 8
	Frequency	vs Load current	Figure 9
	Frequency	vs Supply voltage	Figure 10

Submit Documentation Feedback





Figure 1.



EFFICIENCY VS LOAD CURRENT




Figure 2.





Figure 4.

I_{OUT}

100 mA/div

SLVS859-JUNE 2008 www.ti.com





LOAD TRANSIENT RESPONSE LOW FREQUENCY (650 kHz)





Figure 5.

200 μs/div

Figure 6.



SUPPLY CURRENT vs SUPPLY VOLTAGE





Figure 7.

Figure 8.










Figure 9.

Figure 10.

SLVS859-JUNE 2008 www.ti.com



DETAILED DESCRIPTION




Figure 11. Block Diagram

The boost converter is designed for output voltages up to 18.5 V with a switch peak current limit of 2.0 A minimum. The device, which operates in a current mode scheme with quasi-constant frequency, is externally compensated for maximum flexibility and stability. The switching frequency is selectable between 650 kHz and 1.2 MHz and the minimum input voltage is 2.3 V. To control the inrush current at start-up a soft-start pin is available.

During the on-time, the voltage across the inductor causes the current in it to rise. When the current reaches a threshold value set by the internal GM amplifier, the power transistor is turned off, the energy stored into the inductor is then released and the current flows through the Schottky diode towards the output of the boost converter. The off-time is fixed for a certain V_{IN} and V_{S} , and therefore maintains the same frequency when varying these parameters.

However, for different output loads, the frequency may slightly change due to the voltage drop across the Rdson of the power transistor which will have an effect on the voltage across the inductor and thus on t_{ON} (t_{OFF} remains fixed). Some slight frequency changes might also appear with a fixed output load due to the fact that the output voltage V_{S} is not sensed directly but via the SW Pin, which affects accuracy.

Because of the quasi-constant frequency behavior of the device, the TPS61085 eliminates the need for an internal oscillator and slope compensation, which provides better stability for the system over a wide of input and output voltages range, and more stable and accurate current limiting operation compared to boost converters operating with a conventional PWM scheme. The TPS61085 topology has also the benefits of providing very good load and line regulations, and excellent load transient response.



SLVS859-JUNE 2008 www.ti.com

Design Procedure

The first step in the design procedure is to verify that the maximum possible output current of the boost converter supports the specific application requirements. A simple approach is to estimate the converter efficiency, by taking the efficiency numbers from the provided efficiency curves or to use a worst case assumption for the expected efficiency, e.g. 90%.

1. Duty Cycle:
$$D = 1 - \frac{V_{IN} \times \eta}{V_S}$$

2. Maximum output current:
$$Iout = \left(I_{swpeak} - \frac{\Delta I_L}{2}\right) \times (1 - D)$$

3. Peak switch current:
$$I_{swpeak} = \frac{\Delta I_L}{2} + \frac{I_{out}}{1 - D}$$

$$\Delta I_L = \frac{V_{IN} \times D}{f_S \times L}$$

with

and

I_{swpeak} = converter switch current (minimum switch current limit = 2.0 A)

fs = Converter switching frequency (typically 1.2 MHz)

L = Selected inductor value

 η = Estimated converter efficiency (please use the number from the efficiency plots or 90% as an estimation)

 ΔI_1 = Inductor peak-to-peak ripple current

The peak switch current is the steady state peak switch current that the integrated switch, inductor and external Schottky diode has to be able to handle. The calculation must be done for the minimum input voltage where the peak switch current is the highest.

Soft-start

The boost converter has an adjustable soft-start to prevent high inrush current during start-up. To minimize the inrush current during start-up an external capacitor connected to the soft-start pin SS is used to slowly ramp up the internal current limit of the boost converter when charged with a constant current. When the EN pin is pulled high, the soft-start capacitor C_{SS}) is immediately charged to 0.3 V. The capacitor is then charged at a constant current of 10 μ A typically until the output of the boost converter V_S has reached its Power Good threshold (90%) of V_S nominal value). During this time, the SS voltage directly controls the peak inductor current, starting with 0 A at $V_{SS} = 0.3$ V up to the full current limit at $V_{SS} \approx 800$ mV. The maximum load current is available after the soft-start is completed. The larger the capacitor the slower the ramp of the current limit and the longer the soft-start time. A 100 nF capacitor is usually sufficient for most of the applications. When the EN pin is pulled low, the soft-start capacitor is discharged to ground.

Inductor Selection

The TPS61085 is designed to work with a wide range of inductors. The main parameter for the inductor selection is the saturation current of the inductor which should be higher than the peak switch current as calculated in the Design Procedure section with additional margin to cover for heavy load transients. An alternative, more conservative, is to choose an inductor with a saturation current at least as high as the maximum switch current limit of 3.2 A. The other important parameter is the inductor dc resistance. Usually, the lower the dc resistance the higher the efficiency. It is important to note that the inductor dc resistance is not the only parameter determining the efficiency. Especially for a boost converter where the inductor is the energy storage element, the type and core material of the inductor influences the efficiency as well. At high switching frequencies of 1.2 MHz inductor core losses, proximity effects and skin effects become more important. Usually, an inductor with a larger form factor gives higher efficiency. The efficiency difference between different inductors can vary between 2% to 10%. For the TPS61085, inductor values between 3 μH and 6 μH are a good choice with a switching frequency of 1.2 MHz, typically 3.3 μH. At 650 kHz we recommend inductors between 6 μH and 13 μH, typically 6.8 μH. Possible inductors are shown in Table 1.

SLVS859-JUNE 2008 www.ti.com



Typically, it is recommended that the inductor current ripple is below 20% of the average inductor current. The following equation can therefore be used to calculate the inductor value:

$$L = \left(\frac{V_{IN}}{V_{S}}\right)^{2} \times \left(\frac{V_{S}-V_{IN}}{Iout_max \times f}\right) \times \left(\frac{\eta}{0.35}\right)$$
(1)

Table 1. Inductor Selection

L (μ H)	SUPPLIER COMPONENT SIZE (LxWxH mm)		DCR TYP (mΩ)	Isat (A)					
	1.2 MHz								
3.3	Sumida	CDH38D09	4 x 4 x 1	240	1.25				
4.7	Sumida	CDPH36D13	5 × 5 × 1.5	155	1.36				
3.3	Sumida	CDPH4D19F	5.2 x 5.2 x 2	33	1.5				
3.3	Sumida	CDRH6D12	6.7 x 6.7 x 1.5	62	2.2				
4.7	Würth Elektronik	7447785004	$5.9 \times 6.2 \times 3.3$	60	2.5				
5	Coilcraft	MSS7341	$7.3 \times 7.3 \times 4.1$	24	2.9				
		650 kHz							
6.8	Sumida	CDP14D19	5.2 x 5.2 x 2	50	1				
10	Coilcraft	LPS4414	4.3 × 4.3 × 1.4	380	1.2				
6.8	Sumida	CDRH6D12/LD	6.7 x 6.7 x 1.5	95	1.25				
10	Sumida	CDR6D23	5 × 5 × 2.4	133	1.75				
10	Würth Elektronik	744778910	$7.3 \times 7.3 \times 3.2$	51	2.2				
6.8	Sumida	CDRH6D26HP	7 x 7 x 2.8	52	2.9				

Rectifier Diode Selection

To achieve high efficiency, a Schottky type should be used for the rectifier diode. The reverse voltage rating should be higher than the maximum output voltage of the converter. The averaged rectified forward current I_{avg}, the Schottky diode needs to be rated for, is equal to the output current I_{aut}:

$$I_{avg} = I_{out}$$

Usually a Schottky diode with 2 A maximum average rectified forward current rating is sufficient for most applications. The Schottky rectifier can be selected with lower forward current capability depending on the output current I_{out} but has to be able to dissipate the power. The dissipated power is the average rectified forward current times the diode forward voltage.

$$P_D = I_{avg} \times V_{forward}$$

Typically the diode should be able to dissipate around 500mW depending on the load current and forward voltage.

Table 2. Rectifier Diode Selection

CURRENT RATING lavg	Vr	V _{forward / lavg}	SUPPLIER	COMPONENT CODE	PACKAGE TYPE
750 mA	20 V	0.425 V / 750 mA	Fairchild Semiconductor	FYV0704S	SOT 23
1 A	20 V	0.39 V / 1 A	NXP	PMEG2010AEH	SOD 123
1 A	20 V	0.52 V / 1 A	Vishay Semiconductor	B120	SMA
1 A	20 V	0.5 V / 1 A	Vishay Semiconductor	SS12	SMA
1 A	20 V	0.44 V / 1 A	Vishay Semiconductor	MSS1P2L	μ-SMP (Low Profile)

10

Setting the Output Voltage

The output voltage is set by an external resistor divider. Typically, a minimum current of 50 μ A flowing through the feedback divider gives good accuracy and noise covering. A standard low side resistor of 18 k Ω is typically selected. The resistors are then calculated as:

$$R2 = \frac{Vref}{70\mu A} \approx 18k\Omega \qquad R1 = R2 \times \left(\frac{Vs}{Vref} - 1\right) \tag{2}$$

Compensation (COMP)

The regulator loop can be compensated by adjusting the external components connected to the COMP pin. The COMP pin is the output of the internal transconductance error amplifier. Standard values of $R_{COMP} = 13 \text{ k}\Omega$ and $C_{COMP} = 3.3 \text{ nF}$ will work for the majority of the applications.

Please refer to Table 3 for dedicated compensation networks giving an improved load transient response. The following equations can be used to calculate R_{COMP} and C_{COMP}:

$$R_{COMP} = \frac{125 \times V_{IN} \times V_{S} \times Cout}{L \times Iout_max} \qquad C_{COMP} = \frac{V_{S} \times Cout}{5 \times Iout_max \times R_{COMP}}$$
(3)

Table 3. Recommended Compensation Network Values at High/Low Frequency

FREQUENCY	L	Vs	V _{IN} ± 20%	R _{COMP}	C _{COMP}
		15 V	5 V	82 kΩ	1.1 nF
		15 V	3.3 V	75 kΩ	1.6 nF
Lliab (4.2 MLI=)	2 2	12.1/	5 V	51 kΩ	1.1 nF
High (1.2 MHz)	3.3 µH	12 V	3.3 V	47 kΩ	1.6 nF
		0.1/	5 V	30 kΩ	1.1 nF
		9 V	3.3 V	27 kΩ	1.6 nF
		15 \/	5 V	43 kΩ	2.2 nF
		15 V	3.3 V	39 kΩ	3.3 nF
I a (CEO I-II-)	0.0	0.0 11	5 V	27 kΩ	2.2 nF
Low (650 kHz)	6.8 µH	12 V	3.3 V	24 kΩ	3.3 nF
		9 V	5 V	15 kΩ	2.2 nF
			3.3 V	13 kΩ	3.3 nF

Table 3 gives conservatives Rcomp and Comp values for certain inductors, input and output voltages providing a very stable system. For a faster response time, a higher Rcomp value can be used to enlarge the bandwidth, as well as a slightly lower value of Ccomp to keep enough phase margin. These adjustments should be performed in parallel with the load transient response monitoring of TPS61085.

Input Capacitor Selection

For good input voltage filtering low ESR ceramic capacitors are recommended. TPS61085 has an analog input IN. Therefore, a 1 μ F bypass is highly recommended as close as possible to the IC from IN to GND.

One 10 μ F ceramic input capacitors are sufficient for most of the applications. For better input voltage filtering this value can be increased. Refer to Table 4 and typical applications for input capacitor recommendations.

Copyright © 2008, Texas Instruments Incorporated

Submit Documentation Feedback

INSTRUMENTS

SLVS859-JUNE 2008 www.ti.com

Output Capacitor Selection

For best output voltage filtering a low ESR output capacitor like ceramic capcaitor is recommended. Two 10 μ F ceramic output capacitors (or one 22 μ F) work for most of the applications. Higher capacitor values can be used to improve the load transient response. Refer to Table 4 for the selection of the output capacitor.

Table 4. Rectifier Input and Output Capacitor Selection

	CAPACITOR	VOLTAGE RATING	SUPPLIER	COMPONENT CODE
C _{IN}	10 μF/1206	16 V	Taiyo Yuden	EMK212 BJ 106KG
IN bypass	1 μF/0603	16 V	Taiyo Yuden	EMK107 BJ 105KA
C _{OUT}	10 μF/1206	25 V	Taiyo Yuden	TMK316 BJ 106KL

Frequency Select Pin (FREQ)

The frequency select pin FREQ allows to set the switching frequency of the device to 650 kHz (FREQ = low) or 1.2 MHz (FREQ = high). Higher switching frequency improves load transient response but reduces slightly the efficiency. The other benefits of higher switching frequency are a lower output ripple voltage. Usually, it is recommended to use 1.2 MHz switching frequency unless light load efficiency is a major concern.

Undervoltage Lockout (UVLO)

To avoid mis-operation of the device at low input voltages an undervoltage lockout is included that disables the device, if the input voltage falls below 2.2 V.

Thermal Shutdown

A thermal shutdown is implemented to prevent damages due to excessive heat and power dissipation. Typically the thermal shutdown threshold is 150°C. When the thermal shutdown is triggered the device stops switching until the temperature falls below typically 136°C. Then the device starts switching again.

Submit Documentation Feedback

APPLICATION INFORMATION




Figure 12. Typical Application, 3.3 V to 12 V ($f_{sw} = 1.2 \text{ MHz}$)




Figure 13. Typical Application, 3.3 V to 12 V ($f_{sw} = 650 \text{ kHz}$)






Figure 14. Typical Application, 3.3 V to 9 V ($f_{sw} = 1.2 \text{ MHz}$)




Figure 15. Typical Application, 3.3 V to 9 V (f_{sw} = 650 kHz)

Submit Documentation Feedback




Figure 16. Typical Application with External Load Disconnect Switch

TFT LCD APPLICATION




Figure 17. Typical Application 3.3 V to 9 V (f_{sw} = 1.2 MHz) for TFT LCD with External Charge Pumps (VGH, VGL)

SLVS859-JUNE 2008 www.ti.com



WHITE LED APPLICATIONS




Figure 18. Simple Application (3.3V input - f_{sw} = 650 kHz) for wLED Supply (3S3P) (with optional clamping Zener diode)




Figure 19. Simple Application (3.3V input - f_{sw} = 650 kHz) for wLED Supply (3S3P) with Adjustable Brightness Control using a PWM Signal on the Enable Pin (with optional clamping Zener diode)




Figure 20. Simple Application (3.3V input - f_{sw} = 650 kHz) for wLED Supply (3S3P) with Adjustable Brightness Control using an Analog Signal on the Feedback Pin (with optional clamping Zener diode)





.com 30-Jul-2008

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	e Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾
TPS61085DGKR	ACTIVE	MSOP	DGK	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085DGKRG4	ACTIVE	MSOP	DGK	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085DGKT	ACTIVE	MSOP	DGK	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085DGKTG4	ACTIVE	MSOP	DGK	8	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085PW	ACTIVE	TSSOP	PW	8	150	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085PWG4	ACTIVE	TSSOP	PW	8	150	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085PWR	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM
TPS61085PWRG4	ACTIVE	TSSOP	PW	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)


(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.




TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS61085DGKR	MSOP	DGK	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS61085DGKT	MSOP	DGK	8	250	180.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS61085PWR	TSSOP	PW	8	2000	330.0	12.4	7.0	3.6	1.6	8.0	12.0	Q1





*All dimensions are nominal

ı	7 III GIITTOTOTOTO GI O TTOTTITTGI							
	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
	TPS61085DGKR	MSOP	DGK	8	2500	346.0	346.0	29.0
	TPS61085DGKT	MSOP	DGK	8	250	190.5	212.7	31.8
	TPS61085PWR	TSSOP	PW	8	2000	346.0	346.0	29.0

PW (R-PDSO-G**)

14 PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153

DGK (S-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
- E. Falls within JEDEC MO-187 variation AA, except interlead flash.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products Amplifiers amplifier.ti.com Data Converters dataconverter.ti.com DSP dsp.ti.com Clocks and Timers www.ti.com/clocks Interface interface.ti.com Logic logic.ti.com Power Mgmt power.ti.com Microcontrollers microcontroller.ti.com www.ti-rfid.com RF/IF and ZigBee® Solutions www.ti.com/lprf

Applications	
Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2008, Texas Instruments Incorporated