

FL MGUARD GT/GT - Router



2700197

<https://www.phoenixcontact.com/us/products/2700197>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Security appliance, 10/100/1000 Mbps, NAT, advanced firewall, SFP combo ports, functionally extendable with licenses

Your advantages

- Intelligent stateful inspection firewall
- Central management tool
- Secure remote services (VPN) according to IPsec standard
- Replaceable configuration memory
- Fast operation by means of configuration and remote maintenance portal
- Comprehensive connection options
- Flexible routing

Commercial data

Item number	2700197
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN30
Product key	DNN311
Catalog page	Page 335 (C-6-2019)
GTIN	4046356499651
Weight per piece (including packing)	828 g
Weight per piece (excluding packing)	660 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Dimensions

Width	128 mm
Height	110 mm
Depth	69 mm

Material specifications

Color	gray aluminum
Housing material	Metal

Interfaces

Ethernet (combo)

Connection method	SFP/RJ45
Note on the connection method	Either SFP port or RJ45 port active
Transmission speed	10/100/1000 Mbps (SFP module: 100/1000 Mbps)
Transmission physics	Copper or SFP module
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	2 (Combo ports)

Serial (RS-232)

Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)
-------------------	---

Fiber optic interface

Connection method	SFP
Transmission speed	1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
Transmission length	up to 80 km (Depending on the fiber/SFP module used)

System properties

Functionality

Basic functions	Router with intelligent firewall and Gigabit connectivity
-----------------	---

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Type	Stand-Alone
Product type	Security router for the DIN rail

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Security functions

Number of VPN tunnels	0 (up to 250 tunnels with additional license as an option)
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Filtering	MAC and IP addresses, ports, protocols
Firewall data throughput	max. 417 Mbps (Router mode, default firewall rules, bidirectional throughput) max. 174 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Basic functions	Router with intelligent firewall and Gigabit connectivity
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Network Time Protocol (NTP) client	Client
Remote Syslog Logging	on external server
Routing	Standard routing, NAT, 1:1-NAT, port forwarding
Protection against	IP spoofing, DoS and Syn Flood Protection
Encryption methods	DES, 3DES, AES-128, -192, -256
Virtual private network (VPN) throughput	max. 106 Mbps (Router mode, VPN bidirectional throughput)

Electrical properties

Power consumption	6.5 W
Maximum power dissipation for nominal condition	typ. 6.48 W
Test voltage	500 V DC
Test section	for one minute 500 V DC

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	18 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	270 mA
Typical current consumption	270 mA (at U _S = 24 V DC)

Function

Signal contact control voltage	24 V DC (typical)
Signal contact control current	270 mA (typical)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz

Air pressure (operation)	86 hPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 hPa ... 108 kPa (3500 m above sea level)

Standards and regulations

Free from substances that could impair the application of coating	In acc. with VW specification
---	-------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMC data

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge
	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 2000 MHz)
	IEC 61000-6-2 IEC 61000-4-4 (burst) 2 kV power line, 1kV data line
	IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)
Noise immunity	EN 61000-6-2:2005
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-4

Signaling

Status display	LEDs: LNK, Mode, Inf, ACT, SPD, FD, US1, US2, Fail, and 7-segment display
----------------	---

2700197

<https://www.phoenixcontact.com/us/products/2700197>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700197>



EAC

Approval ID: RU*DE*08.B.00731/19



DNV GL

Approval ID: TAA00002CU



LR

Approval ID: LR22191720TA



BV

Approval ID: 42674/B0 BV



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705



RINA

Approval ID: ELE121121XG

ABS

Approval ID: 23-2450089-PDA

cULus Listed

FL MGUARD GT/GT - Router



2700197

<https://www.phoenixcontact.com/us/products/2700197>

Classifications

ECLASS

ECLASS-11.0	19170406
ECLASS-12.0	19170406
ECLASS-13.0	19170406

ETIM

ETIM 9.0	EC001478
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



Accessories

FL CAT5 PATCH 0,3 - Patch cable

2832250

<https://www.phoenixcontact.com/us/products/2832250>

Patch cable, CAT5, assembled, 0.3 m



FL CAT5 PATCH 0,5 - Patch cable

2832263

<https://www.phoenixcontact.com/us/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>

Patch cable, CAT5, assembled, 1 m



FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>

Patch cable, CAT5, assembled, 1.5 m



FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL CAT5 PATCH 2,0 - Patch cable

2832289

<https://www.phoenixcontact.com/us/products/2832289>



Patch cable, CAT5, assembled, 2 m

FL CAT5 PATCH 3,0 - Patch cable

2832292

<https://www.phoenixcontact.com/us/products/2832292>



Patch cable, CAT5, assembled, 3 m

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL CAT5 PATCH 5,0 - Patch cable

2832580

<https://www.phoenixcontact.com/us/products/2832580>



Patch cable, CAT5, assembled, 5 m

FL CAT5 PATCH 7,5 - Patch cable

2832616

<https://www.phoenixcontact.com/us/products/2832616>



Patch cable, CAT5, assembled, 7.5 m

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL CAT5 PATCH 10,0 - Patch cable

2832629

<https://www.phoenixcontact.com/us/products/2832629>

Patch cable, CAT5, assembled, 10 m



FL CAT6 PATCH 12,5 - Patch cable

2891369

<https://www.phoenixcontact.com/us/products/2891369>

Patch cable, CAT6, preassembled, 12.5 m



FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL CAT6 PATCH 15,0 - Patch cable

2891372

<https://www.phoenixcontact.com/us/products/2891372>



Patch cable, CAT6, preassembled, 15.0 m

FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/us/products/2891576>



Patch cable, CAT6, preassembled, 20.0 m

FL MGUARD GT/GT - Router

2700197


<https://www.phoenixcontact.com/us/products/2700197>



FL RJ45 PROTECT CAP - Dust protection

2832991

<https://www.phoenixcontact.com/us/products/2832991>



Dust protection caps for RJ45 socket

FL PLUG RJ45 GR/2 - RJ45 connector

2744856

<https://www.phoenixcontact.com/us/products/2744856>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: gray, Ethernet

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL PLUG RJ45 GN/2 - RJ45 connector

2744571

<https://www.phoenixcontact.com/us/products/2744571>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: green, Ethernet

FL CRIMPTOOL - Assembly tool

2744869

<https://www.phoenixcontact.com/us/products/2744869>



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL MEM PLUG - Configuration memory

2891259

<https://www.phoenixcontact.com/us/products/2891259>



Exchangeable configuration memory of the device settings for simple device exchange and set-up

FL MGUARD LIC CIM - License

2701083

<https://www.phoenixcontact.com/us/products/2701083>



License for activating CIFS Integrity Monitoring (CIM) on an FL MGUARD

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL MGUARD LIC VPN-10 - License

2700194

<https://www.phoenixcontact.com/us/products/2700194>



License for up to 10 additional VPN online connections

MGUARD SECURE VPN CLIENT LIC - License

2702579

<https://www.phoenixcontact.com/us/products/2702579>



License for mGuard Secure VPN Client v11.x

FL MGUARD GT/GT - Router

2700197

<https://www.phoenixcontact.com/us/products/2700197>



FL MGUARD DM UNLIMITED - Software

2981974

<https://www.phoenixcontact.com/us/products/2981974>



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com