# SPECIFICATION FOR APPRONAL

Customer	•
Customer	•

Product Name: Mechanical Buzzer

Model Name: VSMB2315P

Drawing No. : VS20200722014

# Signature of Voise

Approved by	Checkde by	Issued by	Date



Office Add:Haoyangguang B-302# No.968 Baizhang Road, Ningbo China Factory add: Shishan Industrial Park Moushan Town Yuyao City China Tel:86-0574-87471601 Fax:86-0574-87471603 P.C.315000 Http://www.nbvoise.com E-mail:sales@nbvoise.com

Specification for Mechanical Buzzer	Page	2/5
	Revision No.	1.0
Model No.: VSMB2315P	Drawing No.	VS20200722014

## **Table of contents**

- 1. Revision
- 2. Scope
- 3. General Characteristics
- 4. Electrical and Acoustic Characteristics.
- 5. Dimensions
- 6. Packing

### 1. Revision

Rev.No.	Date	Page	Description of Revision
1.0	2019/5/17		Preliminary

Specification for Mechanical Buzzer	Page	3/5
1	Revision No.	1.0
Model No. : VSMB2315P	Drawing No.	VS20200722014

## 2. Scope

This specification is applied to the buzzer used for sounder in alarm systems, Please contact us when using this product for any other applications than described in the above.

#### 3. General

3.1 Out-Diameter : 23 mm
3.2 Height : 16.4 mm
3.3 Weight : 10 ±3g
3.4 Operating Temperature range:

-20~+60°C without loss of function

3.5 Store Temperature range:


-30~+70°C without loss of function

#### 4. Electrical and Acoustic Characteristics.

Test condition : 15 ~ 35 ℃, 25% ~ 85% RH, 860~1060 mbar

No	Items	Specification
1	Rated Voltage	1.5V DC
2	Working Voltage	1.3-2 VDC
3	Max Rated Current	30mA/1.5VDC
4	Min Sound Preesure Level	70dB/1.5VDC/20cm
5	Resonant Frequency	400±100Hz
6	Housing Material	ABS
7	Color	Black
8	Waterproof	IP30

Specification for Mechanical Buzzer	Page	4/5		
- F	Revision No.	1.0		
Model No. : VSMB2315P	Drawing No.	VS20200722014		
5 Dimoneione				



Specification for Mechanical Buzzer	Page	5/5
'	Revision No.	1.0
Model No. : VSMB2315P	Drawing No.	VS20200722014

## 6. Packing

Each minimum package unit of products shall be in a carton box and it shall be clearly marked with Part Number ,quantity and outgoing inspection number.

There shall be no mechanical damage on products during in storage.

Total:200 pcs per box Size:41.5x27x31cm