EXTERNAL DESKTOP POWER SUPPLY 56VDC 120WATT





Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM



Description:

Our Range of 120 Watt AC/DC switch mode power supplies provide 120 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.


| Specification | |
|-------------------------------|--|
| Part Code | SW4667 |
| Input Voltage Range | 100 → 240 Vac |
| Input Frequency Range | 47 → 63Hz |
| Input Connector | IEC 320-C14 |
| Input Current Rated | 2A Max |
| Inrush Current | 80A Max. at 230VAC Cold Start |
| Leakage Current | <3.5mA |
| Efficiency | 87% |
| Input Power (Output: No Load) | 0.21 W (At 230Vac & No load) |
| Output Voltage Rating | 56VDC |
| Output Current Range | 2.14A Max |
| Output Min Current | 0A |
| Output Connection Type | 2.1 x 5.5 x 12 mm centre positive – Straight |
| Line and Load Regulation | +/-5% |
| Over Voltage Protection | Auto Recovery |
| Over Load Protection | Auto Recovery |
| Short Circuit Protection | Auto Recovery |
| Ripple Voltage | 1—2% Vp-p Max of O/P V at Full load |
| Hi-Pot | 3000Vac 10mA 1 min. (I.P. to O.P.) |
| Safety Approved | CB, UL, Cul, FCC, GS, CE, PSE, CCCC |
| EMI Standard | CE / FCC Class B; Conduction & Radiation Met |
| Operating Temperature Range | 0°C → +40°C |
| Storage Temperature | -20°C → +80°C |
| Operating Humidity | 20% to 80% |
| Storage Humidity | 10% to 90% |
| Dimensions | 168(L) x 66(W) x 39(H) mm |
| Product Weight | 590g |
| Regulator Type | Switched Mode Power Supply |

EXTERNAL DESKTOP POWER SUPPLY 56VDC 120WATT



POWERPAX: SW4667

Diagrams



POWERPAX

© TT Electronics plc