



AMP | AMPSEAL 16

TE Internal #: 2203876-1

AMPSEAL 16, Other Automotive Connector Accessories, Mounting Clip, Wire-to-Wire, PBT GF, Red, Operating Temperature Range -40 – 125 °C

[View on TE.com >](#)

Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories



Automotive Connector Accessory Type: **Mounting Clip**

Connector System: **Wire-to-Wire**

Primary Product Material: **PBT GF**

Primary Product Color: **Red**

Sealable: **No**

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
Connector System	Wire-to-Wire
Sealable	No

Body Features

Primary Product Material	PBT GF
Primary Product Color	Red

Usage Conditions

Operating Temperature Range	-40 – 125 °C, -40 – 125 °C
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94-HB
------------------------	----------

Packaging Features

Packaging Quantity	320
Packaging Method	Bulk



Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2272889-1
16POS,HYBRID,HDR ASSY,180DEG,
COD A




TE Part # 2272889-2
16POS,HYBRID,HDR ASSY,180DEG,
COD B



TE Part # 2272889-4
24POS,HYBRID,HDR ASSY,180DEG,
COD D



TE Part # 2272889-3
16POS,HYBRID,HDR ASSY,180DEG,
COD C



TE Part # 2272889-5
24POS, HYBRID, HDR ASSY, 180DEG, COD E




TE Part # 2272889-6
24POS, HYBRID, HDR ASSY, 180DEG, COD F

Also in the Series | AMPSEAL 16



Automotive Connector Caps & Covers (76)



Automotive Connector Locks & Position Assurance (2)



Automotive Headers (3)



Automotive Housings (237)



Automotive Seals & Cavity Plugs (4)



Automotive Terminals (33)




Other Automotive Connector Accessories (11)

Customers Also Bought



TE Part #EM63332001
Single Wall RNF-100 Reel HS Tubing



TE Part #1586840-1
VAL-U-LOK PIN 16AWG BR SN LP



TE Part #DT04-3P-P004
DEUTSCH DT Series Housings & Connectors



TE Part #776308-1
AMPSEAL 16 HOUSINGS




TE Part #2-1703648-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS




TE Part #927865-1
TIMER, RECEPTACLE AND TAB



TE Part #4-643818-4
14P MTA156 CONN ASSY 20AWG YEL



TE Part #163307-4
MATE-N-LOK PIN



Documents

Product Drawings

[MOUNTING CLIP, ML CONN, 5MM PANEL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2203876-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2203876-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2203876-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English