


Product: [8885MN](#) 

SpaceMaker™, 12 C #22 Str TC, PO Ins, OS, PVC Jkt, AWM 2937



 [Request Sample](#)

Product Description

SpaceMaker™, 12 Conductor 22AWG (19x34) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, AWM 2937

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	19x34	TC - Tinned Copper	12

Conductor Count: 12

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.016 in

Color Chart

Color
Black
White
Red
Dark Green
Brown
Dark Blue
Orange
Yellow
Purple
Gray
Pink
Tan

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.244 in	0.016 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
14.9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
33.0 pF/ft	66.0 pF/ft

Inductance

Nominal Inductance
0.031 μ H/ft

Impedance

Nominal Characteristic Impedance
22 Ohm

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	80°C
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	62 lbs/1000ft
Max. Pull Tension:	61 lbs
Min. Bend Radius During Installation:	0.980 in
Min. Bend Radius (Continuous Flexing):	2.440 in

Standards

NEC/(UL) Compliance:	800
UL AWM Style Compliance:	UL Style AWM 2937 (300 V 80C)
Other Specification:	NFPA 79

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	300 V RMS

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
8885MN 006100	Blue, Light	Reel	100 ft	612825392309
8885MN 0061000	Blue, Light	Reel	1,000 ft	612825392330
8885MN 008100	Gray	Reel	100 ft	612825392316
8885MN 0081000	Gray	Reel	1,000 ft	612825392354
8885MN 004100	Yellow	Reel	100 ft	612825392293
8885MN 0041000	Yellow	Reel	1,000 ft	612825392323

History

Update and Revision:	Revision Number: 0.205 Revision Date: 08-27-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.