


# KADN/KAMN30 SERIES

## AC - DC POWER MODULE 30W SINGLE & DUAL OUTPUT



### FEATURES

- AC/DC POWER MODULE
- UNIVERSAL INPUT 85 ~ 265 VAC
- HIGH EFFICIENCY UP TO 86%
- SHORT CIRCUIT PROTECTION
- INTERNAL INPUT FILTER
- 3 YEARS WARRANTY
- MEDICAL SAFETY APPROVED
- LOW LEAKAGE CURRENT
- TWO MOPP INSULATIONS



### MODEL LIST

MODEL NO.	INPUT VOLTAGE	OUTPUT WATTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	EFF. (min.)	EFF. (typ.)	CAPACITOR LOAD (max.)
<b>Single Output Models</b>							
KADN/KAMN3005	85 ~ 265 VAC	30 WATTS	+ 5 VDC	6000 mA	79%	81%	7000 $\mu$ F
KADN/KAMN3012	85 ~ 265 VAC	30 WATTS	+ 12 VDC	2500 mA	83%	85%	7000 $\mu$ F
KADN/KAMN3015	85 ~ 265 VAC	30 WATTS	+ 15 VDC	2000 mA	84%	86%	7000 $\mu$ F
KADN/KAMN3024	85 ~ 265 VAC	30 WATTS	+ 24 VDC	1250 mA	84%	86%	3500 $\mu$ F
<b>Dual Output Models</b>							
KAMN3012D	85 ~ 265 VAC	30 WATTS	$\pm$ 12 VDC	$\pm$ 1250 mA	82%	84%	$\pm$ 7000 $\mu$ F
KAMN3015D	85 ~ 265 VAC	30 WATTS	$\pm$ 15 VDC	$\pm$ 1000 mA	83%	85%	$\pm$ 7000 $\mu$ F
KAMN30512D	85 ~ 265 VAC	30 WATTS	+5 / + 12 VDC	+3A / + 1.25A	80%	82%	7000 $\mu$ F

### SPECIFICATION

All Specifications Typical At Nominal Line, Full Load, 25°C Unless Otherwise Noticed

GENERAL						
Characteristics	Conditions	min.	typ.	max.	unit	
Switching frequency	$V_i$ nom, $I_o$ nom		65		KHz	
Isolation voltage	Input - Output	4,236 / 6,000			VAC/VDC	
Isolation resistance	Input - Output, @ 500VDC	100			M $\Omega$	
Ambient temperature (I)	Operating at $V_i$ nom, $I_o$ nom	-40		+ 71	°C	
Case temperature	Operating at $V_i$ nom, $I_o$ nom			+ 85	°C	
Derating	$V_i$ nom, +6l to + 71°C			2.5	% / °C	
Storage temperature	Non operational	-40		+100	°C	
Relative humidity	$V_i$ nom, $I_o$ nom	20		95	% RH	
Temperature coefficient	$V_i$ nom, $I_o$ min			$\pm$ 0.03	% / °C	

NOTE 1 : Pls refer to DERATING CURVE.

www.chinfa.com

sales@chinfa.com

2021.05.04



CHINFA ELECTRONICS IND. CO., LTD.  
ISO 9001 Certified

PI

# KADN/KAMN30 SERIES

## AC - DC POWER MODULE

### SPECIFICATION

All Specifications Typical At Nominal Line, Full Load, 25°C Unless Otherwise Noticed

#### GENERAL

Characteristics	Conditions		min.	typ.	max.	unit
MTBF	Bellcore issue 6 @40°C, GB	5V & 512D		703,000		Hours
		12V, 12D & 15D		722,000		Hours
		15V & 24V		740,000		Hours
Altitude during operation	EN 62368-1				5,000	m
Dimension		KAMN30	L89 x W63.5 x H25			mm
		KADN30	L85.3 x W60.3 x H24.2			mm
Cooling	Free air convection					

#### INPUT SPECIFICATIONS

Characteristics	Conditions		min.	typ.	max.	unit
Rated input voltage	Io nom		100		240	VAC
Input voltage range	Ta min ... Ta max, Io nom	AC in	85		265	VAC
		DC in	120		375	VDC
Input current	Vi : 115 / 230 VAC, Io nom			0.56 / 0.34		A
Rated input current	Vi : 100 ~ 240 VAC, Io nom				0.8 - 0.4	A
Line frequency (Note 2)	Vi nom, Io nom		47		63	Hz
Inrush current	Vi : 115 / 230 VAC, Io nom				20/40	A
Leakage current (Note 2)	Normal condition				100	μA
	Single fault condition				300	μA

NOTE 2 : The unit can be worked at 440 Hz of line frequency but the leakage current would be 600μA max. , and output load should be derated under 90%

#### OUTPUT SPECIFICATIONS

Characteristics	Conditions		min.	typ.	max.	unit
Output voltage accuracy	Vi nom, Io nom	single output models			± 1	%
		dual output models			± 2	%
Minimum load	Vi nom	single output models	0			%
		dual output models (each output)	20			%
Line regulation	Io nom, Vi min ... Vi max				± 1	%
Load regulation	Vi nom, Io min ... Io nom	single output models			± 1	%
		dual output models			± 2	%
Cross regulation (Dual model)	Asymmetrical load 20% / 100% FL				± 6	%
Hold up time	Vi : 115 / 230 VAC, Io nom		20 / 100			ms
Turn on time	Vi nom, Io nom				1,000	ms
Rise time	Vi nom, Io nom				150	ms
Fall time	Vi nom, Io nom				150	ms
Transient recovery time	Vi nom, I ~ 0.5 Io nom				1	ms
Ripple & noise	Vi nom, Io nom, BW = 20MHz				100	mV
External trim ADJ. Range (Note 3) (for single output only)	Io = 5% ... 100%		-10		+10	%
Efficiency	Vi nom, Io nom, Po / Pi		Up to 86%, See model list and typ efficiency curve			

NOTE 3 : Pls refer to Fig 1 & Table 1 for connection and resistance recommended.

#### CONTROL AND PROTECTION

Characteristics	Conditions	min.	typ.	max.	unit
Input fuse		T2A / 250VAC internal			
Internal surge voltage protection	IEC 61000-4-5	Varistor			
Output short circuit		Hiccup mode			
Rated over load protection	Vi nom (see typ current limited curve)	120			%

# KADN/KAMN30 SERIES

AC - DC POWER MODULE

## SPECIFICATION

All Specifications Typical At Nominal Line, Full Load, 25°C Unless Otherwise Noticed


### APPROVALS AND STANDARDS

TUV	EN 62368-1, EN 60601-1
cTUVus	UL 62368-1, ANSI / AAMI ES 60601-1
CE	EN 60601-1-2, EN 61000-6-3, EN 55032 Class B, EN 61000-3-2, EN 61000-3-3 EN 61000-6-2, EN 55024, EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5 EN 61000-4-6, EN 61000-4-8, EN 61000-4-11, EN 61204-3, CISPR 11
Vibration resistance	meet IEC 60068-2-6 (10-500 Hz, 2G, along X, Y, Z each Axis, 60 min for each Axis)
Shock resistance	meet IEC 60068-2-27 (15G, 11ms, 3 axes, 6 Faces, 3 times for each Face)

### PHYSICAL CHARACTERISTICS

Case size	KAMN30 : 89 × 63.5 × 25mm ( 3.5 × 2.5 × 0.98 inches)	KADN30 : 85.3 × 60.3 × 24.2mm ( 3.36 × 2.37 × 0.95 inches)
Case material	Plastic case / PCB base	
Weight	KAMN30 : 250g	KADN30 : 130g
Potting material	KAMN30 : Epoxy	

### MECHANISM & PIN CONFIGURATION




### PIN ASSIGNMENT

#### GENERAL


PIN NO.	1	2	3	4	5
SINGLE	AC IN	AC IN	Vo +	Vo -	Trim
DUAL 12D, 15D	AC IN	AC IN	Vo +	com	Vo -
512D	AC IN	AC IN	+5V	com	+12V

### CIRCUIT SCHEMATIC

• Block diagram for KAM(D)N30 series with single output




• Block diagram for KAMN30 series with dual output




# KADN/KAMN30 SERIES

AC - DC POWER MODULE



## CIRCUIT SCHEMATIC




## TYP. CURRENT LIMITED CURVE



## DERATING CURVE



## TYP. EFFICIENCY CURVE



## Fig. 1 Trim connection (For single output only)




Table 1 Typical resistor values for various output voltage adjustment settings and max continuous power

Type	Rext 1		Rext 2		Max continuous power
	Vo nom -5%	Vo nom -10%	Vo nom +5%	Vo nom +10%	
KAM(D)N3005	5.1KΩ	1KΩ	6.8KΩ	2KΩ	30 W
KAM(D)N3012	39KΩ	20KΩ	10KΩ	0Ω	30 W
KAM(D)N3015	180KΩ	56KΩ	30KΩ	5.1KΩ	30 W
KAM(D)N3024	150KΩ	51KΩ	8.2KΩ	0Ω	30 W