



AUXILIARY CONTACTS
CN
0.5

Product designation

Product type designation

Number of DIN modules

Electrical features

IEC Conventional free air thermal current I _{th}	A	6
Rated insulation voltage U _i IEC/EN	V	500
Rated impulse withstand voltage U _{imp}	kV	4
Minimum switching capacity		≥12V ≥5mA

Control circuit

Auxiliary contacts

NO Nr. 2

Operations

Mechanical life cycles 3000000

Ambient conditions

Operating temperature

min °C -5
max °C 55

Storage temperature

min °C -30
max °C 80
m 2000

Max altitude

Mechanical features

Tightening torque for terminals

max Nm 0.8

Terminals tool

PZ2

Weight


g 44

Resistance & Protection

Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1
 IEC/EN 60947-4-1
 IEC/EN 60947-5-1
 IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000041 -
 Auxiliary contact
 block