



# **EMI C E 25**

#### Features

- DIP 2"x1" package with international standard pinout
- 2:1 wide input range
- Low patient leakage current <5µA</li>
- Wide operating temperature range -40 ~ +90°C
- Medical safety approved (2xMOPP) according to IEC60601-1
- · No minimum load required
- Protections: Short circuit (Continuous) / Overload / Input under voltage
- 4000VAC hight I/O isolation (Reinforced isolation)
- · 3 years warranty



# Applications

- Medical devices
- Medical oxygen monitor
- CT scanning
- · Medical carts
- · Oral care equipment


#### GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

# Description

MDS15 series is 15W isolated and requlated module type medical grade DC-DC converter with 2"x1" package. It features international standard pins, a high efficiency up to 88%, wide working temperature range -40 $^{+}$ 90 $^{\circ}$ C, 4KVAC I/P-O/P hight isolation voltage, compliance with IEC60601-1 medical standard, continuous-mode short circuit protection, etc. The models account for different input voltage 9 $^{+}$ 18V, 18 $^{+}$ 36V and 36 $^{+}$ 75V 2:1 wide input range, and various output voltage 5V/12V/15V/24V, which are suitable for medical systems, ultra low leakage current.

# Model Encoding





MODEL SELECTION TABLE							
ORDER NO.	INPUT			OUTPUT			
	INPUT VOLTAGE (RANGE)	INPUT CURRENT		OUTPUT	OUTPUT	EFFICIENCY (Typ.)	CAPACITOR LOAD (MAX.)
		NO LOAD	FULL LOAD	VOLTAGE	CURRENT	(31)	(,
MDS15A-05	Normal 12V (9 ~ 18V)	10mA	1500mA	5V	3000mA	85%	5600µF
MDS15A-12		10mA	1450mA	12V	1250mA	88%	1000µF
MDS15A-15		10mA	1450mA	15V	1000mA	87%	720µF
MDS15A-24		10mA	1450mA	24V	625mA	85%	220µF
MDS15B-05	Normal 24V (18 ~ 36V)	7mA	750mA	5V	3000mA	87%	5600µF
MDS15B-12		7mA	700mA	12V	1250mA	87%	1000µF
MDS15B-15		7mA	700mA	15V	1000mA	86%	720µF
MDS15B-24		7mA	720mA	24V	625mA	87%	220µF
MDS15C-05	Normal 48V (36 ~ 75V)	5mA	390mA	5V	3000mA	86%	5600µF
MDS15C-12		5mA	350mA	12V	1250mA	87%	1000µF
MDS15C-15		5mA	360mA	15V	1000mA	87%	720µF
MDS15C-24		5mA	360mA	24V	625mA	88%	220µF




SPECIFICAT	TION								
		A: 9~18Vdc							
	VOLTAGE RANGE	B: 18~36Vdc							
INPUT	SUBGE VOLTAGE (100ms max )	C: 36~75Vdc							
INI OI	, ,	12Vin models : 25Vdc, 24Vin models : 50Vdc, 48Vin models : 100Vdc							
	FILTER	Pitype							
	PROTECTION	Fuse recommended. 12Vin models: 4A delay time Type, 24Vin models: 2A delay time Type, 48Vin models: 1A delay time Type							
	VOLTAGE ACCURACY	±1%							
OUTPUT	RATED POWER	15W							
		60mVp-p +0.5%							
	LINE REGULATION Note.3								
	LOAD REGULATION Note.4								
		12Vin/24Vin:250KHz, 48Vin:300KHz							
	SHORT CIRCUIT	Protection type: Continuous, automatic recovery							
		110 ~ 185% rated output power							
		Protection type: Recovers automatically after fault condition is removed							
		12Vin: 7.5Vdc, 24Vin: 15Vdc, 48Vin: 33Vdc							
	COOLING	Free-air convection							
	WORKING TEMP.	-40 ~ +90°C (Refer to "Derating Curve")							
	CASE TEMPERATURE	+110°C max.							
ENVIRONMENT	WORKING HUMIDITY	20% ~ 90% RH non-condensing							
		-55 ~ +125°C, 10 ~ 95% RH non-condensing							
	TEMP. COEFFICIENT	0.03% / °C (0 ~ 70°C)							
	SOLDERING TEMPERATURE	1.5mm from case of 1 ~ 3sec./260°C max.							
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes							
	SAFETY STANDARDS	IEC60601-1(LVD) 3 <sup>rd</sup> edition, EAC TP TC 020/2011(EAC TP TC 004 for 48Vin type only) approved							
	WITHSTAND VOLTAGE	I/P-O/P 4KVAC							
	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH							
	ISOLATION CAPACITANCE (Typ.)								
	EMC EMISSION	Parameter	Standard	Test Level / Note					
SAFETY &		Conducted	BS EN/EN55011	Class A without external components					
		Radiated	BS EN/EN55011	N/A					
EMC	EMC IMMUNITY	Parameter	Standard	Test Level / Note					
( Note.6)		ESD	BS EN/EN61000-4-2	Level 1, ±15KV air, ±8KV contact					
		Radiated Susceptibility	BS EN/EN61000-4-3	Level 1, 10V/m					
		EFT/Burest	BS EN/EN61000-4-4	Level 1, ±2KV					
		Surge	BS EN/EN61000-4-5	Level 1, ±1KV Line-Line, ±2KV Line-GND					
		Conducted	BS EN/EN61000-4-6	Level 1, 10Vrms(e.m.f.)					
		Magnetic Field	BS EN/EN61000-4-8	Level 2, 10A/m					
	MTBF	1060Khrs MIL-HDBK-217F(25°C)							
OTHERS	DIMENSION (L*W*H)	50.8*25.4*12mm (2*1*0.47 inch)							
	CASE MATERIAL	UL94V-0 plastic case							
	PACKING	30g; 18pcs/per tube, 432pcs/24 tube max./carton							
NOTE	2.Ripple & noise are mea     3.Line regulation is measu     4.Load regulation is measu     5.2xMOPP base on a word     6.The final equipment murefer to "EMI testing of continuous and the statement of the s	pple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1μf & 47μf capacitor.  ne regulation is measured from low line to high line at rated load.  NOPP base on a working voltage of 250Vac between Primary to Secondary.  ne final equipment must be re-confirm that it still meet EMC directives. For guidance on how to perform these EMC tests, please fer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)  roduct Liability Disclaimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx							


Unit:mm(inch)



#### ■ Mechanical Specification

- All dimensions in mm(inch)
- Tolerance: $x.x\pm0.5$ mm( $x.xxx\pm0.125$ ") Pin size is  $1\pm0.1$ mm( $0.04\pm0.004$ ")






## ■ Pin Configuration

Pin No.	Pin-Out		
1	+Vin		
2	-Vin		
3	+Vout		
4	NoPin		
5	-Vout		

### ■ Derating Curve



## ■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html