

SPECIFICATION FOR APPROVAL

CUSTOMER :	
MODEL NO:	12038 (AC Fan)
PART NO:	FA8B12-D1041G2AL
DATE:	2012.10.19

CUSTOMER APPROVAL

1 41 11 411	
ACT DV TECHNOLOGY CODDODATION	TEL • 996 2 92421111

2F, No.192, Lian Cheng Road, Zhonghe Dist.,

New Taipei City 235, Taiwan (R.O.C.) FAX: 886-2-82452200

Approved	QC	Checked	Checked	Prepared



CONTENTS

1.	<u>SCOPE</u>	3
2.	<u>ELECTRICAL</u>	3
3.	MATERIAL	4
4.	MECHANICAL	4
5.	EXPECTED LIFE SPAN (MTTF)	4
6.	NOISE MEASUREMENT	5
7.	RELIABILITY	6
8.	PRODUCT LABEL	6
9.	PERFORMANCE CHART	7
10	. <u>ASSEMBLY DIAGRAM</u>	8
11	ORDERING AND OPERATING REMARKS	9
12	FAN PACKING DATA	10



1. SCOPE

This document is a specification defining the electrical and mechanical characteristics of the product.

2. ELECTRICAL

Standard operating condition is 25°C, 65%RH ambient, unless otherwise specified.

	Item	Specification	Test Condition
1	Rated Voltage	100V ~ 240V	AC power supply
2	Rated Current	0.3 Amp (Typical)	AC power supply at Rated Voltage This is for Safety Regulation.
3	Starting Voltage	100V (Min.)	AC power supply
4	Insulation Resistance	10MΩ (Min.)	
5	Speed	2200 RPM ±10%	Measured at 5 minutes after starting under 25±5°C, 65± 5%RH ambient
6	Acoustical Noise	41.26 dB(A) (measurement tolerance ± 2 dBA)	Measured at typical speed with an acoustic microphone 1 meter away from the fan intake in a test chamber with background noise level below 18dB(A) under ISO-3745 Standard, refer to NOISE MEASUREMENT ITEM 7.
7	Static Pressure	4.23 mm-H ₂ O (0.17 inch-H ₂ O)	Refer to PERFORMANCE CHART ITEM 9 at zero airflow. This measurement is performed AMCA 210-99 Standard.
8	Air Flow	92.68 CFM (2.62CMM)	Refer to PERFORMANCE CHART ITEM 9 at zero static Pressure. This measurement is performed AMCA 210-99 standard.
9	Direction of rotation	Counter- anticlockwise	AC power supply, viewed from impeller.



ACT-RX TECHNOLOGY CORPORATION

3. MATERIAL

Impeller		PBT UL94-V0
Frame		PBT UL94-V0
Bobbin		PBT UL94-V0
Lead Wire	 ∨1: Grey ∨2: Grey : PWM : O/P: White	✓ 24UL 3266☐ 26☐ 28

4.MECHANICAL

Dimensions	L * W * H =120*120*38 (mm)
Weight	270 grams
Standard operating temperature range	-10 °C ~ 75 °C
Standard storage temperature	-20 °C ~ 80 °C
	☐ Two Ball Bearing
	☐ One Ball One Sleeve Bearing
Bearing system	☐ Sleeve Bearing
	Alloy Sleeve with Ceramic Shaft
	☐ Ceramic Bearing with Ceramic Shaft


5.EXPECTED LIFE SPAN (MTTF)

At a standard operating condition of $25\pm5^{\circ}$ C, $65\pm5^{\circ}$ RH ambient, the expected life(expressed as Mean Time To Failure) of products are evaluated under MIL-STD-781 Standard as below:

☑ Two Ball Bearing: 65000 hrs, Continuous operating under 25°C 65%RH
☐ One Ball One Sleeve Bearing: 50000 hrs, Continuous operating under 25°C 65%RH
☐ Sleeve Bearing: 30000 hrs, Continuous operating under 25°C 65%RH
☐ Alloy Sleeve with Ceramic Shaft: 300000 hrs, Continuous operating under 25°C 65%RH
☐ Ceramic Bearing with Ceramic Shaft: 500000 hrs, Continuous operating under 25°C
65% DH



6. NOISE MEASUREMENT:



Noise is measured under Rated Voltage in free air in the anechoic chamber with B & K Nexus 4350 conditioning amplifier, with B & K 4190 microphone at a distance of one meter from the fan intake. The background noise is 18dBA max under the ISO-3745 Standard.

ACT-RX TECHNOLOGY CORPORATION

7. RELIABILITY

	Item	Specification	Test Condition
1	Locked Rotor Test	Flameproof and damage free	Rotor locked for 72 hrs with Rated Voltage
2	Balance Test	No protruding beyond the circle within 10 seconds	The fan runs in a circle, scaled by fan radius plus 20mm, on a perfectly smooth plate for 10 seconds under the ISO 1940 G6.3 grade Standard.

8. PRODUCT LABEL




LABEA (ϕ 45)




9. PERFORMANCE CHART

This measurement is according to the AMCA 210-99 Standard.


PQ curve for FA8B12-D1041G2AL under Rated Voltage.








10.ASSEMBLY DIAGRAM





11. ORDERING AND OPERATING REMARKS

- 11.1 Please indicate Part No. on every order.
- 11.2 For those not specified but vital to your requirement, ACT-RX is in full position to supply qualified substitutes.
- 11.3 ACT-RX does not guarantee the product if applications exceed specified limitations.
- 11.4 Please do not touch the impeller and never carry the fan the lead wires. The bearings and the lead wires may be damaged.



- 11.5 Please do not use the fan in the environment of corrosive gas or liquid.
- 11.6 Please do not store the fan in the environment of high humidity. Please avoid storage of the fan over 6 months. For long term storage, please connect power to the fan shortly every 6 months even through the fan is stored in room temperature.
- 11.7 Improper use may lead to malfunction. To ensure normal operation, avoid dipping the fan into watery and oily liquid, or exposing it to heat, etc.
- 11.8 Please do not lock the rotor for those fan models without Auto Restart function during operation to prevent over heating which may cause permanent damage.
- 11.9 Warrantee period is 12 months max. under the environment condition IP-20 specified in IEC60529.
- 11.10 All specifications subject to change without prior notice.



12.FAN PACKING DATA

