






**OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINJSI**

NUMBER 926 933




ZEICHNUNG GÜLTIG AB KW41/83



Freimaßtoleranz ±0,4

**MANGESCHLAGENEM ZUSTAND PASSEND IN BOHRUNG Ø 1,5 mm bei 0,75mm<sup>2</sup>**




926 933 - 9	60 000	0,75 - 1mm <sup>2</sup>	CuNi2Zn24 Temp. 1/2 Hard	blank
926 933 - 8	30 000	0,75 - 1mm <sup>2</sup>	CuSn4 F56 (Geme 4)	blank
926 933 - 7	30 000	0,75 - 1mm <sup>2</sup>	CuSn4 F56	verzinnt
926 933 - 6	60 000	0,75 - 1mm <sup>2</sup>	CuSn4 F56	blank
926 933 - 5	60 000	0,75 - 1mm <sup>2</sup>	CuSn4 F56	vorverzinnt
926 933 - 4	30 000	0,75 - 1mm <sup>2</sup>	Messing	blank
926 933 - 3	30 000	0,75 - 1mm <sup>2</sup>	Messing	vorverzinnt
926 933 - 2	60 000	0,75 - 1mm <sup>2</sup>	Messing	blank
926 933 - 1	60 000	0,75 - 1mm <sup>2</sup>	Messing	vorverzinnt

BAND STANDARD NUMBER	Teile pro Nickerleinnert	DRAHT GROSSENBEREICH	MATERIAL	HEAT TREAT	OBERFLÄCHE	COATING OR PLATING
----------------------	--------------------------	----------------------	----------	------------	------------	--------------------

**CUSTOMER COPY REFERENCE ONLY**

FIRST USED	WIRE RANGE	CLASS	TYPE
P.P.P.	AREA	SCALE 10:1	
DR 9.6.81 <i>Grella</i>			



LOC	REV B2
A	

B2	REVISED PER ECO-11-005140	RK	3MAY11	APP
LTR	REVISION RECORD	ECN	DATE	REL

NAME ADER-END-KRALLE