



Product: [9271](#)

124Ω Twinax, #25-2c TC, PO, O/A Foil, PVC Jkt, CM

Product Description

124 Ohm Twinax, 25 AWG stranded (7x33) tinned copper conductors, polyethylene insulation, Beldfoil® shield (100% coverage), stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

| Conductor | | | | |
|------------------|-----------|--------------------|------------------|--------------|
| AWG | Stranding | Material | Nominal Diameter | No. of Pairs |
| 25 | 7x33 | TC - Tinned Copper | 0.021 in | 1 |
| Conductor Count: | | | 2 | |

| Insulation | |
|-------------------|------------------------|
| Material | Nominal Wall Thickness |
| PE - Polyethylene | 0.031 in |

| Color Chart | |
|-------------|--------------|
| Number | Color |
| 1 | Blue & Clear |

| Outer Shield Material | | | | | | |
|-----------------------|-------------------------|---------------------|--------------|--------------------|---------------|------------------------------|
| Type | Material | Material Trade Name | Coverage [%] | Drainwire Material | Drainwire AWG | Drainwire Construction n x D |
| Tape | Bi-Laminate (Alum+Poly) | Beldfoil® | 100% | TC - Tinned Copper | 22 | 7x30 |

| Outer Jacket Material | | |
|--------------------------|------------------|------------------------|
| Material | Nominal Diameter | Nominal Wall Thickness |
| PVC - Polyvinyl Chloride | 0.24 in | 0.035 in |

Construction and Dimensions

| Stranding | |
|-----------|---------|
| Diameter | 0.17 mm |

| Electrical Characteristics | | |
|---|-----------------------|---|
| Conductor DCR | | |
| Nominal Conductor DCR | Nominal Conductor DCR | Conductor Resistance |
| 31.8 Ohm/1000ft | 31.8 Ohm/1000ft | |
| | | Nominal Outer Shield DCR |
| | | 12 Ohm/1000ft |
| Capacitance | | |
| Nom. Capacitance Conductor to Conductor | | Nom. Capacitance Conductor to Other Conductor to Shield |
| 12.2 pF/ft | | 22 pF/ft |

| Inductance | |
|--------------------|--|
| Nominal Inductance | |

| |
|-------------|
| 0.188 µH/ft |
|-------------|

Impedance

| Nominal Characteristic Impedance |
|----------------------------------|
| 124 Ohm |

High Frequency (Nominal/Typical)

| Frequency [MHz] | Nom. Insertion Loss |
|-----------------|---------------------|
| 1 MHz | 0.6 dB/100ft |
| 10 MHz | 1.7 dB/100ft |
| 50 MHz | 3.6 dB/100ft |
| 100 MHz | 5 dB/100ft |
| 200 MHz | 6.9 dB/100ft |
| 400 MHz | 9.6 dB/100ft |

Delay

| Max. Delay Skew | Nominal Delay | Nominal Velocity of Propagation (VP) [%] |
|-----------------|---------------|--|
| 66 ns/100m | 1.54 ns/ft | 66% |

High Freq

| Frequency [MHz] |
|-----------------|
| 1 MHz |
| 10 MHz |
| 50 MHz |
| 100 MHz |
| 200 MHz |
| 400 MHz |

Voltage

| UL Description | UL Voltage Rating |
|-------------------|-------------------|
| UL AWM Style 2092 | 300 V RMS |

Temperature Range

| | |
|-----------------------|--------------------------|
| UL Temp Rating: | 60°C (UL AWM Style 2092) |
| Operating Temp Range: | -20°C To +60°C |

Mechanical Characteristics

| | |
|------------------------------|---------------|
| Bulk Cable Weight: | 25 lbs/1000ft |
| Max. Pull Tension: | 17 lbs |
| Min. Bend Radius/Minor Axis: | 2.5 in |

Standards

| | |
|--------------------------|----------------------------|
| NEC/(UL) Compliance: | CM |
| CEC/C(UL) Compliance: | CM |
| UL AWM Style Compliance: | UL Style 2092 (300 V 60°C) |
| CPR Euroclass: | Eca |

Applicable Environmental and Other Programs

| | |
|-----------------------------|-----|
| EU Directive Compliance: | Yes |
| EU CE Mark: | Yes |
| MII Order #39 (China RoHS): | Yes |

Flammability, LS0H, Toxicity Testing

| | |
|--------------------|-------------------|
| UL Flammability: | UL1685 UL Loading |
| IEC Flammability: | IEC 60332-1-2 |
| UL voltage rating: | 300 V RMS |

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Part Number

| |
|--|
| |
|--|

Variants

| Item # | Color | Put-Up Type | Length | UPC |
|---------------|-------|-------------|----------|--------------|
| 9271 006100 | Blue | Reel | 100 ft | 612825226192 |
| 9271 006500 | Blue | Reel | 500 ft | 612825226215 |
| 9271 0061000 | Blue | Reel | 1,000 ft | 612825226208 |
| 9271 006U1000 | Blue | UnReel | 1,000 ft | 612825226185 |

| | |
|-----------|------------------------|
| Footnote: | C - CRATE REEL PUT-UP. |
|-----------|------------------------|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.335 Revision Date: 08-27-2021 |
|----------------------|--|

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.