



SITOP PSU300S 24 V/20 A  
 SITOP PSU300S 20 A STABILIZED POWER SUPPLY INPUT: 400-500 V 3 AC OUTPUT: 24 V DC/20 A

Input	
Input	3-phase AC
Rated voltage value $V_{in}$ rated	400 ... 500 V
Voltage range AC	340 ... 550 V
Wide-range input	Yes
Mains buffering at $I_{out}$ rated, min.	6 ms; at $V_{in} = 400$ V
Rated line frequency	50 ... 60 Hz
Rated line range	47 ... 63 Hz
Input current	
• at rated input voltage 400 V	1.2 A
• at rated input voltage 500 V	1 A
Switch-on current limiting (+25 °C), max.	36 A
$I^2t$ , max.	0.9 A <sup>2</sup> ·s
Built-in incoming fuse	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

Output	
Output	Controlled, isolated DC voltage
Rated voltage $V_{out}$ DC	24 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.5 %
Static load balancing, approx.	1 %
Residual ripple peak-peak, max.	150 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV

Adjustment range	24 ... 28 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 480 W
Status display	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	No overshoot of Vout (soft start)
Startup delay, max.	1.5 s
Voltage rise, typ.	30 ms
Voltage increase time of the output voltage maximum	500 ms
Rated current value Iout rated	20 A
Current range	0 ... 20 A
• Note	24 A up to +45°C; +60 ... +70 °C: Derating 5%/K
Active power supplied typical	480 W
Short-term overload current	
• on short-circuiting during the start-up typical	35 A
• at short-circuit during operation typical	35 A
Duration of overloading capability for excess current	
• on short-circuiting during the start-up	100 ms
• at short-circuit during operation	100 ms
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

### Efficiency

Efficiency at Vout rated, Iout rated, approx.	91 %
Power loss at Vout rated, Iout rated, approx.	47 W

### Closed-loop control

Dynamic mains compensation (Vin rated ±15 %), max.	3 %
Dynamic load smoothing (Iout: 50/100/50 %), Uout ± typ.	3 %
Load step setting time 50 to 100%, typ.	2 ms
Load step setting time 100 to 50%, typ.	2 ms
Setting time maximum	10 ms

### Protection and monitoring

Output overvoltage protection	protection against overvoltage in case of internal fault Vout < 35 V
Current limitation, typ.	25 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Electronic shutdown, automatic restart
Enduring short circuit current RMS value	
• maximum	7 A
Overcurrent overload capability in normal operation	overload capability 150 % Iout rated up to 5 s/min

### Safety

Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current	
• maximum	3.5 mA
• typical	1 mA
CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	ATEX (EX) II 3G Ex nAC IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
Certificate of suitability IECEx	No
Certificate of suitability NEC Class 2	No
FM approval	-
CB approval	Yes
Marine approval	GL, ABS
Degree of protection (EN 60529)	IP20

## EMC

Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

## Operating data

Ambient temperature	
• during operation	0 ... 70 °C
— Note	with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation

## Mechanics

Connection technology	screw-type terminals
Connections	
• Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm <sup>2</sup> single-core/finely stranded
• Output	+, -: 2 screw terminals each for 0.2 ... 4 mm <sup>2</sup>
• Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 ... 1.5 mm <sup>2</sup>
Width of the enclosure	90 mm
Height of the enclosure	145 mm
Depth of the enclosure	150 mm
Weight, approx.	1.6 kg

Product property of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Buffer module
Mechanical accessories	Device identification label 20 mm × 7 mm, pastel-turquoise 3RT1900-1SB20
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)