

Power PCB Relay RT1 Inrush Power

- 1 pole 16A, 1 form A (NO) contact (AgSnO₂ or W pre-make contact + AgSnO₂)
- Mono- or bistable coil
- 5kV/10mm coil-contact
- **■** Reinforced insulation
- Test tab (manual operator) optional for bistable versions
- WG version: product in accordance to IEC60335-1
- RTS3T: Electronic ballast UL508/NEMA 410 rated
- RTS3T: 165/20ms inrush peak current

Typical applications

LED lighting systems, filament and incandescent lamp loads, movement detectors, light sensors, intelligent wall sockets, motors (RTS3L).


Aр	provals	;
		_

VDE Cert. No. 40007571,UL E214025, cCSAus 1142018

Technical data of approved types on request.

Contact Data	RT.3T	RTS3L
Contact arrangement	1 form A (N	O) contact
Rated voltage	250\	/AC
Max. switching voltage	400\	/AC
Rated current	16	A
Limiting continuous current	16A, UL: 20	OA (RTS3L)
Limiting making current,		
max. 20ms (incand. lamps)	165A peak	120A peak
max. 200µs	800A peak	
Breaking capacity max.	4000	OVA
Contact material	W (pre-make cont.)	AgSnO ₂
	+AgSnO ₂	
Contact style	pre-make contact	single contact
Frequency of operation, with/with	out load 360/36	600h ⁻¹
Operate/release time max., DC co	il 10/5	ims
Operate/Reset time max., bistable	version 10/10	Oms
Bounce time max.	4m	าร

Contact	ratings		
Туре	Contact	Load	Cycles
IEC 6181	0		
RTS3L	A (NO)	20A, 250VAC resistive, 70°C	20x10 ³
RTS3L m	onostable A	(NO) 16A, 250VAC resistive, 85°C	100x10 ³
RTS3T	A (NO)	16A, 250VAC resistive, 85°C	5x10 ³
UL 61810	0-1 (former	UL 508)	
RTS3L	A (NO)	20A, 250VAC, general purpose, 70°C	20x10 ³
RTS3L	A (NO)	16A, 250VAC, resistive, 85°C	50x10 ³
RTS3L	A (NO)	TV8, 240VAC, 40°C	25x10 ³
RTS3L	A (NO)	1.5hp, 240VAC, 70°C	30x10 ³
RTS3T	A (NO)	1200W Tungsten, 120VAC/277VAC,	
		60Hz, 50°C	6x10 ³
RTS3T	A (NO)	2A, 480VAC, magnetic ballast, 80°C	10x10 ³
RTS3T	A (NO)	2A, 480VAC, electronic ballast, 80°C	10x10 ^{3*}
RTS3T	A (NO)	3A, 277VAC, electronic ballast, 80°C	15x10 ³
RTS3T	A (NO)	5A, 120VAC, electronic ballast, 80°C	15x10 ³
* Special test	conditions availab	le on request	






Contact Data (continued)	RT.3T	RTS3L
Mechanical endurance		
DC coil	>5x10 ⁶ ops.	>10x10 ⁶ ops.
bistable version	>3x10 ⁶ ops.	>5x10 ⁶ ops.
tab manually operated	>1x10 ³ ops.	-

Coil Data, monostable DC coil		
Coil voltage range	5 to 110VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL1446	class F	

Coil vers	sions, monos	stable DC co	il		
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%^{1)}$	mW
005	5	3.5	0.5	62	403
006	6	4.2	0.6	90	400
009	9	6.3	0.9	203	400
012	12	8.4	1.2	360	400
024	24	16.8	2.4	1440	400
048	48	33.6	4.8	5520	417
060	60	42.0	6.0	8570 ¹⁾	420
110	110	77.0	11.0	288001)	420

1) Coil resistance ±12%.

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



Coil Data, bistable coils	1 coil	2 coils	
Magnetic system	polarized, bistable		
Coil voltage range	3 to 24VDC		
Operative range, IEC 61810		2	
Limiting voltage, % of rated coil voltage	age 120%	150%	
Min./Max. energization duration	30ms/1min at	<10% duty factor	
Coil insulation system according UL	1446 cla	ass F	
Ooii iribalatiori bystorii according OL	1440 010	200 1	




Power PCB Relay RT1 Inrush Power (Continued)


Coil Da	ita (continu	ed)			
	sions, bista				
Coil	Rated	Set	Reset	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
Coil vers	sions, bista	ble 1 coil			
A03	3	2.1	1.7	21	429
A12	12	8.4	6.6	360	400
A24	24	16.8	13.2	1440	400
Coil vers	sions, bista	ble 2 coils			
F03	3	2.1	1.7	15	600
F12	12	8.4	6.6	240	600
F24	24	16.8	13.2	886	650

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

Bistable coils - operation

Version	1	coil	2 coils
Coil terminals	A1	A2	A1 A3 A2
Operate	+	-	+ -
Reset	-	+	- +
Contact position not defined at delivery			





Insulation Data	
Initial dielectric strength	
between open contacts	1250V _{ms}
between contact and coil	5000V
Clearance/creepage	IIII
between contact and coil	≥10/10mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI 250V

Other Data	RT.3T	RTS3L			
Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content					
		ice Support Center at			
www.te.co	<u>m/customersuppo</u>	ort/rohssupportcenter			
Ambient temperature					
monostable DC coil	-40 to	85°C			
bistable 1 coil	-10 to	85°C			
bistable 2 coils	-40 to	85°C			
Category of environmental protection	١				
IEC 61810	RTII - flo	ux proof			
RTIII - wash tight available upon requ	iest				
Vibration resistance (functional),	10g	20g			
monostable version					
Shock resistance (destructive)	10	10g			
Terminal type	PCB-TH1	Γ, plug-in ²⁾			
Weight, without / with test tab	14/16g	14g/-			
Resistance to soldering heat THT					
IEC 60068-2-20	270°0	C/10s			
Packaging/unit					
without test tab	tube/20 pcs.,	tube/20 pcs.,			
	box/500 pcs.	box/500 pcs.			
with test tab	tray/25 pcs.,	-			
	box/100 pcs.	-			

2) RTT3T or bistable 2 coil version: PCB mounting only. See Accessories.

Accesso	ries	RTS3.
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	,,,,,,,	

For details see datasheet Accessories Industrial Power Relay RT

Socket available for 1 coil version only.

NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.




Power PCB Relay RT1 Inrush Power (Continued)


Terminal assignment

Bottom view on solder pins

monostable version




bistable version




- a) Indicated contact position during or after coil energization with reset voltage.
- b) for 2 coil version only

Dimensions / PCB layout

version without test tab










b) for 2 coil version only

version with test tab





*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.





Power PCB Relay RT1 Inrush Power (Continued)

Product	code structure		Typical product code	RT	S	3	Т	A12
Type RT	· Power PCB Relay RT1 Inrush Po	wer		_				
Version S	Without test tab	т	With test tab (manual operator) for contact material ,T' and bistable coil only					
Contact c	onfiguration					_		
3	1 form A (NO) contact							
Contact n	naterial						-	
L	AgSnO ₂	Т	Tungsten (W) pre-make + AgSnO ₂					
Coil								_
Co	il code: please refer to coil versions ta	ıble						
Version								
Bla	ank Standard Version	005 1						
WC	G Product in accordance to IEC 60	330- I						

Product code	Version	Contacts	Contact material	Coil version	Coil	Version	Part number
RTS3L005	Without test tab,	1 form A (NO)	AgSnO ₂	Monostable	5VDC	Standard	1-1415898-8
RTS3L006	16mm high	contact	_		6VDC		4-1415898-4
RTS3L012					12VDC		1-1415898-9
RTS3L024					24VDC		1-1415898-4
RTS3LA12				Bistable, 1 coil	12VDC		2-1415898-3
RTS3LF12				Bistable, 2 coils			2-1415898-5
RTS3T005	Without test tab,		W pre-make + AgSnO ₂	Monostable	5VDC		1-1415898-6
RTS3T012	15.7mm high		_		12VDC		1415898
RTS3T024					24VDC		1415898-1
RTS3T048					48VDC		1-1415898-1
RTS3T060					60VDC		1-1415898-2
RTS3TA05				Bistable, 1 coil	5VDC		1-1415898-5
RTS3TA06					6VDC		3-1415898-1
RTS3TA12					12VDC		1415898-2
RTS3TF03				Bistable, 2 coils	3VDC		1415898-4
RTS3TF12					12VDC		1415898-5
RTS3TF24					24VDC		1415898-6
RTT3TA12	With test tab,			Bistable, 1 coil	12VDC		1415898-7
RTT3TF24	23.6mm high			Bistable, 2 coils	24VDC		1-1415898-0
RTS3L012WG	Without test tab,	1form A (NO)	AgSnO ₂	Monostable	12VDC	IEC60335-1	2-1415898-7
RTS3L024WG	15.7 mm high	contact			24VDC	compliant	5-1415898-1
RTS3T012WG			W pre-make + AgSnO ₂		12VDC		5-1415898-6
RTS3TA24WG				Bistable 1 coil	24VDC		4-1415898-7

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request.