

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1068450099](#)  
**Status:** **Active**  
**Overview:** Polymicro Capillary Tubing  
**Description:** Polymicro Inner-Lok GC Union (5 pk), Inner Diameter 200 µm, Outer Diameter 1800µm, TQNE2502000

**Documents:**

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)


**General**

Product Family	Capillary Tubing
Series	<a href="#">106845</a>
Application	Industrial, Medical, Research, Scientific, and other
Application Notes and Articles	<a href="http://www.molex.com/polymicro/literature.html">www.molex.com/polymicro/literature.html</a>
Capillary Configurator	<a href="http://www.molex.com/polymicro/capillaryconfigurator.html">www.molex.com/polymicro/capillaryconfigurator.html</a>
Capillary Series	CC
Catalog	<a href="http://www.molex.com/polymicro/catalog.html">www.molex.com/polymicro/catalog.html</a>
Comments	Ideal for Capillary to Capillary connections
Overview	<a href="#">Polymicro Capillary Tubing</a>
Polymicro	Yes
Product Name	Inner-Lok
Temp - Operating Continuous	950° C
Temp - Operating Short-term	1200° C
Type	Capillary Tubing
UPC	884982476011

**Physical**

Internal Diameter	200µm
Internal Diameter Tolerance	+100µm / - 0
Material - Tubing	Synthetic Fused Silica
Net Weight	2.065/g
Outer Diameter	1800µm
Outer Diameter Tolerance	+ 0 / - 20µm
Packaging Type	Bag
Tubing Length	38.00mm

**Material Info**



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[106845 Series](#)

**Use With**

Polymicro Synthetic Fused Silica Tubing