

## Specification Sheet

Part Number: 156-00538



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

2-Piece Cable Tie & Edge Clip, 8.0" Long, EC4B, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

**Article Number** 156-00538

**Type** T50REC4B

**Color** Black (BK)

**Quantity Per** bag

**Product Description** HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

**Short Description** 2-Piece Cable Tie & Edge Clip, 8.0" Long, EC4B, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

**Global Part Name** T50REC4B-PA66HS/PA66HIRHS-BK

**Minimum Tensile Strength (Imperial)** 50.0

**Minimum Tensile Strength (Metric)** 225

**Length L (Imperial)** 8.0

**Length L (Metric)** 203.2

**Fixation Method** EdgeClip, top, assembled, 2 piece

**Identification Plate Position** none

**Releasable Closure** No

**Variant** Inside Serrated

**Width W (Imperial)** 0.18

**Width W (Metric)** 4.6

**Bundle Diameter Min (Imperial)** 0.20

**Bundle Diameter Min (Metric)** 5.0

**Bundle Diameter Max (Imperial)** 2.0

**Bundle Diameter Max (Metric)** 50.0

**Thickness T (Imperial)** 0.05

<b>Thickness T (Metric)</b>	1.2
<b>Height H (Imperial)</b>	0.05
<b>Height H (Metric)</b>	1.20
<b>Panel Thickness Min (Imperial)</b>	0.04
<b>Panel Thickness Max (Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Shortcut</b>	PA66HIRHS PA66HS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)