


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0330013004](#)  
**Status:** **Active**  
**Overview:** [MX150 Connector System](#)  
**Description:** MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 16, 18 and 20 AWG, Left Reel Payoff

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification AS-33012-002-CH-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Test Summary TS-33001-002-001 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	<a href="#">33001</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff, Small Polarization Rib
Crimp Quality Equipment	Yes
Overview	<a href="#">MX150 Connector System</a>
Product Name	MX150
Taxonomy	Crimp Terminals
UPC	822350084178

**Physical**

Gender	Female
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Unplated
Net Weight	0.435/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size AWG	18, 20
Wire Size mm²	0.75-1.00

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33012-002-CH-001
Sales Drawing	SD-33012-002-001
Test Summary	TS-33001-002-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[33001](#) Series

**Use With**

[33472](#) Dual Row Housing. [33476](#) Hybrid Housing. [33471](#) Single Row Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Toolkit for MX150 Connectors	<a href="#">2002220700</a>
FA2 Mechanical Feed Applicator for MX150 18 Grip Receptacle Terminals, 20 AWG and 0.75mm² Wire	<a href="#">638082600</a>
FA2 Pneumatic Feed Crimp Applicator	<a href="#">638082610</a>

for MX150 18 Grip  
 Receptacle, 20  
 AWG and 0.75mm<sup>2</sup>  
 Wire  
 FA2 Mechanical 638082800  
 Feed Applicator  
 for MX150 18 Grip  
 Female Terminals,  
 18 AWG and  
 1.00mm<sup>2</sup> Wire  
 FA2 Pneumatic Feed 638082810  
 Crimp Applicator  
 for MX150 Crimp  
 Terminals, 18 AWG  
 PremiumGrade 638116000  
 Hand Crimp Tool  
 for MX150 Female  
 Terminals, 18-22  
 AWG  
 PremiumGrade 638116100  
 Hand Crimp Tool  
 for MX150 Female  
 Terminals for  
 1.00mm<sup>2</sup> and  
 1.50mm<sup>2</sup> Metric  
 Wires  
 Hand Crimp Tool 638116200  
 Metric 0.5 and 0.75  
 Extraction Tool for 638131500  
 MX150L, MX150, PT  
 Bulb Socket, iGrid,  
 SPOX, and Wire-to-  
 Motor Terminals  
 FineAdjust Applicator 639040400  
 for SRC Connector  
 using MX150  
 Receptacle  
 Terminals, 0.75mm<sup>2</sup>  
 wires  
 FineAdjust Applicator 639040500  
 for SRC Connector  
 using MX150  
 Receptacle  
 Terminals, 1.00mm<sup>2</sup>  
 wires  
 ServiceGrade 640160133  
 Hand Crimp Tool  
 for MX150 Crimp  
 Terminals, 14-22  
 AWG

This document was generated on 02/02/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**