

Enamelled copper wire on mini bobbin
CUL 500/1,50



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 500/1,50**

Type	CUL 500/1,50	Type	CUL 500/1,50
Electrical data		30 Operating data	
		current car. cap.	6.50 A
		Environment	
		Heat resistance	155 °C (CL.F)
		insulating varnish	min. Polyurethan, mod.
		Tin-plate	>350 °C
		Measures and weights	
		Wire diameter	1.50 mm
		Weight	0.50 kg
		Length m (min.)	25

Subjects to change.