



6 GHz/ 12 Gbps Clock/ Data Fanout Buffer with Internal Termination

Features


- → Input Clock Frequency up to 6 GHz Typical
- → Maximum Input Data Rate up to 12 Gbps Typical
- → 4 pairs of differential CML outputs
- → Low additive jitter, < 0.05ps (max)
- → Input accepts: CML, LVDS, CML, SSTL input level
- → Output to Output skew: <20ps
- → Operating Temperature: -40°C to 85°C
- → Power supply: $3.3V \pm 10\%$ or $2.5V \pm 5\%$
- → Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- → Halogen and Antimony Free. "Green" Device (Note 3)
- → Packaging (Pb-free & Green):
 - 16-pin TQFN (ZH)

Block Diagram



The PI6C5946004 is a high-performance low-skew 1-to-4 CML clock or data fanout buffer. The inputs accept CML, LVDS, CML and SSTL signals with internal termination resistors. PI6C5946004 is ideal for clock / data distribution applications.

Pin Configuration



Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.





Pin Description

Pin #	Name	Туре	Description
1, 2	Q1+, Q1-	Output	Differential output pair, CML interface level.
3, 4	Q2+, Q2-	Output	Differential output pair, CML interface level.
5, 6	Q3+, Q3-	Output	Differential output pair, CML interface level.
7	V _{DD}	Power	Core Power Supply
8	EN	Input	Synchronous Output Enable, with internal 25k-ohm pull-up resistor. Logic high selects enable, and logic low selects disable.
9	REF_IN-	Input	Differential IN negative input, AC and DC coupled
10	V _{REF-AC}	Output	Reference Voltage: Biased to VDD-1.4V. Used when AC coupling inputs
11	V _{TH}	Input	Differential pair IN center-tap node. Tie to VREF-AC for AC coupled inputs.
12	REF_IN+	Input	Differential IN positive input, AC and DC coupled
13	GND	Power	Ground
14	V _{DD}	Power	Core Power Supply
15, 16	Q0+, Q0-	Output	Differential output pair, CML interface level.





Maximum Ratings (Over operating free-air temperature range)

	Note:
Storage Temperature65°C to+155°C Ambient Temperature with Power Applied40°C to+85°C	Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions
3.3V Core Supply Voltage-0.5 to +4.6VESD Protection (HBM)2000V	above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

- ---

DC Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
			3.0		3.6	V
V _{DD}	Core Power Supply Voltage		2.375		2.625	V
T _A	Ambient Temperature		-40		85	°С
I _{DD}	Power Supply Current	No load, max V _{DD}			130	mA
R _{DIFF_IN}	Differential Input Resistance (REF_IN+ to REF_IN-)		90	100	110	Ω
V _{IH}	Input High Voltage		1.2		V _{DD} - 0.9	V
V _{IL}	Input Low Voltage		0.4		V _{IH} - 0.1	V
V _{IN}	Input Voltage Swing		0.1		1.7	V
V _{DIFF_IN}	Differential Input Swing		0.2			V
V _{REF-AC}	Output Reference Voltage		V _{DD} -1.50	V _{DD} -1.30	V _{DD} -1.15	V

LVCMOS/LVTTL DC Characteristics (TA = -40°C to +85°C, V_{DD} = 2.5V ±5% to 3.3V ±10%)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V _{IH}	Input High Voltage		2.0		V _{DD}	V
V _{IL}	Input Low Voltage		0		0.8	V
I _{IH}	Input High Current		-125		20	μΑ
I _{IL}	Input Low Current		-300			μΑ

CML DC Characteristics (T_A = -40°C to +85°C, V_{DD} = $3.3V \pm 10\%$, $2.5V \pm 5\%$)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V _{OUT}	Output Voltage Swing	Single Ended	325	400		mV






Symbol	Parameter	Conditions	Min	Тур	Max	Units
f _{max}	Output Frequency			6		GHz
t _{pd}	Propagation Delay ⁽¹⁾				400	ps
T	Output-to-output Skew ⁽²⁾				20	ps
T _{sk}	Device to Device skew				200	ps
Ts	Setup time			240		ps
T _h	Hold time			240		ps
V _{PP}	Differential peak to peak voltage	$f \le 3 \text{ GHz}$	600	800	850	mV
t _r /t _f	Output Rise/Fall time	20% - 80%, f ≤ 4 GHz	40		90	ps
		f ≤ 1 GHz	48		52	%
t _{odc}	Output duty cycle	$1 \text{ GHz} \le f < 6 \text{ GHz}$	40		60	%
tj	Buffer additive jitter RMS	156.25MHz with 12KHz to 20MHz integration range (CML)		40		fs

AC Characteristics ($T_A = -40^{\circ}C$ to $+85^{\circ}C$, $V_{DD} = 3.3V \pm 10\%$, 2.5V $\pm 5\%$)

Notes:

1. Measured from the differential input to the differential output crossing point

2. Defined as skew between outputs at the same supply voltage and with equal loads. Measured at the output differential crossing point




Output Swing vs Frequency








Typical Output Eye Diagrams



10.5Gb/s Fiber Channel CML output waveform












Configuration Test Load Board Termination for CML Outputs



Thermal Information

Symbol	Description	Condition	
Θ_{JA}	Junction-to-ambient thermal resistance	Still air	54.4 °C/W
Θ _{JC} Junction-to-case thermal resistance			40.8 °C/W





Application Information Suggest for Unused Inputs and Outputs

LVCMOS Input Control Pins

It is suggested to add pull-up=4.7k and pull-down=1k for LVCMOS pins even though they have internal pull-up/down but with much higher value (>=50k) for higher design reliability.

REF_IN=/ REF_IN- Input Pins

They can be left floating if unused. For added reliability, connect $1k\Omega$ to GND.


Outputs


All unused outputs are suggested to be left open and not connected to any trace. This can lower the IC power supply power.

Power Decoupling & Routing

VDD Pin Decoupling

As general design rule, each VDD pin must have a 0.1uF decoupling capacitor. For better decoupling, 1uF can be used. Locating the decoupling capacitor on the component side has better decoupling filter result as shown in Fig. 1.





Differential Clock Trace Routing

Always route differential signals symmetrically, make sure there is enough keep-out space to the adjacent trace (>20mil.). In 156.25MHz XO drives IC example, it is better routing differential trace on component side as the following Fig. 2.




Fig 2: IC routing for XO drive

Clock timing is the most important component in PCB design, so its trace routing must be planned and routed as a first priority in manual routing. Some good practices are to use minimum vias (total trace vias count <4), use independent layers with good reference plane and keep other signal traces away from clock traces (>20mil.) etc.





CML and LVDS Input Interface

LVPECL and LVDS DC Input

LVPECL and LVDS clock input to this IC is connected as shown in the Fig. 3.




Fig 3: CML/ LVDS Input

LVPECL and LVDS AC Input

LVPECL and LVDS AC drive to this clock IC requires the use of the VREF-AC output to recover the DC bias for the IC input as shown in Fig. 4




Fig 4: CML/ LVDS AC Coupled Input

CML AC-Coupled Input

CML AC-coupled drive requires a connection to VREF-AC as shown in Fig. 5. The CML DC drive is not recommended as different vendors have different CML DC voltage level. CML is mostly used in AC coupled drive configuration for data and clock signals.




Fig 5: CML AC-Coupled Input Interface





HCSL AC-Coupled Input

It is suggested to use AC coupling to buffer PCIe HCSL 100MHz clock since its V_cm is relatively low at about 0.4V, as shown in Fig. 6.




Fig 6: HCSL AC-Coupled Input Interface

CMOS Clock DC Drive Input

LVCMOS clock has voltage Voh levels such as 3.3V, 2.5V, 1.8V. CMOS drive requires a Vcm design at the input: Vcm= ½ (CMOS V) as shown in Fig. 7. Rs =22 ~33ohm typically.




Fig 7: CMOS DC Input Vcm Design



A product Line of Diodes Incorporated

PI6C5946004

Device LVPECL Output Terminations

LVPECL Output Popular Termination

The most popular LVPECL termination is 1500hm pull-down bias and 1000hm across at RX side. Please consult ASIC datasheet if it already has 1000hm or equivalent internal termination. If so, do not connect external 1000hm across as shown in Fig. 8. This popular termination's advantage is that it does not allow any bias through from V_{DD} . This prevents V_{DD} system noise coupling onto clock trace.




Fig. 8 LVPECL Output Popular Termination

LVPECL Output Thevenin Termination

Fig. 9 shows CML output Thevenin termination which is used for shorter trace drive (<5in.), but it takes V_{DD} bias current and V_{DD} noise can get onto clock trace. It also requires more component count. So it is seldom used today.




Fig. 9 LVPECL Thevenin Output Termination

CML Output AC Thevenin Termination

CML AC Thevenin terminations require a 1500hm pull-down before the AC coupling capacitor at the source as shown in Fig. 10. Note that pull-up/down resistor value is swapped compared to Fig. 9. This circuit is good for short trace (<5in.) application only.




Fig. 10 CML Output AC Thenvenin Termination





CML Output Drive HCSL Input

Using the CML output to drive a HCSL input can be done using a typical CML AC Thenvenin termination scheme. Use pull-up/ down 450/600hm to generate Vcm=0.4V for the HCSL input clock. This termination is equivalent to 500hm load as shown in Fig. 11.




Fig. 11 CML Output Drive HCSL Termination

LVPECL Output V_swing Adjustment

It is suggested to add another cross 1000hm at TX side to tune the LVPECL output V_swing without changing the optimal 1500hm pull-down bias in Fig. 12. This form of double termination can reduce the V_swing in ½ of the original at the RX side. By fine tuning the 100ohm resistor at the TX side with larger values like 150 to 200ohm, one can increase the V_swing by > 1/2 ratio.





Fig. 12 LVPECL Output V_swing Adjustment

CML AC Output Drive

CML is implemented mostly via AC coupling. With AC coupling, CML can drive CML and LVDS inputs as well with an external 100 ohm equivalent differential termination.







Clock Jitter Definitions

Total jitter= RJ + DJ

Random Jitter (RJ) is unpredictable and unbounded timing noise that can fit in a Gaussian math distribution in RMS. RJ test values are directly related with how long or how many test samples are available. Deterministic Jitter (DJ) is timing jitter that is predictable and periodic in fixed interference frequency. Total Jitter (TJ) is the combination of random jitter and deterministic jitter: , where is a factor based on total test sample count. JEDEC std. specifies digital clock TJ in 10k random samples.

Phase litter

Phase noise is short-term random noise attached on the clock carrier and it is a function of the clock offset from the carrier, for example dBc/Hz@10kHz which is phase noise power in 1-Hz normalized bandwidth vs. the carrier power @10kHz offset. Integration of phase noise in plot over a given frequency band yields RMS phase jitter, for example, to specify phase jitter <=1ps at 12k to 20MHz offset band as SONET standard specification.

PCIe Ref CLK Jitter

PCIe reference clock jitter specification requires testing via the PCI-SIG jitter tool, which is regulated by US PCI-SIG organization. The jitter tool has PCIe Serdes embedded filter to calculate the equivalent jitter that relates to data link eye closure. Direct peak-peak jitter or phase jitter test data, normally is higher than jitter measure using PCI-SIG jitter tool. It has high-frequency jitter and low-frequency jitter spec. limit. For more information, please refer to the PCI-SIG website: http://www.pcisig.com/specifications/pciexpress/

Device Thermal Calculation

Fig. 13 shows the JEDEC thermal model in a 4-layer PCB.




Fig. 13 JEDEC IC Thermal Model

Important factors to influence device operating temperature are:

1) The power dissipation from the chip (P_chip) is after subtracting power dissipation from external loads. Generally it can be the no-load device Idd.

2) Package type and PCB stack-up structure, for example, loz 4 layer board. PCB with more layers and are thicker has better heat dissipation.

3) Chassis air flow and cooling mechanism. More air flow M/s and adding heat sink on device can reduce device final die junction temperature Tj.





The individual device thermal calculation formula:

Tj =Ta + Pchip x Ja

Tc = Tj - Pchip x Jc

Ja ____ Package thermal resistance from die to the ambient air in C/W unit; This data is provided in JEDEC model simulation. An air flow of 1m/s will reduce Ja (still air) by 20~30%

Jc ____ Package thermal resistance from die to the package case in C/W unit

Tj ____ Die junction temperature in C (industry limit <125C max.)

Ta Ambiant air température in C

Tc ____ Package case temperature in C

Pchip___ IC actually consumes power through Iee/GND current

Thermal calculation example

To calculate Tj and Tc of PI6CV304 in an SOIC-8 package: Step 1: Go to Pericom web to find Ja=157 C/W, Jc=42 C/W http://www.pericom.com/support/packaging/packaging-mechanicals-and-thermal-characteristics/

Step 2: Go to device datasheet to find Idd=40mA max.

		C _L = 33pF/33MHz	20	
		C _L = 33pF/66MHz	40	
	Supply Current	C _L = 22pF/80MHz	35	mA
ID		CL = 15pF/100MHz	32	mA
		C _L = 10pF/125MHz	28	
		CL = 10pF/155MHz	41	

Step 3: P_total= 3.3Vx40mA=0.132W Step 4: If Ta=85C

Tj= 85 + Ja xP_total= 85+25.9 = 105.7C

Tc = Tj + Jc xP total = 105.7-5.54 = 100.1C

Note:

The above calculation is directly using Idd current without subtracting the load power, so it is a conservative estimation. For more precise thermal calculation, use P_unload or P_chip from device Iee or GND current to calculate Tj, especially for CML buffer ICs that have a 150ohm pull-down and equivalent 100ohm differential RX load.

Part Marking

ZH Package




YY: Year WW: Workweek 1st X: Assembly Code 2nd X: Fab Code





Packaging Mechanical: 16-TQFN (ZH)



14-0244

For latest package info.

please check: http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/

Ordering Information

Ordering Code	Package Code	Package Description
PI6C5946004ZHIEX	ZH	16-contact, Thin Fine Pitch Quad Flat No-Lead (TQFN)
NT /		

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free. 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm

antimony compounds.

4. E = Pb-free and Green

5. X suffix = Tape/Reel





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the

failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: PI6C5946004ZHIEX