

Three Phase Bridge Rectifier, 25 A, 35 A


D-63

FEATURES

- Universal, 3 way terminals: push-on, wrap around or solder
- High thermal conductivity package, electrically insulated case
- Center hole fixing
- Excellent power/volume ratio
- UL E300359 approved 
- Nickel plated terminals solderable using lead (Pb)-free solder; solder alloy Sn/Ag/Cu (SAC305); solder temperature 260 °C to 275 °C
- Designed and qualified for industrial and consumer level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

I_O	25 A, 35 A
V_{RRM}	50 V to 1600 V
Package	D-63
Circuit configuration	Three phase bridge

DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and instrumentation applications.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES 26MT..	VALUES 36MT..	UNITS
I_O		25	35	A
	T_C	70	60	°C
I_{FSM}	50 Hz	360	475	A
	60 Hz	375	500	
I^2t	50 Hz	635	1130	A ² s
	60 Hz	580	1030	
V_{RRM}		50 to 1600		V
T_J		-55 to +150		°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT T_J MAXIMUM mA
VS-26MT.. VS-36MT..	05	50	75	2
	10	100	150	
	20	200	275	
	40	400	500	
	60	600	725	
	80	800	900	
	100	1000	1100	
	120	1200	1300	
	140	1400	1500	
	160	1600	1700	

**FORWARD CONDUCTION**

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES 26MT..	VALUES 36MT..	UNITS
Maximum DC output current at T_C	I_O	120° rect. conduction angle	25 70	35 60	A °C
Maximum peak, one-cycle non-repetitive forward current	I_{FSM}	$t = 10\text{ ms}$ $t = 8.3\text{ ms}$ $t = 10\text{ ms}$ $t = 8.3\text{ ms}$	No voltage reapplied 100 % V_{RRM} reapplied	Initial $T_J = T_J\text{ maximum}$	A
Maximum I^2t for fusing	I^2t	$t = 10\text{ ms}$ $t = 8.3\text{ ms}$ $t = 10\text{ ms}$ $t = 8.3\text{ ms}$	No voltage reapplied 100 % V_{RRM} reapplied	Initial $T_J = T_J\text{ maximum}$	A ² s
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	I^2t for time $t_x = I^2\sqrt{t} \times \sqrt{t_x}$; $0.1 \leq t_x \leq 10\text{ ms}$, $V_{RRM} = 0\text{ V}$	6360	11 300	A ² √s
Low level of threshold voltage	$V_{F(TO)1}$	$(16.7\% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J\text{ maximum}$	0.88	0.86	V
High level of threshold voltage	$V_{F(TO)2}$	$(I > \pi \times I_{F(AV)})$, $T_J\text{ maximum}$	1.13	1.03	V
Low level forward slope resistance	r_{t1}	$(16.7\% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, $T_J\text{ maximum}$	7.9	6.3	mΩ
High level forward slope resistance	r_{t2}	$(I > \pi \times I_{F(AV)})$, $T_J\text{ maximum}$	5.2	5.0	mΩ
Maximum forward voltage drop	V_{FM}	$T_J = 25\text{ °C}$, $I_{FM} = 40\text{ A}_{pk}$ - per single junction	1.26	1.19	V
Maximum DC reverse current	I_{RRM}	$T_J = 25\text{ °C}$, per junction at rated V_{RRM}	100		μA
RMS isolation voltage	V_{INS}	$T_J = 25\text{ °C}$, all terminal shorted; $f = 50\text{ Hz}$, $t = 1\text{ s}$	2700		V

THERMAL - MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES 26MT	VALUES 36MT	UNITS
Maximum junction and storage temperature range	T_J, T_{Stg}		-55 to +150		°C
Maximum thermal resistance, junction to case	R_{thJC}	DC operation per bridge (based on total power loss of bridge)	1.42	1.35	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth, flat and greased	0.2	0.2	
Approximate weight			20		g
Mounting torque $\pm 10\%$		Bridge to heatsink with screw M4	2.0		Nm




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Forward Voltage Drop Characteristics





Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 6 - Current Ratings Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Total Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current






Fig. 10 - Maximum Non-Repetitive Surge Current


Fig. 11 - Thermal Impedance Z_{thJC} Characteristics



Fig. 12 - Thermal Impedance Z_{thJC} Characteristics

ORDERING INFORMATION TABLE

Device code	VS-	36	MT	160
	①	②	③	④
①	- Vishay Semiconductors product			
②	- Current rating code			
③	- Basic part number			
④	- Voltage code x 10 = V_{RRM}			

26 = 25 A (average)
 36 = 35 A (average)

CIRCUIT CONFIGURATION




LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95251



D-63

DIMENSIONS in millimeters (inches)



Not to scale



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.