

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 34_QLA-01-0-2/112_N

Rev.: C 

Description

Bulkhead adaptor jack/jack
QLA-01 jack (female) / QLA-01 jack (female)

Interface standards
NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 1.4 GHz

Mechanical Data

Number of matings 10000
Weight 0.0046 kg

Environmental Data

Operating Temperature -55 °C to 150 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts (QLA-01)

Centre contact	Material	Copper Beryllium Alloy
Outer contact		
Body	Material	Brass
Insulator		PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Nickel Plating

Piece Parts (QLA-01)

Centre contact	Material	Copper Beryllium Alloy
Outer contact		
Body	Material	Brass
Insulator		PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Nickel Plating

Related Documents

Mounting hole DOU-00009113

Ordering Information

Single package 34_QLA-01-0-2/112_NE
Bulk 100 pcs package 34_QLA-01-0-2/112_NC

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions