



ENGLISH

Datasheet

Aluminium Electrolytic Capacitor

RS Stock number 711-2040




Specifications:

Item	Performance Characteristics																																												
Operating Temperature Range	-40 to +105°C	-25 to +105°C																																											
Rated Voltage Range	6.3 to 100 VDC	160 to 450 VDC																																											
Capacitance Tolerance	± 20% (120Hz, +20°C)																																												
Leakage Current (at 20°C, max.)	I < 0.01 CV or 3 (µA). After 1 minute whichever is greater measured with rated working voltage applied.	I < 0.03 CV or 3 (µA). After 1 minute with rated working voltage applied.																																											
Dissipation Factor (120Hz, 20°C)	<table border="1"> <tr> <td>Working voltage (VDC)</td> <td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td> </tr> <tr> <td>D.F (%) Max.</td> <td>23</td><td>20</td><td>16</td><td>14</td><td>12</td><td>10</td><td>10</td><td>10</td><td>15</td><td>15</td><td>16</td><td>20</td><td>20</td><td>20</td> </tr> </table>															Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20
	Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																														
D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20																															
For capacitance > 1000µ F, add 2% per another 1000µ (+20°C at 120Hz)																																													

Specifications:

Item	Performance Characteristics														
Low Temperature Characteristics (at 120Hz)	Impedance ratio max.														
	W.V (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450
	Z- 25°C/+20°C	4	3	2	2	2	2	2	2	3	3	3	5	6	15
Z- 40°C/+20°C	9	6	4	4	3	3	3	3	-	-	-	-	-	-	
For capacitance value 1000 μ F, add 0.5 per another 1000 μ F for -25°C/+20°C For capacitance value 1000 μ F, add 1 per another 1000 μ F for -40°C/+20°C															
Load Life	Test Conditions: Duration time: 2000hrs Ambient temperature: +105°C Applied voltage: Rated DC working voltage After test requirements: +20°C After test requirements: $\leq \pm 20\%$ of initial measured value Dissipation Factor: $\leq 200\%$ of the initial specified value Leakage Current: \leq the initial specified value														
Shelf Life	Test Conditions: Duration time: 1000hrs Ambient temperature: +105°C Applied Voltage: None After test requirements at +20°C: Same limits as load life. Pre-treatment for measurements shall be conducted after application of DC working voltage for 30 minutes.														

Diagram of Dimensions:



	(Unit: mm)									
D	5	6	8	10	13	16	18	22	25	
F	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	12	
φd	0.5			0.6			0.8			1.0

**Features:**

- Used in communication equipment's, switching power supply, etc.
- Safety vent construction design

Ripple Current & Temperature

Temperature (°C)	45	60	70	85	105
Multiplier	2.10	1.90	1.65	1.40	1.00

Ripple Current & Frequency Multipliers

CAP (μF)/Hz	50 (60)	120	400	1K	10K	50 – 100K
CAP ≤ 10	0.8	1.0	1.30	1.45	1.65	1.70
10 < CAP ≤ 100	0.8	1.0	1.23	1.36	1.48	1.53
100 < CAP ≤ 1000	0.8	1.0	1.16	1.25	1.35	1.38
1000 < CAP	0.8	1.0	1.11	1.18	1.25	1.28

Case Size

Ø D x L (mm)

WV (SV) uF	6.3		{8}		10		{13}		16		{20}		25		{32}		35		{44}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
4.7													5x11	27	5x11	29				
6.8													5x11	35	5x11	38				
10									5x11	38	5x11	40	5x11	42						
22			5x11	50	5x11	56	5x11	60	5x11	65	5x11	70	5x11	78						
33	5x11	56	5x11	60	5x11	65	5x11	70	5x11	78										
47	5x11	68	5x11	72	5x11	100	5x11	105	5x11	110	115	135	5x11	105	5x11	110	115			
68	5x11	77	5x11	82	5x11	105	5x11	110	5x11	115	135	6.3x11	120	6.3x11	140					
100	5x11	98	5x11	110	5x11	115	5x11	120	5x11	125	150	6.3x11	150	6.3x11	165	180				
220	5x11 6.3x11	160 180	6.3x11	180	6.3x11	220 230	6.3x11 8x11	220 230	6.3x11	240	8x11	240	8x11	240	8x11	300 330	8x11	10x12	300 330	
330	6.3x11	200	6.3x11 8x11	260 280	6.3x11	300	8x11	300	8x11	350 355	8x11 10x12	350 355	8x11	410 420	10x12 10x15	410 420				
470	6.3x11 8x11	280 310	6.3x11 8x11	300 315	6.3x11	380 400	8x11 10x12	380 400	8x11	415 445 460	8x14 10x12 10x15	415 445 460	8x11	480 520	10x17 10x20	480 520				
560	8x11	320	8x11	330	8x11	410	10x12	410	10x12	460	10x15	460	10x12	540	10x17	540				
680	8x11	360	10x12	420	10x12	480	10x12	480	10x12	520	10x15	520	10x12	650	10x20	650				
820	8x11	390	10x12	480	10x12	550	10x15	550	10x15	640	10x15	640	10x12	780	10x20	780				
1000	8x11	420	10x12 10x15	530 580	10x12	570 630	8x15 10x15 10x17	570 630	10x15	740 800 850	10x15 10x17 10x20	740 800 850	10x15	870 880	10x25 13x21	870 880				
1200	10x15	480	10x15	650	10x15	710	10x20	710	10x20	850	10x20	850	10x20							
1500	10x15	620	10x17	770	10x17	820	10x20	820	10x20	910	13x21	910	13x21	970	13x26	970				
2200	10x17 10x20	780 800	10x17 10x20	870 900	10x17	1020 1060	13x21 13x26	1020 1060	13x21	1210 1270 1270	13x21 13x26 16x16	1210 1270 1270	13x21	1300 1400	16x26 16x31	1300 1400				
2700	10x20	850	13x21	920	13x21	1100	13x21	1100	13x21	1330	16x26	1330	16x26	1500	16x31	1500				
3300	10x20 13x21	970 1010	10x25 13x21	1110 1160	13x21	1220 1240	13x21 13x26	1220 1240	13x21	1480 1540	16x26 16x31	1480 1540	16x26	1680	16x36	1680				
4700	10x25 13x21	1160 1200	13x21 13x26	1360 1380	16x26	1620	16x26	1620	16x26	1800	16x31	1800	16x31	1900	18x36	1900				
5600	13x26	1320	16x26	1510	16x31	1720	16x31	1720	16x31	1890	16x36	1890	16x36	2000	18x36	2000				
6800	16x26	1470	16x26	1680	16x31	1880	16x31	1880	16x31	2040	18x36	2040	18x36	2090	18x41	2090				
8200	16x26	1520	16x31	1840	16x36	1950	16x36	1950	16x36	2090	18x36	2090	18x36	2180	22x42	2180				
10000	16x26 16x31	1690 1740	16x36 18x36	1900 1990	16x36	2060 2080	18x36 18x41	2060 2080	16x36	2200	22x42	2200	22x42	2300	25x44	2300				
15000	16x36 18x36	2080 2190	18x36	2230	22x40	2300	22x40	2300	22x40	2500	22x42	2500	22x42	-	-	-				

Ripple Current(mA,rms)at105□120Hz

Case Size uF	50 {63}		63 {79}		100 {125}		160 {200}		200 {250}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.1	5x11	1.3	5x11	1.3	5x11	1.3	-	-	-	-
0.22	5x11	2.9	5x11	2.9	5x11	2.9	-	-	-	-
0.33	5x11	4.2	5x11	4.2	5x11	4.2	-	-	-	-
0.47	5x11	8	5x11	8	5x11	8	5x11	12	5x11	12
1	5x11	14	5x11	14	5x11	15	5x11	17	6.3x11	17
2.2	5x11	20	5x11	21	5x11	22	6.3x11	28	6.3x11	33
3.3	5x11	28	5x11	28	5x11	30	6.3x11	32	6.3x11	43
4.7	5x11	32	5x11	34	5x11	38	6.3x11 8x11	38 42	8x11	51
6.8	5x11	40	5x11	42	6.3x11	47	8x11	58	10x12	63
10	5x11	50	5x11	51	6.3x11	60	8x11 10x12	75 78	10x12 10x15	83 90
22	5x11	75	5x11 6.3x11	75 85	6.3x11 8x11	98 105	10x15	105	10x20	135
33	5x11 6.3x11	90 95	6.3x11 8x11	105 115	8x11 10x12	145 155	10x20	170	13x21	180
47	6.3x11	120	6.3x11 8x11	145 155	10x12 10x15	170 180	13x21	210	13x21 13x28	220 230
68	8x11	155	8x11	185	10x15	240	13x28	280	16x28	300
100	8x11	200	10x12	240	10x20	290	13x28 16x28	320 330	16x28	360
220	10x12 10x15	350 380	10x17 10x20	400 430	13x28 16x28	530 580	16x38	580	18x38	590
330	10x17 10x20	450 470	13x21	570	16x28	680	18x31	710	18x38	740
470	13x21	610	13x21 13x28 16x28	640 700 720	16x28 16x31	840 880	18x41	880	22x42	890
560	13x21	680	13x28	770	16x38	880	-	-	-	-
680	13x28	770	16x28	880	16x38	920	-	-	-	-
820	13x28	850	16x28	920	18x31	970	-	-	-	-
1000	13x28 16x28	900 1010	16x32 16x38	1190 1220	18x41	1250	-	-	-	-
1500	16x31	1300	18x31	1350	22x42	1500	-	-	-	-
2200	18x38	1550	18x38	1590	25x44	1880	-	-	-	-
2700	18x38	1610	22x42	1720	-	-	-	-	-	-
3300	18x38	1780	22x42	1900	-	-	-	-	-	-
4700	22x42	2050	25x44	2200	-	-	-	-	-	-
5600	25x42	2180	-	-	-	-	-	-	-	-
6800	25x44	2280	-	-	-	-	-	-	-	-

Ripple Current(mA,rms)at105□120Hz

Case Size WV {SV} uF	Ø D x L (mm)															
	250		{300}		350		{400}		400		{450}		450		{500}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.47	5x11	12	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15	6.3x11	15
1	6.3x11	17	6.3x11	20	8x11	22	8x11	22	8x11	22	8x11	22	8x11	22	8x11	22
2.2	8x11	36	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39	10x12	39
3.3	8x11	43	10x12	53	10x12 10x15	53	53	55	10x15 10x20	53	55	55	10x15 10x20	53	55	55
4.7	10x12	51	10x12 10x15	63	66	66	10x15	69	10x15	69	10x20	64	10x20	64	10x20	64
6.8	10x12	70	10x15	79	10x15	85	10x15	85	10x15	85	10x20	75	10x20	75	10x20	75
10	10x15	90	10x20	110	10x15 10x20 13x21	100 112 115	10x20 13x21	110	10x20 13x21	110	13x21 13x26	92	13x21 13x26	92	98	98
22	10x20	160	13x26	180	13x21 16x26	170 190	13x21 16x26	180	13x21 16x26	180	16x26 16x31	175 180	16x26 16x31	175 180	16x26 16x31	175 180
33	13x21 13x26	175	180	16x26	190	16x26	220	16x26	16x26	220	16x36	210	16x36	210	16x36	210
47	13x26	240	16x31	250	16x31	300	16x31	300	16x31	300	16x36	280	16x36	280	16x36	280
68	16x26	320	16x31	330	16x36	355	16x36	355	16x36	355	18x36	330	18x36	330	18x36	330
100	16x31	400	18x36	420	18x36	450	18x36	450	18x36	450	-	-	-	-	-	-
120					18x31	440			18x31	440						

Ripple Current(mA,rms)at105□120Hz