


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - , 1985.
 © COPYRIGHT 1985 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

DIN 46247

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AI	-						
		E97-9621	A	726389-3 WAS E85-9173-12, -1,1--1,-2,1--2,1--3 ADDED	26JUN85	LOHR	-
			B	VERSION 1-726389-4 ADDED	21DEC89	SCHNAUB.	-
			C	NEW CAD-DRAWING, TOL. AT MATERIAL ADDED	02APR91	A.HO	-
			D	NEW DRAWING	04JAN97	STOLZ	FELDMEIER
	F1	MIN. 2.5µm Cu WAS MIN. 1.5µm Cu	25FEB03	STOLZ	FELDMEIER		



- ① MIN. 4.5 µm Sn OVER MIN. 2.5 µm Cu
 - ② MIN. 3µm Sn OVER MIN. 0.8µm Ni
 - ③ PACKING: MAX. 3000 PIECES
PACKED INTO CARDBOARD BOX
 - ④ RECOMMENDED DIA. FOR PCB: ø1.4 -0.1
-
- ① MIN. 4.5 µm Sn ÜBER MIN. 2.5 µm Cu
 - ② MIN. 3µm Sn ÜBER MIN. 0.8µm Ni
 - ③ VERPACKUNG: MAX. 3000 TEILE
IN KARTON VERPACKT
 - ④ EMPFOHLENE LEITERPLATTENBOHRUNG: ø1.4 -0.1

0.8	1-726389-4	②	CuZn
0.8	1-726389-3	MIN. 2 µm Ni	CuZn
0.8	1-726389-2	①	CuZn
0.8	1-726389-1	PLAIN BLANK	CuZn
0.5	726389-3	MIN. 2 µm Ni	CuZn
0.5	726389-2	①	CuZn
0.5	726389-1	PLAIN BLANK	CuZn
"A" DIMENSION MASS	AMP ORDER NO. BESTELL-NR.	SURFACE OBERFLAECHE COLOUR/FARBE	MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WEITZEL 28-MAY-85	AMP AMP Deutschland GmbH D - 63225 Langen
DIMENSIONS: mm		CHK PFEIFER 28-MAY-85	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		APVD MORITZ 02-JUL-85	FASTON TAB 4.8 FLACHSTECKER 4.8
MATERIAL SEE TABLE SIEHE TABELLE		PRODUCT SPEC ACCORDING TO DIN 46244	SIZE A3
ANGLES FINISH ±-		APPLICATION SPEC WEIGHT -	CAGE CODE 00779
SEE TABLE SIEHE TABELLE		CUSTOMER DRAWING	DRAWING NO C=726389
			RESTRICTED TO -
			SCALE 5:1
			SHEET 1 OF 1
			REV F1