Switch-mode Power Rectifiers

These state-of-the-art devices are a series designed for use in switching power supplies, inverters and as free wheeling diodes.

Features

- Ultrafast 35 and 60 Nanosecond Recovery Time
- 175°C Operating Junction Temperature
- High Voltage Capability to 600 V
- ESD Ratings:
 - Machine Model = C
 - Human Body Model = 3B
- Low Forward Drop
- Low Leakage Specified @ 150°C Case Temperature
- Current Derating Specified @ Both Case and Ambient Temperatures
- SUR8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- All Packages are Pb-Free*

Mechanical Characteristics:


- Case: Epoxy, Molded
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds




ON Semiconductor®

http://onsemi.com

ULTRAFAST RECTIFIERS 15 AMPERES, 100–600 VOLTS



MARKING DIAGRAMS



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ORDERING INFORMATION See detailed ordering and shipping information in the package

dimensions section on page 7 of this data sheet.

© Semiconductor Components Industries, LLC, 2014 February, 2014 – Rev. 10

MAXIMUM RATINGS

		MUR/SUR8					
Rating	Symbol	1510	1515	1520	1540	1560	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	100	150	200	400	600	V
Average Rectified Forward Current (Rated V _R)	I _{F(AV)}	15 @ $T_{\rm C}$ = 150°C 15 @ $T_{\rm C}$ = 145°C		А			
Peak Rectified Forward Current (Rated V _R , Square Wave, 20 kHz)	I _{FRM}	$30 @ T_C = 150^{\circ}C$ $30 @ T_C = 145^{\circ}C$		А			
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I _{FSM}	200 150		A			
Operating Junction Temperature and Storage Temperature Range	T _J , T _{stg}	-65 to +175			°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS


Characteristic	Symbol	Value	Unit
MUR1510 Series: Thermal Resistance Junction-to-Case Junction-to-Ambient	R _{θJC} R _{θJA}	1.5 73	°C/W
MURF1560: Thermal Resistance Junction-to-Case Junction-to-Ambient	${\sf R}_{ heta {\sf JC}} \ {\sf R}_{ heta {\sf JA}}$	4.25 75	°C/W

ELECTRICAL CHARACTERISTICS


Characteristic	Symbol	1510	1515	1520	1540	1560	Unit
Maximum Instantaneous Forward Voltage (Note 1) (i _F = 15 A, T _C = 150°C) (i _F = 15 A, T _C = 25°C)	VF		0.85 1.05		1.12 1.25	1.20 1.50	V
Maximum Instantaneous Reverse Current (Note 1) (Rated DC Voltage, $T_C = 150^{\circ}C$) (Rated DC Voltage, $T_C = 25^{\circ}C$)	i _R		500 10		500 10	1000 10	μΑ
Maximum Reverse Recovery Time (I _F = 1.0 A, di/dt = 50 A/μs)	t _{rr}		35			60	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width = 300 μ s, Duty Cycle \leq 2.0%.



MUR1510G, MUR1515G, MUR1520G, SUR81520G



100 200 iF, INSTANTANEOUS FORWARD CURRENT (AMPS) 100 T_J = 150°C C 50 150 IR, REVERSE CURRENT (MA) 100°C 20 25°C 10 10 100°C 5 2 1 0.5 1 25°C 0.2 0.1 0.05 0.02 L 150 0.1 200 250 300 0.2 1.0 1.2 1.4 1.6 350 400 450 500 550 600 650 0.4 0.6 0.8 **v**_E INSTANTANEOUS VOLTAGE (VOLTS) V_R, REVERSE VOLTAGE (VOLTS) Figure 11. Typical Forward Voltage Figure 12. Typical Reverse Current I_{F(AV)}, AVERAGE FORWARD CURRENT (AMPS) 16 10 I_{F(AV)}, AVERAGE FORWARD CURRENT (AMPS) dc 9.0 14 dc 8.0 $R_{\theta JA} =$ 16°C/W As Obtained 12 Square Wave From A Small TO-220 7.0 Square Wave Heatsink 10 6.0 8.0 5.0 4.0 dc 6.0 3.0 4.0 Square Wave **Rated Voltage Applied** 2.0 $R_{\theta JA} = 60^{\circ}C/W$ 2.0 1.0 As Obtained in Free Air, No Heat Sink 0 0 160 170 180 160 200 140 150 20 60 100 120 140 180 0 40 80 T_C, CASE TEMPERATURE (°C) T_A, AMBIENT TEMPERATURE (°C) Figure 13. Current Derating, Case Figure 14. Current Derating, Ambient IFSM; NON-REPETITIVE SURGE CURRENT (A) 000'01 01 01 P_{F(AV)}, AVERAGE POWER DISSIPATION (WATTS) 16 I_{PK} =5.0 dc (Capacitive Load) 14 I_{A\} 10 12 10 20 Square Wave 8.0 $\frac{I_{PK}}{I_{PK}} = \pi$ 6.0 (Resistive-Inductive Load) IAV 4.0 T_J = 125°C 2.0 0 10 100 1,000 10,000 0 2.0 4.0 6.0 8.0 10 12 14 16 $t_{\text{p}},$ SQUARE WAVE PULSE DURATION (µs) IF(AV), AVERAGE FORWARD CURRENT (AMPS) Figure 16. Typical Non-Repetitive Surge Figure 15. Power Dissipation Current

MUR1560G, MURF1560G, SUR81560G

* Typical performance based on a limited sample size. ON Semiconductor does not guarantee ratings not listed in the Maximum Ratings table.




Figure 19. Thermal Response, (MURF1560G) Junction-to-Ambient ($R_{\theta JA}$)





Figure 20. Typical Capacitance

ORDERING INFORMATION

Device	Package	Shipping [†]
MUR1510G	TO-220AC (Pb-Free)	50 Units / Rail
MUR1515G	TO-220AC (Pb-Free)	50 Units / Rail
MUR1520G	TO-220AC (Pb-Free)	50 Units / Rail
SUR81520G	TO-220AC (Pb-Free)	50 Units / Rail
MUR1540G	TO-220AC (Pb-Free)	50 Units / Rail
MUR1560G	TO-220AC (Pb-Free)	50 Units / Rail
SUR81560G	TO-220AC (Pb-Free)	50 Units / Rail
MURF1560G	TO-220FP (Pb-Free)	50 Units / Rail


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





DOCUMENT NUMBER:	98AON52563E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	TO-220 FULLPACK, 2-LEA	JLLPACK, 2-LEAD				
the suitability of its products for any pa	articular purpose, nor does ON Semiconducto	stries, LLC dba ON Semiconductor or its subsidiaries in the United States y products herein. ON Semiconductor makes no warranty, representation r assume any liability arising out of the application or use of any product or ncidental damages. ON Semiconductor does not convey any license under	r circuit, and specifically			





4. ANODE

4. CATHODE

DOCUMENT NUMBER:	98ASB42149B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	TO-220, 2-LEAD		PAGE 1 OF 1			

ON Semiconductor and (1) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

Email Requests to: orderlit@onsemi.com onsemi Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

<u>MUR1510</u> <u>MUR1510G</u> <u>MUR1515</u> <u>MUR1515G</u> <u>MUR1520G</u> <u>MUR1540G</u> <u>MUR1540G</u> <u>MUR1540G</u> <u>MUR1540G</u> <u>MUR1560G</u>