



PRODUCT DATA SHEET

CRYSTAL CONTROLLED OSCILLATORS

4 PIN 5.0V HCMOS VCXO

	MAXIMUM RATINGS		1	1	1		TABLE 1.0
PARAMETER		UNITS	MINIMUM	NOMINAL	MAXIMUM	UNITS	NOTE
Storage Temper	rature		-40	-	85	°C	
Supply Voltage		(Vcc)	-0.5	-	7	Vdc	
Control Voltage		(Vc)	-0.5	-	7	Vdc	
	CIFICATIONS						
MODEL NUMBE	ER		1		1		TABLE 2.0
HV51-xxx	Frequency Stability:		-25	-	25	ppm	1
HV52-xxx	Frequency Stability:		-50	-	50	ppm	1
HV53-xxx	Frequency Stability:		-100	-	100	ppm	1
HV54-xxx	Frequency Stability:		-20	-	20	ppm	1
HV55-xxx	Frequency Stability:		-10	-	10	ppm	1
HV56-xxx	Frequency Stability:		-5	-	5	ppm	1
Pullability C	odes (xxx - Add code	to the en	d of the M	odel Numb	per)		TABLE 3.
040	Frequency Pullability:		±20	-	-	ppm	2
100	Frequency Pullability:		±50	-	-	ppm	2
150	Frequency Pullability:		±75	-	-	ppm	2
160	Frequency Pullability:		±80	-	-	ppm	2
200	Frequency Pullability:		±100	-	-	ppm	2
250	Frequency Pullability:		±125	-	-	ppm	2
300	Frequency Pullability:		±150	-	-	ppm	2, 3
350	Frequency Pullability:		±175	-	-	ppm	2, 3
400	Frequency Pullability:		±200	-	-	ppm	2, 3
OPERATING	SPECIFICATIONS						TABLE 4.0
PARAMETER			MINIMUM	NOMINAL	MAXIMUM	UNITS	NOTE
Frequency Rang	je	(Fo)	.080	-	29.999999	MHz	
Operating Temp	erature Range		0	-	70	°C	
Supply Voltage		(Vcc)	4.75	5.0	5.25	Vdc	
Supply Current		(lcc)	-	-	20	mA	
Jitter (BW=10H	z to 20MHz)		-	-	5	ps rms	
Jitter (BW=12kH	Hz to 20MHz)		-	-	1	ps rms	
SSB Phase Nois	se at 100Hz offset		-	-90	-	dBc/Hz	
SSB Phase Nois	se at 1KHz offset		-	-100	-	dBc/Hz	
SSB Phase Nois	se at 10KHz offset		-	-125	-	dBc/Hz	
SSB Phase Nois	se at 100KHz offset		-	-135	-	dBc/Hz	
INPUT CHAP	RACTERISTICS						TABLE 5.0
PARAMETER			MINIMUM	NOMINAL	MAXIMUM	UNITS	NOTE
Control Voltage	Range	(Vc)	0.5	2.5	4.5	Vdc	
Center Frequent	су		2.0	2.5	3.0	Vdc	
Monotonic Linea	arity		-15	-	15	%	
Input Impedance	e		-	50K	-	Ohm	
Modulation Band	dwidth (3dB)		15	-	-	KHz	
HCMOS OUT	TPUT CHARACTERIST	ICS					TABLE 6.0
PARAMETER			MINIMUM	NOMINAL	MAXIMUM	UNITS	NOTE
			-	-	15	pF	NOTE
-	High)	(Voh)	4.5	-	-	Vdc	1
voitage (I	ngn/	(101)	4.5	-	-	Vuc	<u> </u>

PARAMETER		MINIMUM	NOMINAL	MAXIMUM	UNITS	NOTE	
LOAD			-	-	15	pF	
Voltage (High)		(Voh)	4.5	-	-	Vdc	
(Low)		(Vol)	-	-	0.5	Vdc	
Current (80 KHz to 15.999 MHz)	(High)	(loh)	-4	-	-	mA	
(80 KHz to 15.999 MHz)	(Low)	(loh)	-	-	4	mA	
Current (16 MHz to 29.999 MHz)	(High)	(loh)	-8	-	-	mA	
(16 MHz to 29.999 MHz)	(Low)	(loh)	-	-	8	mA	
Duty Cycle at 50% of Vcc			45	50	55	%	
Rise / Fall Time 10% to 90%			-	3	5	ns	

PACKAGE CHARACTERISTICS

Package

TABLE 7.0 Hermetically sealed, metal package.

CW 0426 HV52-150 • 24.704M


HV51-xxx Series HV52-xxx Series HV53-xxx Series HV54-xxx Series HV55-xxx Series HV56-xxx Series

DESCRIPTION

The Connor-Winfield HV5x-xxx series is a 5.0V HCMOS, 14 Pin DIP hermetically sealed, Voltage Controlled Crystal Oscillator (VCXO). Based on a fundamental crystal design the HV5x-xxx is designed for phased lock loop applications requiring low jitter and tight stability.

FEATURES

5.0V OPERATION LOW JITTER <1ps RMS FREQUENCY STABILITY HV51-xxx SERIES ±25PPM HV52-xxx SERIES ±50PPM HV53-xxx SERIES ±100PPM HV54-xxx SERIES ±20PPM HV55-xxx SERIES ±10PPM HV56-xxx SERIES ±5PPM TEMPERATURE RANGE: 0 to 7°C HERMETICALLY SEALED PACKAGE



Specifications subject to change without notice. a Copyright 2001 Connor-Winfield all rights reserved.

DATA SHEET #: _____VX014____PAGE_1__OF_2___REV:_07___DATE:_04/28/06

THE CONNOR-WINFIELD CORP. 2111 COMPREHENSIVE DRIVE. AURORA, IL 60505. FAX (630) 851-5040. PHONE (630) 851-4722. www.comwin.com

PRODUCT DATA SHEET

CRYSTAL CONTROLLED OSCILLATORS

Note:

.~∕~-

- Frequency stability vs. change in temperature, referenced to frequency measured at 25°C with control voltage @ 2.50Vdc.
- 2) Referenced to Fo @ 25°C. Positive Slope.
- 3) The wider frequency pullabilies are not available with models HV55 or HV56 series.

