

2019-V1.0-0318 Specifications

AC-DC Din Rail Mounted Power Supply IS-480 Series, 480W

PAIRUI ELECTRONICS

No. 545 Museum Road Yangzhou, Jiangsu China 225009 Tel: 86 (514) 8279 1592 Fax: 86 (514) 8769 3159 2019

AC-DC Din Rail Mountable Power Supply IS-480 SERIES, SINGLE PHASE INPUT

Features


- 3 Year Warranty
- Universal Input 90~264Vac
- 100% Full Load Burn-in Test
- Cooling by Free Air Convection
- All Round Protections: Short Circuit, Over Voltage, Over Current, Over Temperature
- LED Indicator for DC Power On
- LED Indicator for DC Low

Applications

- Process Control
- Factory Automation

- Traffic & Transportation System
- Other Industrial Applications

Electrical







Electrical

Part Number	Nominal	Output	Output Ripp	Ripple	Effici	ency	Certificate
	Input Voltage	Voltage	Current	(Max.)	Min	Тур	Certificate
IS480-24	100-240VAC	24V	20A	1%Vo mVp-p	93%	94%	CE, FCC, CB, UL, CUL
IS480-48	100-240VAC	48V	10A	1%Vo mVp-p	93%	94%	CE, FCC, CB, UL, CUL

NOTE:

1. The ripple values are measured at 20MHz of bandwidth by using a 12'' twisted pair-wire terminated with 0.1uF & 47uF parallel capacitor under ambient temperature 25°C at rated input voltage and rated load;

2. The efficiency values are measured under ambient temperature 25° C at rated input voltage and rated load.



INPUT

PARAMETER	CONDITIONS	MIN	ТҮР	MAX	UNITS
Input voltage		90		264	Vac
Input frequency		47		63	Hz
Input current	Full load, Vin=115Vac Full load, Vin=230Vac			5 2.5	A A
	Cold start, Vin=115Vac Cold start, Vin=230Vac			40 80	A A
Inrush current	 This product is built in inrush limiting from surge current damages when the per- can occur by repeating the input voltage sufficient interval should be given betwee power; To avoid connecting the switch or fuse the power supply), more consideration of the parts that can endure the inrush current 	ower is e on and een turr e to inp should b	turned l off rap ning on a ut term	on. Malf idly. The and off t inal(out	unction erefore, he side of
Power factor(PF)	Full load, Vin=115Vac Full load, Vin=230Vac		0.99 0.97		
Stand-by power consumption	Vin=230Vac			5	W
Surge voltage	L-N			2	KV



<u>OUTPUT</u>

PARAMETER	CONDITIONS	MIN	ТҮР	МАХ	UNITS	
Output voltage accuracy				2	%	
	IS480-24 IS480-48		22-27 43-52		V V	
Output voltage adjustment range	Output voltage can be adjusted within above range by V-ADJ. variable resistance inside of the power supply. When output voltage exceeds the range, the power supply will be in failure or get into over voltage protection mode. To avoid the case that the output voltage is higher than rated voltage, output current should be used under rated current					
Minimum load		0			%	
Line regulation	Vin from 100Vac to 240Vac			2	%	
Load regulation	Vout from min. to max.			3	%	
Turn-on delay time	Full load, Vin=115Vac		3600		ms	
Hold up time	Full load, Vin=115Vac		20		ms	



Protection

Short circuit	Hiccuo mode, it will recover automatically after fault condition is removed
	IS480-24: over voltage protection value 32V IS480-48: over voltage protection value 62V
Over voltage	 (1) When output voltage exceeds above over voltage protection value or reversal voltage occurs, the protection will be started and the output voltage will be cut off in order to protect the power supply; (2) The power supply will recover after the power is turned on again
Over current	IS480-24: over current protection value 30A IS480-48: over current protection value 15A
	 (1) When output voltage exceeds above over current protection value, the protection will be started and the output voltage will be cut off in order to protect the power supply; (2) The power supply will recover automatically after the fault condition is removed
	Over temperature protection value: 110±10°C
Over temperature	 (1) When the ambient temperature exceeds above over temperature protection value, the protection will be started and go into hiccup mode; (2) The power supply will recover automatically after the fault condition is removed



Environment

PARAMETER	CONDITIONS	MIN	ТҮР	MAX	UNITS	
Ambient operating temperature	Startup at rated voltage	-25		+70	°C	
Operating relative humidity	Non condensing	20		95	%	
Storage temperature	Humidity 5 ~ 95% RH	-40		+85	°C	
MTBF	Full load, 220Vac input, 25°C ambient 230			Khrs		
DC-OK led	LED(Green) DC OK LED light will be ON when properly operated					
DC-Low led	LED(Red) DC Low LED light will be ON: (1) when output voltage is below 85%(±2.5%) from the rated output voltage; (2) when get over voltage, over current, over temperature and short circuit fault					
Colling	Free air convection					
Mounting method	Vertical					
Dimension(W x H x D)	60.0 x 130.0 x 125.0mm (2.36 x 5.12 x 4.92inch)					
Weight	1000g					
Packing	11pcs/12.5kg/0.7cuft/carton Carton size 620 x 260 x 175mm(LxWxH)					




Safety/EMC


Isolation voltage	I/P-O/P: 3KVac, I/P-FG: 1.5KVac, O/P-FG: 0.5KVac
Insulation resistance	100MΩ Max./500VDC
Safety	Design refer to UL60950-1, EN60950-1
EMC	EN 55032:2015 EN 61000-3-2:2014 (IEC 61000-3-2:2014) EN 61000-3-3:2013 (IEC 61000-3-3:2013) EN 55024:2010+A1:2015


NOTE: Unless otherwise specified, all the above parameters are measured at ambient temperature of 25° and Vin=100Vac to 240Vac.




<u>Mechanical</u>













<u>Mechanical</u>




Marking	No.	Assignment	
+	1	DC(+) Output Terminal	
+	2		
-	3		
-	4	DC(-) Output Terminal	
L	5	AC(L) Input Terminal	
N	6	AC(N) Input Terminal	
	7	AC Grounding Terminal	
V-ADJ.	/	DC Output voltage adjustment trimmer	
DC OK	/	DC Output OK indication LED(Green)	
DC LOW	/	DC Output Low indication LED(Red)	



Electrical Curve




Block Diagram





Package




Outer Ca	liton	
L 620 x W	260 x H	185mm

SERIES	QTY/BOX	QTY/CARTON	NET WEIGHT	GROSS WEIGHT	VOLUME
IS-480	1 piece	11 boxes	11kg/carton	12.5kg/carton	0.7cuft/carton



1. Series Operation




Note:

1. Series operation can be connected as shown in above;

2. Load current should be less than the current value of the product with the lowest output current specified at the product specification with the power supply at series connection.



2. Parallel Operation



0000 0000 + + -0 0 000 0000 $> \circ$ LOAD \bigcirc \bigcirc \bigcirc 0 0 LN 🕀 L N 🕀 000 000

Parallel Operation C (Backup)

Note:

1. Parallel operation should be composed with the same products, while the connection should be as shown as "Parallel operation C";


2. In parallel operation C, current capacity cannot be increased, while it should be used for backup only. Moreover, diode that is to be added during parallel operation should be selected after considering it's voltage drop, output voltage and current capacity.



3. Mounting Method


(1) How to fix

Firstly hang A part on the top of Rail as shown in below, then push the power supply into B direction to fix it.



(2) How to remove

Remove the power supply to D direction, pulling C part by using tools, such as a screwdriver, to downward direction.






3. Mounting Method

(3) Mounting Spacing

Mounting method should be considered with airflow. Leave enough space between the units when several units are mounted together. Forced air cooling makes protection against heat better.





4. Cautions

(1) Please confirm if the capacity of the product is suitable for your intended application before putting it in use;

(2) Only the rated input voltage specified on the product should be used;

(3) Only the wires with rated capacity should be connected to this product, as allowable voltage and current is varied according to each type of wire;

(4) Ground terminal of the power supply must be grounded before use to prevent electric shock or electromaganetic interference;

(5) Be cautions to keep the product clean as foreign matter near the input & output terminal or inside if the product could cause series damages;

(6) If a fuse installed in the product blows off, the product should experience damages not only to the fuse but also to other parts as well. Therefore, the product is to be required for maintenance work from customer service department as well as replacement of the fuse;

(7) Due to constant leakage current flows within the product, extra caution should be made if multiple number of products are used connecting to each other as total leakage current c-ould be amounted beyond the capacity;

(8) Be sure to avoid any physical contact with the product since some of the parts inside of the product are being functioned at high voltage, which could cause serious electric shock;

(9) For the purpose of safety as well as reliability of the product, please avoid using the product at the following sites:

- A place near water or fire
- A place with high room temperature and poor ventilation
- A place with a presence of foreign subject or dust
- A place near volatile or flammable compounds
- A place with high humidity
- A place vulnerable for vibration or shock

(10) Do not inspect or repair the product while the power is applied;

(11) Unauthorized modification should be avoided in order to prevent series injury or physical loss due to any malfunction;

(12) In case of power outage while in operation, be sure to turn off the power supply.



5. Warranty

(1) Repair service will be provided for free upon any mechanical, technical or functional defects during the guaranteed warranty, however, any defects or malfunction due to international infliction or negligence by customers will be repaired at the customer's expense;

(2) Guaranteed warranty of the product runs for 3 years, while appearance and specification of the product is subject for change without any prior notification for the purpose of quality improvement of the product.



Update Record

Date	Version	Updated Content	Updated By	Approved By
2019/01/18	2019-V1.0-0118	File created		
2019/03/18	2019-V1.0-0318	File updated		