

Plastic Epitaxial Fast Recovery Rectifiers

Features


- Guardring for overvoltage protection
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed

250°C /10 seconds at terminals

Lead free in comply with EU RoHS 2011/65/EU directives

Mechanical Data

- Case: DO-201AD/ DO-27
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.98 g /0.0345oz



Maximum Ratings and Electrical Characteristics T_A = 25°C unless otherwise specified

Parameter	SYMBOLS MARKING	MUR420	MUR440	MUR460	MUR480	MUR4100	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	200	400	600	800	1000	V
Maximum average forward rectified current	I _{F(AV)}	4.0					A
Non-repetitive peak forward surge current 8.3 ms singlehalf sine-wave	I _{FSM}	100					A
@I _F =4.0A Maximum forward voltage	V _F	0.89	1.28		1.70		V
Maximum reverse current	I _R	10					μA
		100					
I _F =0.5A , I _R =1.0A ,I _{RR} =0.25A MAX. reverse recovery time	T _{RR}	25	50		75		nS
Typical thermal resistance (Note 1)	R _{θJA}	25					°C/W
V _R =4.0V ,f=1MHz Type junction capacitance	C _J	185			150		pF
Operating junction and storage temperature rang	T _J , T _{STG}	-55 --- +150					°C


Note:

1) Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length, PCB mounted.


Plastic Epitaxial Fast Recovery Rectifiers

Characteristic Curves


TYPICAL FORWARD CHARACTERISTIC



FORWARD CURRENT DERATING CURVE



MAXIMUM NON REPETITIVE PEAK FORWARD SURGE CURRENT



Typical Reverse Characteristics

