

SS22BF-AT THRU SS220BF-AT

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS

Forward Current-2A

Reverse Voltage-20V to 200V

FEATURES


- ◆ For surface mount applications
- ◆ High forward surge current capability
- ◆ Low power loss,high efficiency
- ◆ Metal silicon junction,majority carriers conduction

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode

MECHANICAL DATA

- ◆ Case: SMBF molded plastic body
- ◆ Terminals: Solderable per MIL-STD-750 , Method 2026
- ◆ Weight: Approximated 0.057 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derating by 20 %.

PARAMETER	SYMBOL	SS22BF-AT	SS24BF-AT	SS26BF-AT	SS28BF-AT	SS210BF-AT	SS212BF-AT	SS215BF-AT	SS220BF-AT	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	20	40	60	80	100	120	150	200	V
Maximum RMS voltage	V_{RMS}	14	28	42	56	70	84	105	140	V
Maximum DC Blocking Voltage	V_{DC}	20	40	60	80	100	120	150	200	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$	2.0								A
Peak Forward Surge Current(Note1)	I_{FSM}	55				45				A
Max Instantaneous Forward Voltage at 2 A	V_F	0.55		0.70		0.85		0.95		V
Maximum DC Reverse Current at Rated DC Blocking Voltage $T_a = 25^\circ\text{C}$ $T_a = 100^\circ\text{C}$	I_R	0.5 5			0.3 3				mA	
Typical Junction Capacitance(Note2)	C_J	220			110				pF	
Typical Thermal Resistance(Note3)	$R_{\theta JA}$	75								$^\circ\text{C/W}$
Operating Junction Temperature Range	T_J	-55 ~ +125								$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150								$^\circ\text{C}$

Notes: 1. Measured at 8.3 ms single half sine wave superimposed on rated load (JEDEC Method).

2. Measured at 1MHz and applied reverse voltage of 4 V D.C.

3. P.C.B. mounted with 2.0" X 2.0" (5cm X 5 cm) copper pad areas.

SS22BF-AT THRU SS220BF-AT

RATINGS AND CHARACTERISTIC CURVES

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current






Fig.6 Typical Transient Thermal Impedance



SS22BF-AT THRU SS220BF-AT

PACKAGE OUTLINE

SMBF



Dimensions in millimeters

ORDERING INFORMATION

Device	Package	Shipping
SS22BF-AT thru SS220BF-AT	SMBF	5,000/Tape & Reel (13 inches)