

Drg No :- C 34594

INSTALLATION DRAWING

ISSUE	REVISION	DATE
1	FIRST ISSUE	19/03/90
2	ENEC 19 ADDED DPCA 14257	04/12/01

SPECIFICATION

ACTUATING FORCE:- 2.5N(9ozf)MAX.
 RELEASE FORCE:- 0.3N(1ozf)MIN.
 FREE POSITION:- 9.2(.36)MAX.
 OPERATING POSITION:- 8.4 ^{±0.3} (.33)
 MOVEMENT DIFFERENTIAL:- 0.1(.004)MAX
 OVERTRAVEL(AVAILABLE):- DEPRESS TO CASE

SPECIAL FEATURE :-
 TESTED AND STAMPED TO U.L. , CSA AND "ENEC 19" REQUIREMENTS

APPROVAL RATING :-
 5 AMP - 125 OR 250V.AC.





DIAGRAM OF CONNECTIONS



SAIA-Burgess Electronics

SWITCHES•MOTORS•CONTROLLERS
 SAIA-Burgess Electronics Limited
 Dukesway, Team Valley Trading Estate
 Gateshead, Tyne & Wear NE11 0UB
 Tel: (0191)4016100, Fax: (0191)4016322



DO NOT SCALE !
 This drawing must only be amended on CAD system

TOLERANCES UNLESS STATED:-
 NO DECIMAL PLACE ± 0.50 1 DECIMAL PLACES ± 0.25
 2 DECIMAL PLACES ± 0.15 ANGULAR $\pm 1^\circ$
 INCH - OUNCE UNITS (IN BRACKETS)

ALL DIMENSIONS SPECIFIED IN MILLIMETRES

DRAWN	P.S.T.	Approved	
DATE	19/03/90	DRAWING OFFICE	
SCALE	4/1	ENGINEERING	
DATE ISSUED		QUALITY ASSURANCE	

TITLE / DESCRIPTION	V4NST7-UL
Drg No :-	C 34594
	A3