


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS SHEET	SHEET QTY.	STD. PKG. QTY.
LJSL9-Y3-2.5	CLEAR POLYESTER GMY3	0.70 [17.78] X 1.33 [33.78]	80	32	2500

CLEAR AREA
WHITE IMPRINT AREA TYP.



NOTES:
1. MILLIMETERS ARE IN [].

8.267 ± .062
[210 ± 1.6]



.70 [17.78]

TYP. 10 PLCS.
TOL. NON-ACCUM.

.33 [8.38]

TYP. 8 PLCS.

1.33 [33.78]

TYP. 8 PLCS.

11.693 ± .062 [297 ± 1.6]



TITLE	
LJSL9-Y3-2.5 LASER INKJET SELF-LAMINATING LABEL CUSTOMER DRAWING	
ITEM REVISION NAME	100472TF/02
DATASET FILE NAME	100472TF-DC-C10334/02C
MATERIAL:	SEE TABLE
DRAWING NUMBER:	C10334
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	.x ± .12 [3.04] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±
THIRD ANGLE PROJECTION	
DRAWN BY	RVU
DATE	7/30/04
CHK	MSAD
SCALE	NTS
SHT 1 OF 1	A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	4/17/13	RVU	CLW	MSAD	.025 [.635] WAS .025 [6.35]. 3 PLACES DIMENSIONS. ADD +/- .062.	GAECN00785
2	3/25/13	RVU	CLW	MSAD	UPDATE NOTES, TOLERANCES AND TABLE. REMOVE LJSL9-Y3***-2.5 (ALL COLOR EXCEPT WHITE). REDUCE FORMAT FROM B TO A. CHANGE MATERIAL FROM GMY2 TO GMY3.	GAECN00688
1	7/21/06	RVU			ADD +/- .031 TO .33 DIM.	4600
0	7/30/04	RVU			DRAWING RELEASE.	3673

D101000DA/15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[LJSL9-Y3-2.5](#)