

**Industrial Ethernet  
IE-C6FP8LD0100M40V40-D**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Assembled IE cables, patch cable Cabinet Line, Cat. 6,  
LSZH, grey, 90° angled on one side

**General ordering data**

Order No.	<a href="#">1248280100</a>
Type	IE-C6FP8LD0100M40V40-D
Version	Patch cable, RJ45 IP 20, Angled 90°, RJ45 IP 20, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010), LSZH, 10 m
GTIN (EAN)	4050118044812
Qty.	1 pc(s).

**Industrial Ethernet  
IE-C6FP8LD0100M40V40-D**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	10 m	Net weight	395 g
--------	------	------------	-------

**Temperatures**

Operating temperature	-20 °C...+60 °C	Storage temperature	-20 °C...+60 °C
Installation temperature	0 °C...+50 °C		

**Downloads**

Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class EA Category 6A, 2 connector channel	ac107535.pdf	Canadian UL approval	DUXZ7.E349758.pdf
UL Approval	DUXR.E316369.pdf		

**Electrical properties**

Current-carrying capacity at 50 °C	1 A	Dielectric strength, contact / contact	≥ 1000 V DC
Dielectric strength, contact / shield	≤ 1500 V DC	PoE / PoE+	conforming to IEEE 802.3at

**Standards**

Application-specific communication cable facilities	ANSI / TIA / EIA-568-B.2-10, ISO / IEC 11801:2002, EN50173-1:2007	Connector standard	IEC 60603-7-51
---	---	--------------------	----------------

**Cable structure**

Copper diameter	0.43 mm	Strands	7
Cross-section	4*2*AWG 27/7 - 4*2*0.1 mm <sup>2</sup>	Insulation	PE
Insulation cross-section	1.04 mm	No. of wires	8
Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white/blue - blue, white/orange - orange, white/green - green, white/brown - brown
Shielding	S/FTP	Complete shielding	Shielding braid made from copper wiring
Overlap of shielding braid	60 %	Material sheath	LSZH
Sheath diameter, min.	5.5 mm	Sheath diameter, max.	5.9 mm

**Electrical properties of cable**

Category	Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)	Test voltage: wire-wire-shield, at RMS 50Hz, 1 min.	750 V
Characteristic impedance	100 ± 15 Ω at 1–100 MHz	Deviation	25 ns/100m
Resistance differential	5 %	Capacity at 1 kHz	46 nF/km

**Mechanical and material properties of cable**

Min. bending radius, once only	25 mm	Min. bending radius, repetitive	50 mm
Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685	Halogen	in accordance with IEC 60754-2

Creation date December 5, 2012 11:24:50 AM CET

Catalogue status 06.11.2012 / We reserve the right to make technical changes.

**Data sheet...**

**Industrial Ethernet  
IE-C6FP8LD0100M40V40-D**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**plug**

Version connector left	RJ45 IP 20, Angled 90°	Version connector right	RJ45 IP 20
------------------------	------------------------	-------------------------	------------

**Classifications**

ETIM 2.0	EC001262	ETIM 3.0	EC001262
eClass 6.0	27-06-18-01	eClass 7.0	27-06-18-01

**Approvals**

Approvals



**Industrial Ethernet  
IE-C6FP8LD0100M40V40-D**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings****Wiring**

---

RJ45	1	white, orange	1	RJ45
	2	orange	2	
	3	white, green	3	
	4	blue	4	
	5	white, blue	5	
	6	green	6	
	7	white, brown	7	
	8	brown	8	

---

---