

# ECS-.327-12.5-13X-C

32.768 KHz Tuning Fork Crystal



The ECS-.327-12.5-13X-C tuning fork type crystal is used as a clock source in communication equipment, measuring instruments, microprocessors and other time management applications. Their low power consumption makes these crystals ideal for portable equipment.

Request a Sample

## ECS-.327-12.5-13X-C



- Cost Effective
- Tight Tolerance
- Long Term Stability
- Excellent Resistance and **Environmental Characteristics**
- Pb Free/RoHS Compliant

# **OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS**

PARAMETERS		ECS327-12.5-13X-C	UNITS
Frequency	Fo	32.768	KHz
Frequency Tolerance	Δf/fo	±10	ppm
Load Capacitance	$C_L$	12.5	рF
Drive Level (max)	DL	1	μW
Resistance At Series Resonance	R <sub>1</sub>	35(max)	ΚΩ
Q-Factor	Q	70,000(typ.)	
Turnover Temperature	ure T <sub>M</sub> +25 ±5		°C
Temperature Coefficient	ß	-0.040ppm/°C² max.	PPM/ΔC°
Shunt Capacitance	Co	1.35 (typ.)	рF
Capacitance Ratio		450 (typ.)	
Operating Temp	Topr	-20 ~ +70	°C
Storage Temperature	Tstg	-40 ~ +85	°C
Shock Resistance		Drop 3 times on hard wooden board from height of 75cm / ±5 ppm max.	PPM
Insulation Resistance	IR	500 MΩ min./DC100V	МΩ
Aging (First Year)	Δf/fo	±3 ppm max. @ +25°C ±3°C	
Motional Capacitance	C <sub>1</sub>	0.0030(typ.)	рF

# **DIMENSIONS (mm)**





Figure 1) ECS-2X6X

#### RECOMMENDED OSCILLATION CIRCUIT




## **ELECTRICAL CHARACTERISTICS**

IC: TC 4069P Rf: 10MΩ Rd: 330KΩ (As required)  $C_1 = 22pF, C_2 = 22pF$  $V_{DD} = 3.0V$ 

In this circuit, low drive level with a maximum of 1uW is recommended. If excessive drive is applied, irregular oscillation or quartz element fractures may occur.

#### PARABOLIC TEMPERATURE CURVE



To determine frequency stability, use parabolic curvature. For example: What is the stability at 45°C?

1) Change in T (°C)

= 45 -25 = 20°C 2) Change in frequency =  $-0.04 \text{ PPM x } (\Delta T)^2$ 

 $= -0.04 PPM \times (20)^2$ = -16.0 PPM

## **PART NUMBERING GUIDE:**

Manufacture	er	Frequency		Load Capacitance	Package Type*		**Tolerance Spec.
ECS	_	.327	_	12.5	- 13X	_	C

<sup>\*</sup> Package type example (13X = 2x6)

<sup>\*\*</sup> C = ±10 ppm