

P Series

One piece metal shell panel receptacle with large solder cups. The insert is non-removable. The "P" Series is front mountable only and the male and female have different mounting dimensions.

Part drawings ar available courtesy of <u>www.Neutrik.com</u>. For additional drawings, please contact <u>NeutrikUSA</u>.

ORDERING INFORMATION "P" Series Male						
# of	me Shell					
Contacts	Silver contacts	Silver Contacts	Gold Contacts			
3	NC3MP	NC3MP-BAG	NC3MP-B			
4	NC4MP	NC4MP-BAG	NC4MP-B			
5	NC5MP	NC5MP-BAG	NC5MP-B			
6	NC6MP	NC6MP-BAG	NC6MP-B			


Male "P" Series not available in 6 pin Switchcraft equivalent or 7 pin configurations


ORDERING INFORMATION "P" Series Female							
#	Nickel Shell	Black Chro	me Shell				
# of Contacts	Silver contacts	Silver Contacts	Gold Contacts				
3	NC3FP	NC3FP-1-BAG	NC3FP-1-B				
4	NC4FP	NC4FP NC4FP-1-BAG					
5	NC5FP	NC5FP-1-BAG	NC5FP-1-B				
6	NC6FP-1	NC6FP-1-BAG	NC6FP-1-B				
6*	NC6FPS-1	NC6FPS-1-BAG	NC6FPS-1-B				
7	NC7FP-1	N/A	NC7FP-1-B				


*Switchcraft© equivalent

Frontplattenausschnitt (Rückseite)


Panel cut out (rear side)









				*)Lieferant darf ohne Ruecksprache nicht geaendert werden
				Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)
				Benennung:
				NC4
A	Aktuelle Zeichnung	24.03.98	Alin jak	
Ind.	Aenderung	Datum	Name	NEUTRIK




Frontplattenausschnitt (Rückseite)

Panel cut out (rear side)





				*)Lieferant darf ohne Ruecksprache nicht geaendert werden
				Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)
				Benennung:
				NC-
Ind.	Aenderung	Datum	Name	NEUTRIK



Specification	s - XLR Cable	e Connect	tors					
Electrical		X Series	X-1 Series	RC Series	X-HD Series	FX-S Series	FZ-L Series	FX- Spec Series
Number of contacts:	3-7	x	3 only	x	3	3 only	3 only	3 only
Rated Current:	see table below	x	x	x	x	x	6A	x
Contact resistance:	< 3 mΩ	X	X	X	X	X	X	X
Insulation resistance initial:	>2·109mΩ	x	x	x	x	x	x	x
Insulation resistance after damp heat test:	>1.109m Ω	x	x	x	x	x	x	x
Dielectric strength:	1500 V dc	X	X	X	X	X	X	X
Mechani		X Series	X-1 Series	RC Series	X-HD Series	FX-S Series	FZ-L Series	FX- Spec Series
Insertion/withdrawa force:	I ≤ 20N	x	x	x	x	x	x	x
Max. Wire Size:	see table below	x	x	x	x	x	x	x
Cable O.D. range:	3.5mm - 8.0mm	x	4mm - 7mm	4mm - 7mm	x	x	5mm - 6.7mm	x
Environmental		X Series	X-1 Series	RC Series	X-HD Series	FX-S Series	FZ-L Series	FX- Spec Series
Temperature range:	-30°C to +80°C	x	x	x	x	x	x	x
Flammability:	UL 94HB	X	X	X	X	X	X	X
Solderability:	Complies with IEC 68-2-20	x	x	x	x	x	x	x
Protection Class :		N/A	N/A	N/A	IP65	N/A	N/A	N/A
Materials		X Series	X-1 Series	RC Series	X-HD Series	FX-S Series	FZ-L Series	FX- Spec Series
Shell:	ZnAl4Cu1, black Chrome over Cu plating	×	×	x	×	x	x	Black Cr. Only
Cover:	EPDM (natural rubber)	N/A	N/A	N/A	N/A	N/A	x	N/A
Insert:	PA 6.6 30% GR (glass reinforced)	x	x	x	x	x	x	x

Locking Ring :	ZnAl4Cu1, gal Ni or black Chrome over Cu plating	N/A	N/A	N/A	N/A	N/A	×	Black Cr.
Contacts:	female (3 pole) CuSn6	x	x	x	x	x	x	N/A
Contacts:	female (4-7 pole) & male CuZn 39P63	x	x	x	x	N/A	N/A	N/A
Contact surface:	gal 0.3 µm Au hard alloy over 2 µm Ni	x	x	x	x	x	gal 0.1 µm AuCo hard alloy over 2 µm Ni15 (Tribor)	Silvor
Latch lock:	St3K32 (latch)/CK 67 (spring)	x	x	x	x	x	x	x
Strain relief clamp:	POM	X	X	X	X	X	X	X
Antikink boot:	PUR	X	X	X	PUR	X	EPDM	X

XLR Rated Current						
Х	1[A]	C[pF]				
3	16	2.5/14	≤ 4			
4	10	1.5/16	≤ 7			
5	7.5	1.0/18	≤ 7			
6	7.5	1.0/18	≤ 7			
7	5	1.0/18	≤ 9			

Part drawings are available courtesy of

www.neutrik.com. For additional drawings, please contact NeutrikUSA.