

Polypropylene (PP) Film and Foil Capacitors for Pulse Applications in PCM 7.5 mm to 15 mm. Capacitances from 100 pF to 0.22 µF. Rated Voltages from 63 VDC to 1000 VDC.

Special Features

- Pulse duty construction
- Very low dissipation factor
- Negative capacitance change versus temperature
- Very low dielectric absorption
- According to RoHS 2011/65/EU

Typical Applications

For high frequency applications e.g.

- Sample and hold
- Timing
- LC-Filtering
- Oscillating circuits
- Audio equipment

Construction


Dielectric:

Polypropylene (PP) film

Capacitor electrodes:

Metal foil

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations:

Tinned wire.

Marking:

Colour: Red. Marking: Black.

Electrical Data

Capacitance range:

100 pF to 0.22 µF (E12-values on request)

Rated voltages:

63 VDC, 100 VDC, 250 VDC, 400 VDC, 630 VDC, 850 VDC, 1000 VDC

Capacitance tolerances:

±20%, ±10%, ±5%

Operating temperature range:

-55° C to +105° C

Test specifications:

In accordance with IEC 60384-13

Climatic test category:

55/100/56 in accordance with IEC

Insulation resistance at +20° C:

≥ 3 x 10⁵ MΩ

Measuring voltage:

U_r = 63 V: U_{test} = 50 V/1 min.

U_r ≥ 100 V: U_{test} = 100 V/1 min.

Test voltage: 2 U_r, 2 sec.

Maximum pulse rise time:

1000 V/µsec.

Dielectric absorption:

0.05 %

Temperature coefficient:

-200 x 10⁻⁶/° C (general guide)

Dissipation factors at +20° C: tan δ

at f	C ≤ 0.1 µF	0.1 µF < C ≤ 0.22 µF
1 kHz	≤ 5 x 10 ⁻⁴	≤ 5 x 10 ⁻⁴
10 kHz	≤ 6 x 10 ⁻⁴	≤ 6 x 10 ⁻⁴
100 kHz	≤ 8 x 10 ⁻⁴	-

Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from +85° C for DC voltages and from +75° C for AC voltages.

Reliability:

Operational life > 300 000 hours

Failure rate < 5 fit (0.5 x U_r and 40° C)

Mechanical Tests

Pull test on pins:

10 N in direction of pins according to IEC 60068-2-21

Vibration:

6 hours at 10...2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

Low air density:

1 kPa = 10 mbar in accordance with IEC 60068-2-13

Bump test:

4000 bumps at 390 m/sec² in accordance with IEC 60068-2-29

Packing

Available taped and reeled.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data

Capacitance	63 VDC/40 VAC*					100 VDC/63 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF						3	8.5	10	7.5	FKP3D001002B00_____
150 "						3	8.5	10	7.5	FKP3D001502B00_____
220 "						3	8.5	10	7.5	FKP3D002202B00_____
330 "						3	8.5	10	7.5	FKP3D003302B00_____
470 "						3	8.5	10	7.5	FKP3D004702B00_____
680 "						3	8.5	10	7.5	FKP3D006802B00_____
1000 pF						3	8.5	10	7.5	FKP3D011002B00_____
1500 "						3	8.5	10	7.5	FKP3D011502B00_____
2200 "						3	8.5	10	7.5	FKP3D012202B00_____
3300 "						3	8.5	10	7.5	FKP3D013302B00_____
4700 "						3	8.5	10	7.5	FKP3D014702B00_____
6800 "						4	9	10	7.5	FKP3D016802C00_____
0.01 µF						4	9	10	7.5	FKP3D021002C00_____
0.015 "	4	9	10	7.5	FKP3C021502C00_____	4	9.5	13	10	FKP3D021503D00_____
0.022 "	4	9.5	13	10	FKP3C022203D00_____	5	11	13	10	FKP3D022203F00_____
0.033 "	4	9.5	13	10	FKP3C023303D00_____	6	12	13	10	FKP3D023303G00_____
0.047 "	5	11	13	10	FKP3C024703F00_____	5	11	18	15	FKP3D024704B00_____
0.068 "	6	12	13	10	FKP3C026803G00_____	6	12.5	18	15	FKP3D026804C00_____
0.1 µF	6	12.5	18	15	FKP3C031004C00_____	7	14	18	15	FKP3D031004D00_____
0.15 "	8	15	18	15	FKP3C031504F00_____	9	16	18	15	FKP3D031504J00_____
0.22 "	9	16	18	15	FKP3C032204J00_____					


Capacitance	250 VDC/160 VAC*					400 VDC/250 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	3	8.5	10	7.5	FKP3F001002B00_____	3	8.5	10	7.5	FKP3G001002B00_____
150 "	3	8.5	10	7.5	FKP3F001502B00_____	3	8.5	10	7.5	FKP3G001502B00_____
220 "	3	8.5	10	7.5	FKP3F002202B00_____	3	8.5	10	7.5	FKP3G002202B00_____
330 "	3	8.5	10	7.5	FKP3F003302B00_____	3	8.5	10	7.5	FKP3G003302B00_____
470 "	3	8.5	10	7.5	FKP3F004702B00_____	3	8.5	10	7.5	FKP3G004702B00_____
680 "	3	8.5	10	7.5	FKP3F006802B00_____	3	8.5	10	7.5	FKP3G006802B00_____
1000 pF	3	8.5	10	7.5	FKP3F011002B00_____	3	8.5	10	7.5	FKP3G011002B00_____
1500 "	3	8.5	10	7.5	FKP3F011502B00_____	4	9	10	7.5	FKP3G011502C00_____
2200 "	4	9	10	7.5	FKP3F012202C00_____	4	9	10	7.5	FKP3G012202C00_____
						4	9.5	13	10	FKP3G012203D00_____
3300 "	3	9	13	10	FKP3F013303A00_____	4	9.5	13	10	FKP3G013303D00_____
4700 "	4	9.5	13	10	FKP3F014703D00_____	5	11	13	10	FKP3G014703F00_____
6800 "	5	11	13	10	FKP3F016803F00_____	6	12	13	10	FKP3G016803G00_____
0.01 µF	5	11	13	10	FKP3F021003F00_____	5	11	18	15	FKP3G021004B00_____
0.015 "	6	12	13	10	FKP3F021503G00_____	6	12.5	18	15	FKP3G021504C00_____
						5	11	18	15	FKP3F021504B00_____
0.022 "	6	12.5	18	15	FKP3F022204C00_____	7	14	18	15	FKP3G022204D00_____
0.033 "	7	14	18	15	FKP3F023304D00_____	8	15	18	15	FKP3G023304F00_____
0.047 "	8	15	18	15	FKP3F024704F00_____	9	16	18	15	FKP3G024704J00_____
0.068 "	9	16	18	15	FKP3F026804J00_____					

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

$d = 0.5 \phi$ if $W = 3$
 $d = 0.6 \phi$ if $W \geq 4$ } PCM 7.5 and 10
 $d = 0.8 \phi$ if PCM = 15



Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J

Packing: bulk = S
Pin length: 6-2 = SD

Taped version see page 161.

Rights reserved to amend design data without prior notification.

Continuation

General Data

Capacitance	630 VDC/300 VAC*					850 VDC/300 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	3	8.5	10	7.5	FKP3J001002B00_____	3	8.5	10	7.5	FKP3M001002B00_____
150 "	3	8.5	10	7.5	FKP3J001502B00_____	3	8.5	10	7.5	FKP3M001502B00_____
220 "	3	8.5	10	7.5	FKP3J002202B00_____	3	8.5	10	7.5	FKP3M002202B00_____
330 "	3	8.5	10	7.5	FKP3J003302B00_____	3	8.5	10	7.5	FKP3M003302B00_____
470 "	3	8.5	10	7.5	FKP3J004702B00_____	3	8.5	10	7.5	FKP3M004702B00_____
680 "	3	8.5	10	7.5	FKP3J006802B00_____	3	8.5	10	7.5	FKP3M006802B00_____
1000 pF	4	9	10	7.5	FKP3J011002C00_____	4	9	10	7.5	FKP3M011002C00_____
1500 "	4	9.5	13	10	FKP3J011503D00_____	4	9.5	13	10	FKP3M011503D00_____
2200 "	4	9.5	13	10	FKP3J012203D00_____	4	9.5	13	10	FKP3M012203D00_____
3300 "	5	11	13	10	FKP3J013303F00_____	5	11	13	10	FKP3M013303F00_____
4700 "	6	12	13	10	FKP3J014703G00_____	6	12	13	10	FKP3M014703G00_____
6800 "	5	11	18	15	FKP3J016804B00_____	5	11	18	15	FKP3M016804B00_____
0.01 µF	6	12.5	18	15	FKP3J021004C00_____	6	12.5	18	15	FKP3M021004C00_____
0.015 "	8	15	18	15	FKP3J021504F00_____	8	15	18	15	FKP3M021504F00_____
0.022 "	9	16	18	15	FKP3J022204J00_____	9	16	18	15	FKP3M022204J00_____
0.033 "	9	16	18	15	FKP3J023304J00_____					

Capacitance	1000 VDC/300 VAC*				
	W	H	L	PCM**	Part number
100 pF	3	8.5	10	7.5	FKP3O101002B00_____
150 "	3	8.5	10	7.5	FKP3O101502B00_____
220 "	3	8.5	10	7.5	FKP3O102202B00_____
330 "	3	8.5	10	7.5	FKP3O103302B00_____
470 "	3	8.5	10	7.5	FKP3O104702B00_____
680 "	3	8.5	10	7.5	FKP3O106802B00_____
1000 pF	4	9	10	7.5	FKP3O111002C00_____
1500 "	4	9.5	13	10	FKP3O111503D00_____
2200 "	4	9.5	13	10	FKP3O112203D00_____
3300 "	5	11	13	10	FKP3O113303F00_____
4700 "	6	12	13	10	FKP3O114703G00_____
6800 "	5	11	18	15	FKP3O116804B00_____
0.01 µF	6	12.5	18	15	FKP3O121004C00_____
0.015 "	8	15	18	15	FKP3O121504F00_____
0.022 "	9	16	18	15	FKP3O122204J00_____


Part number completion:
 Tolerance: 20 % = M
 10 % = K
 5 % = J
 Packing: bulk = S
 Pin length: 6-2 = SD
 Taped version see page 161.

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

$d = 0.5 \phi$ if $W = 3$
 $d = 0.6 \phi$ if $W \geq 4$
 $d = 0.8 \phi$ if $\text{PCM} = 15$






Rights reserved to amend design data without prior notification.






Continuation page 43

Continuation

Impedance change with frequency
(general guide).



Permissible AC voltage
in relation to frequency
at 10° C internal temperature rise
(general guide).



Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{max.} \leq 125^{\circ}C$
soldering: $T_{max.} \leq 135^{\circ}C$

Polypropylene: preheating: $T_{max.} \leq 100^{\circ}C$
soldering: $T_{max.} \leq 110^{\circ}C$

Single wave soldering

Soldering bath temperature: $T < 260^{\circ}C$


Dwell time: $t < 5 \text{ sec}$

Double wave soldering

Soldering bath temperature: $T < 260^{\circ}C$

Dwell time: $\Sigma t < 5 \text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



WIMA Quality and Environmental Philosophy

ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories by the infaz (Institut für Auditierung und Zertifizierung) certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2011/65/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2011/65/EU

WIMA capacitors are lead free in accordance with RoHS 2011/65/EU

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 162)	ROLL/AMMO			AMMO				
	REEL	φ 360 max. φ 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions	REEL	φ 360 max. φ 30 ±1	52 ±2 58 ±2 or 66 ±2	REEL	φ 500 max. φ 25 ±1
Unit	see details page 163.							

Dims in mm.

* Diameter of pins see General Data.


* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P₀ = 12.7 or 15.0 is possible


Please clarify customer-specific deviations with the manufacturer.

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

- WIMA supplier number
- Date code
- Customer's P/O number
- P/O line
- Customer's part number
- WIMA part number
- Quantity
- WIMA confirmation number
- Country of origin
- Customer name
- Handling unit number
- Week of delivery.

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- technical note
- capacitance tolerance
- packing
- connecting information

BARCODE PDF417
BARCODE 2D Datamatrix

WIMA Best Capacitors Made in Germany	
Werk Aurich	
Supplier-ID: LIEF.NR.	Date Code: 20210419
Purchase Order No. (P/O): Bestellung xyz	P/O line: 100
Customer Part No.: KUNDENTEILENUMMER	
WIMA Part No.: MKP1F041006B00KSSD	Quantity: 459
WIMA Confirmation No.: 0001105072000100	
Customer No.: 0000100002	RoHS 2011/65/EU
Gross Weight [g]: 4557	COO: DE
WIMA - MKP 10 WIMA Part No.: MKP1F041006B00KSSD MKP 10 1.0 µF 250 VDC 11x21x31.5 RM27.5 Standard 10% Lose - Standard Drähte 6-2 Vorlage Debitor Inland	
	0001105072000100
1002021443	QTY: 459 Week 19/2021

Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm



PCM	Size				bulk	pcs. per packing unit								
						ROLL		REEL				AMMO		
	W	H	L	Codes		S	H16.5	H18.5	ø 360	ø 500	340 x 340	490 x 370		
					N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000		2200	2500				2800		
	3	7.5	4.6	0C	5000		2000	2300				2300		
	3.8	8.5	4.6	0D	5000		1500	1800				1800		
	4.6	9	4.6	0E	5000		1200	1500				1500		
	5.5	10	4.6	0F	5000		900	1200				1200		
5 mm	2.5	6.5	7.2	1A	5000		2200	2500				2800		
	3	7.5	7.2	1B	5000		2000	2300				2300		
	3.5	8.5	7.2	1C	5000		1600	2000				2000		
	4.5	6	7.2	1D	6000		1300	1500				1500		
	4.5	9.5	7.2	1E	4000		1300	1500				1500		
	5	10	7.2	1F	3500		1100	1400				1400		
	5.5	7	7.2	1G	4000		1000	1200				1200		
	5.5	11.5	7.2	1H	2500		1000	1200				1200		
	6.5	8	7.2	1I	2500		800	1000				1000		
	7.2	8.5	7.2	1J	2500		700	1000				1000		
	7.2	13	7.2	1K	2000		700	950				1000		
	8.5	10	7.2	1L	2000		600	800				800		
8.5	14	7.2	1M	1500		600	800				800			
11	16	7.2	1N	1000		500	600				640			
7.5 mm	2.5	7	10	2A	5000			2500	4400			2500		
	3	8.5	10	2B	5000			2200	4300			2300	4150	
	4	9	10	2C	4000			1700	3200			1700	3000	
	4.5	9.5	10.3	2D	3500			1500	2900			1400	2700	
	5	10.5	10.3	2E	3000			1300	2500			1300		
	5.7	12.5	10.3	2F	2000			1000	2200			1100		
	7.2	12.5	10.3	2G	1500			900	1800			1000		
10 mm	3	9	13	3A	3000			1100	2200				1900	
	4	8.5	13.5	FA	3000			900	1600				1450	
	4	9	13	3C	3000			900	1600				1450	
	4	9.5	13	3D	3000			900	1600				1400	
	5	10	13.5	FB	2000			700	1300				1200	
	5	11	13	3F	3000			700	1300				1100	
	6	12	13	3G	2400			550	1100				1000	
	6	12.5	13	3H	2400			550	1100				1000	
8	12	13	3I	2000			400	800				740		
15 mm	5	11	18	4B	2400			600	1200				1150	
	5	13	19	FC	1000			600	1200				1200	
	6	12.5	18	4C	2000			500	1000				1000	
	6	14	19	FD	1000			500	1000				1000	
	7	14	18	4D	1600			450	900				850	
	7	15	19	FE	1000			450	900				850	
	8	15	18	4F	1200			400	800				740	
	8	17	19	FF	500			400	800				740	
	9	14	18	4H	1200			350	700				650	
	9	16	18	4J	900			350	700				650	
22.5 mm	5	14	26.5	5A	1200				800				770	
	6	15	26.5	5B	1000				700				640	
	7	16.5	26.5	5D	760				600				550	
	8	20	28	FH	500				500				480	
	8.5	18.5	26.5	5F	500				480				450	
	10	22	28	FI	570*				420				380	
	10.5	19	26.5	5G	594*				400				360	
	10.5	20.5	26.5	5H	594*				400				360	
11	21	26.5	5I	561*				380				350		
12	24	28	FJ	480*				350				310		

* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.



Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	pcs. per packing unit												
						ROLL		REEL				AMMO						
	W	H	L	Codes		S	N	O	ø 360		ø 500		340 x 340		490 x 370			
								H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	
								F	I	H	J	A	C	B	D			
27.5 mm	9	19	31.5	6A	567*	-	-	-	-	460/340*	-	-	-	-	-	-	-	
	11	21	31.5	6B	459*	-	-	-	-	380/280*	-	-	-	-	-	-	-	
	13	24	31.5	6D	378*	-	-	-	-	300	-	-	-	-	-	-	-	
	13	25	33	FK	405*	-	-	-	-	-	-	-	-	-	-	-	-	
	15	26	31.5	6F	324*	-	-	-	-	270	-	-	-	-	-	-	-	
	15	26	33	FL	324*	-	-	-	-	-	-	-	-	-	-	-	-	
	17	29	31.5	6G	198*	-	-	-	-	-	-	-	-	-	-	-	-	
	17	34.5	31.5	6I	198*	-	-	-	-	-	-	-	-	-	-	-	-	
	20	32	33	FM	162*	-	-	-	-	-	-	-	-	-	-	-	-	-
	20	39.5	31.5	6J	162*	-	-	-	-	-	-	-	-	-	-	-	-	-
37.5 mm	9	19	41.5	7A	441*	-	-	-	-	-	-	-	-	-	-	-	-	
	11	22	41.5	7B	357*	-	-	-	-	-	-	-	-	-	-	-	-	
	13	24	41.5	7C	294*	-	-	-	-	-	-	-	-	-	-	-	-	
	15	26	41.5	7D	252*	-	-	-	-	-	-	-	-	-	-	-	-	
	17	29	41.5	7E	154*	-	-	-	-	-	-	-	-	-	-	-	-	
	19	32	41.5	7F	140*	-	-	-	-	-	-	-	-	-	-	-	-	
	20	39.5	41.5	7G	126*	-	-	-	-	-	-	-	-	-	-	-	-	
	24	45.5	41.5	7H	112*	-	-	-	-	-	-	-	-	-	-	-	-	
	28	38	41.5	7L	84*	-	-	-	-	-	-	-	-	-	-	-	-	
	31	46	41.5	7I	84*	-	-	-	-	-	-	-	-	-	-	-	-	
	35	50	41.5	7J	35*	-	-	-	-	-	-	-	-	-	-	-	-	
40	55	41.5	7K	28*	-	-	-	-	-	-	-	-	-	-	-	-		
48.5 mm	19	31	56	8D	120*	-	-	-	-	-	-	-	-	-	-	-	-	
	23	34	56	8E	80*	-	-	-	-	-	-	-	-	-	-	-	-	
	27	37.5	56	8H	84*	-	-	-	-	-	-	-	-	-	-	-	-	
	33	48	56	8J	25*	-	-	-	-	-	-	-	-	-	-	-	-	
	37	54	56	8L	25*	-	-	-	-	-	-	-	-	-	-	-	-	
52.5 mm	25	45	57	9D	70*	-	-	-	-	-	-	-	-	-	-	-	-	
	30	45	57	9E	60*	-	-	-	-	-	-	-	-	-	-	-	-	
	35	50	57	9F	25*	-	-	-	-	-	-	-	-	-	-	-	-	
	45	55	57	9H	20*	-	-	-	-	-	-	-	-	-	-	-	-	
	45	65	57	9J	20*	-	-	-	-	-	-	-	-	-	-	-	-	

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions. Rights reserved to amend design data without prior notification.

Updated data on www.wima.com



A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2		-		20%	bulk	6 -2		

<p>Type description:</p> <p>SMD-PET = SMDT SMD-PEN = SMDN SMD-PPS = SMDI FKP 02 = FKPO MKS 02 = MKS0 FKS 2 = FKS2 FKP 2 = FKP2 FKS 3 = FKS3 FKP 3 = FKP 3 MKS 2 = MKS2 MKP 2 = MKP2 MKS 4 = MKS4 MKP 4 = MKP4 MKP 10 = MKP1 FKP 4 = FKP4 FKP 1 = FKP1 MKP-X2 = MKX2 MKP-X1 R = MKX1 MKP-Y2 = MKY2 MP 3-X2 = MPX2 MP 3-X1 = MPX1 MP 3-Y2 = MPY2 MP 3R-Y2 = MPRY MKP 4F = MKPF Snubber MKP = SNMP Snubber FKP = SNFP GTO MKP = GTOM DC-LINK MKP 4 = DCP4 DC-LINK MKP 6 = DCP6 DC-LINK HC = DCHC</p>	<p>Rated voltage:</p> <p>50 VDC = B0 63 VDC = C0 100 VDC = D0 250 VDC = F0 400 VDC = G0 450 VDC = H0 520 VDC = H2 600 VDC = I0 630 VDC = J0 700 VDC = K0 800 VDC = L0 850 VDC = M0 900 VDC = N0 1000 VDC = O1 1100 VDC = P0 1200 VDC = Q0 1250 VDC = R0 1500 VDC = S0 1600 VDC = T0 1700 VDC = TA 2000 VDC = U0 2500 VDC = V0 3000 VDC = W0 4000 VDC = X0 6000 VDC = Y0 250 VAC = 0W 275 VAC = 1W 300 VAC = 2W 305 VAC = AW 350 VAC = BW 440 VAC = 4W 500 VAC = 5W ...</p>	<p>Capacitance:</p> <p>22 pF = 0022 47 pF = 0047 100 pF = 0100 150 pF = 0150 220 pF = 0220 330 pF = 0330 470 pF = 0470 680 pF = 0680 1000 pF = 1100 1500 pF = 1150 2200 pF = 1220 3300 pF = 1330 4700 pF = 1470 6800 pF = 1680 0.01 µF = 2100 0.022 µF = 2220 0.047 µF = 2470 0.1 µF = 3100 0.22 µF = 3220 0.47 µF = 3470 1 µF = 4100 2.2 µF = 4220 4.7 µF = 4470 10 µF = 5100 22 µF = 5220 47 µF = 5470 100 µF = 6100 220 µF = 6220 1000 µF = 7100 1500 µF = 7150 ...</p>	<p>Size:</p> <p>4.8x3.3x3 Size 1812 = KA 4.8x3.3x4 Size 1812 = KB 5.7x5.1x3.5 Size 2220 = QA 5.7x5.1x4.5 Size 2220 = QB 7.2x6.1x3 Size 2824 = TA 7.2x6.1x5 Size 2824 = TB 10.2x7.6x5 Size 4030 = VA 12.7x10.2x6 Size 5040 = XA 15.3x13.7x7 Size 6054 = YA 2.5x7x4.6 PCM 2.5 = 0B 3x7.5x4.6 PCM 2.5 = 0C 2.5x6.5x7.2 PCM 5 = 1A 3x7.5x7.2 PCM 5 = 1B 2.5x7x10 PCM 7.5 = 2A 3x8.5x10 PCM 7.5 = 2B 3x9x13 PCM 10 = 3A 4x9x13 PCM 10 = 3C 5x11x18 PCM 15 = 4B 6x12.5x18 PCM 15 = 4C 5x14x26.5 PCM 22.5 = 5A 6x15x26.5 PCM 22.5 = 5B 9x19x31.5 PCM 27.5 = 6A 11x21x31.5 PCM 27.5 = 6B 9x19x41.5 PCM 37.5 = 7A 11x22x41.5 PCM 37.5 = 7B 19x31x56 PCM 48.5 = 8D 25x45x57 PCM 52.5 = 9D ...</p>	<p>Tolerance:</p> <p>±20% = M ±10% = K ±5% = J ±2.5% = H ±1% = E ...</p> <p>Packing:</p> <p>AMMO H16.5 340x340 = A AMMO H16.5 490x370 = B AMMO H18.5 340x340 = C AMMO H18.5 490x370 = D REEL H16.5 360 = F REEL H16.5 500 = H REEL H18.5 360 = I REEL H18.5 500 = J ROLL H16.5 = N ROLL H18.5 = O BLISTER W12 180 = P BLISTER W12 330 = Q BLISTER W16 330 = R BLISTER W24 330 = T Bulk/TPS Standard = S ...</p>
			<p>Version code:</p> <p>Standard = 00 Version A1 = 1A Version A1.1.1 = 1B Version A2 = 2A ...</p>	<p>Pin length (untaped)</p> <p>3.5 ±0.5 = C9 6 -2 = SD 16 ±1 = P1 ... Pin length (taped) none = 00</p>

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

WIMA:

[FKP3F002202B00KSSD](#) [FKP3F004702B00JSSD](#) [FKP3G014703F00JSSD](#) [FKP3G014703F00KSSD](#)
[FKP3J001002B00KSSD](#) [FKP3J001002B00MSSD](#) [FKP3J001502B00JSSD](#) [FKP3J002202B00KSSD](#)
[FKP3J003302B00JSSD](#) [FKP3J004702B00KSSD](#) [FKP3J011503D00JSSD](#) [FKP3J012203D00KSSD](#)
[FKP3J013303F00JSSD](#) [FKP3O111002C00KSSD](#) [FKP3J002202B00JSSD](#) [FKP3J014703G00KSSD](#)
[FKP3J014703G00JSSD](#) [FKP3J004702B00JSSD](#) [FKP3J001002B00JSSD](#) [FKP3C031004C00JSSD](#)
[FKM3G011003A00KSSD](#) [FKP3J004702B00KA00](#) [FKP3-470/630/10P7](#) [FKP3G023304F00JI00](#)
[FKP3J003302B00KSSD](#) [FKP3-2200/630/10P10](#) [FKP3-470/250/5P7](#) [FKP3G021504C00JI00](#) [FKP3G004702B00JA00](#)
[FKP3J001002B00KF00](#) [FKP3-1000/630/10P7](#) [FKP3-220/630/5P7](#) [FKP3-100/1KV/20P7T](#) [FKP3O102202B00KSSD](#)
[FKP3-150/630/5P7](#) [FKP3-330/630/5P7](#) [FKP3-220/250/10P7](#) [FKP3-.033/400/5P15T](#) [FKP3-1000/1KV/10P7](#)
[FKP3J011002C00KSSD](#) [FKP3-4700/400/5P10](#) [FKP3-4700/400/5P10T](#) [FKP3J002202B00KSI0](#) [FKP3-1500/630/5P10](#)
[FKP3-.015/400/5P15T](#) [FKP3-220/630/10P7LL9](#) [FKP3-470/630/5P7](#) [FKM3-1000/400/10P10](#) [FKP3-100/630/20P7](#)
[FKP3F011002B00JC00](#) [FKP3-220/630/10P7](#) [FKP3G014703F00JI00](#) [FKP3-100/630/10P7](#) [FKP3-3300/630/5P10](#)
[FKP3-.01/400/5P15T](#) [FKP3J021004C00KSSD](#) [FKP3G021004B00JI00](#) [FKP3G012203D00KSSD](#)
[FKP3O111503D00JF00](#) [FKP3G011002B00JF00](#) [FKP3G021004B00JSSD](#) [FKP3J013303F00KSSD](#)
[FKP3O111503D00JSSD](#) [FKP3F026804J00JSSD](#) [FKP3J011002C00JSSD](#) [FKP3G011002B00KSSD](#)
[FKP3G011002B00JSSD](#) [FKP3C032204J00KSSD](#) [FKP3F013303A00JSSD](#) [FKP3G011002B00MSSD](#)
[FKP3F011502B00KSSD](#) [FKP3G016803G00JSSD](#) [FKP3O101002B00JSSD](#) [FKP3D023303G00KSSD](#)
[FKP3C032204J00JSSD](#) [FKP3J011503D00MSSD](#) [FKP3C024703F00JSSD](#) [FKP3O104702B00JSSD](#)
[FKP3D031004D00KSSD](#) [FKP3O106802B00JSSD](#) [FKP3J016804B00JD00](#) [FKP3D023303G00JSSD](#)
[FKP3G012202C00KSSD](#) [FKP3O106802B00KSSD](#) [FKP3O121004C00MSSD](#) [FKP3D001002B00MD00](#)
[FKP3J016804B00KB00](#) [FKP3D021002C00MI00](#) [FKP3O101002B00MSSD](#) [FKP3J016804B00JB00](#)
[FKP3O111002C00JA00](#) [FKP3G012203D00JSSD](#) [FKP3D021002C00KSSD](#) [FKP3D031004D00JSSD](#)
[FKP3G013303D00MSC9](#) [FKP3J011002C00KSC9](#) [FKP3D014702B00JSSD](#) [FKP3D021002C00JSSD](#)
[FKP3F013303A00MSSD](#) [FKP3F021003F00JSSD](#)