


Measuring leads

SML 100/1



Product	SML 100/1
description	Silicone measuring lead, 4mm plug with caged spring on both sides. Nickel-plated copper-beryllium contact spring. Highly flexible, double insulated stranded lead, resistant against soldering iron, grip and lead shatter-proof. Built in color indicator for easy identification of insulation damages.
operating instruction	BA401
article-no. / *colour	9733881xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">● 00 black</div> <div style="text-align: center;">● 01 red</div> <div style="text-align: center;">● 02 blue</div> <div style="text-align: center;">● 03 yellow</div> <div style="text-align: center;">● 04 green</div> </div>
drawing	
technical data	
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	0 ⁽²⁾
rated current (consider derating curve)	16 A
material socket	contact pin: brass contact spring: copper - beryllium
housing material	PVC-P
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
cable length	100 cm
conductor size	1 mm ²
cable material	SIL

4 mm system

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022