

Fast Acting Ceramic Tube Fuses - Axial Ledged
Ø6.3mm x 32mm

multicomp PRO

RoHS
Compliant



Electrical Characteristics

Rating	100% Rating		135% Rating		200% Rating	
	Min.	Max.	Min.	Max.	Min.	Max.
500mA - 30A	4hr	-	-	1hr	-	30 Sec

Agency Approvals

Agency

UL Listed
 UL Recognized
 Recognized Component
 for Canada and US
 CSA Certified
 CSA Acceptance
 PSE

Ampere Rating

: 10mA to 15A
 : 15.1A to 30A
 : 15.1A to 30A
 : 100mA to 15A
 : 15.1A to 25A
 : 5.1A to 15A (250V)

Interrupting Rating

500mA to 20A : 10,000A at 125V AC
 500mA to 10A : 750A at 250V DC
 500mA to 1A : 35A at 250V AC
 1.25A to 3.5A : 100A at 250V AC
 4A to 10A : 200A at 250V AC
 10.1A to 15A : 750A at 250V AC/DC
 15.1A to 20A : 750A at 250V AC/DC
 20.1A to 30A : 100A at 250V AC
 400A at 125V DC
 1,000A at 125V AC

Product Characteristics

Operating Temperature : -55°C to 125°C
Material
 Body : Ceramic
 Caps : Nickel Plated Brass
Leads Wire : Ø0.8 mm 12A and less.
 Ø1 mm for rating above 13A to 19A.
 Ø1.2 mm for rating above 20A.



Mechanical Dimensions (mm)


NO.	Part Name		Volume
d3	Dia. of Ceramic	5.72 ±0.2mm	
d4	Dia. of Cap	7 ±0.3mm	
d5	Dia. of Lead Wire Length of Lead Wire	(1) ±0.05mm 38 ±2mm	
L1	Total Length W/Cap-on on Both Ends		33 ±0.75mm

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Mechanical Dimensions





Part Number Table

Ampere Rating (A)	Voltage Rating (V)	Nominal Cold Resistance (Ohms)	Nominal Melting I2t (A2 sec.)	Part Number	
500mA	250V	0.6879	0.1603	MP004290	
750mA		0.3129	0.3544	MP004291	
800mA		0.2828	0.4032	MP004292	
1A		0.1886	0.72	MP004293	
1.25A		0.1428	1.2713	MP004294	
1.5A		0.1132	1.8225	MP004295	
2A		0.1987	5.388	MP004296	
2.5A		0.0794	5.625	MP004297	
3A		0.0635	7.128	MP004298	
3.5A		0.0538	10.584	MP004299	
4A		0.0329	13.824	MP004300	
4.5A		0.0302	27.338	MP004301	
5A		0.0286	33.75	MP004302	
6A		0.0233	58.45	MP004303	
6.3A		0.0184	73.514	MP004304	
7A		0.0164	88.2	MP004305	
7.5A		0.0143	101.25	MP004306	
8A		0.0124	115.2	MP004307	
10A		0.0105	255.46	MP004308	
12A		0.0086	398.39	MP004309	
13A		0.0085	517.14	MP004310	
15A		0.0061	567	MP004311	
16A		0.006	645.12	MP004312	
18A		0.0055	874.8	MP004313	
20A		0.0044	1283	MP004314	
25A		0.0036	2691	MP004315	
30A			0.0026	4155.3	MP004316

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.