



| REV. | DESCRIPTION                    | DATE     | APPROVED |
|------|--------------------------------|----------|----------|
| B    | Engineering Update w/o Changes | 02/23/04 | M. C.    |
| C    | Added 03-NL-BK Material Code   | 08/27/07 | M. C.    |
| D    | Updated Model                  | 07/23/08 | M. C.    |
| E    | Removed Material Code          | 05/21/16 | J. C.    |

| PART NO. | H          | F          | T          |
|----------|------------|------------|------------|
| 460-060  | .060 (1.5) | .010 (.25) | .040 (1.0) |
| 460-070  | .070 (1.8) | .015 (.38) |            |
| 460-080  | .080 (2.0) | .020 (.51) |            |
| 460-090  | .090 (2.3) | .025 (.64) |            |
| 460-100  | .100 (2.5) | .030 (.76) |            |
| 460-110  | .110 (2.8) | .035 (.89) |            |
| 460-120  | .120 (3.0) | .040 (1.0) |            |
| 460-130  | .130 (3.3) | .045 (1.1) |            |
| 460-140  | .140 (3.6) | .050 (1.3) |            |
| 460-150  | .150 (3.8) | .055 (1.4) |            |
| 460-160  | .160 (4.1) | .060 (1.5) |            |
| 460-170  | .170 (4.3) | .065 (1.7) |            |
| 460-180  | .180 (4.6) | .070 (1.8) |            |
| 460-190  | .190 (4.8) | .075 (1.9) |            |
| 460-200  | .200 (5.1) | .080 (2.0) |            |
| 460-210  | .210 (5.3) | .085 (2.2) |            |

| PART NO. | H           | F          | T          |
|----------|-------------|------------|------------|
| 461-360  | .360 (9.1)  | .010 (.25) | .340 (8.6) |
| 461-380  | .380 (9.7)  | .020 (.51) |            |
| 461-400  | .400 (10.2) | .030 (.76) |            |
| 461-420  | .420 (10.7) | .040 (1.0) |            |
| 461-440  | .440 (11.2) | .050 (1.3) |            |
| 461-460  | .460 (11.7) | .060 (1.5) |            |
| 461-480  | .480 (12.2) | .070 (1.8) |            |
| 461-500  | .500 (12.7) | .080 (2.0) |            |
| 461-520  | .520 (13.2) | .090 (2.3) |            |
| 461-540  | .540 (13.7) | .100 (2.5) |            |

| PART NO. | H           | F          | T           |
|----------|-------------|------------|-------------|
| 462-560  | .560 (14.2) | .010 (.25) | .540 (13.7) |
| 462-580  | .580 (14.7) | .020 (.51) |             |
| 462-600  | .600 (15.2) | .030 (.76) |             |
| 462-620  | .620 (15.7) | .040 (1.0) |             |
| 462-640  | .640 (16.3) | .050 (1.3) |             |
| 462-660  | .660 (16.8) | .060 (1.5) |             |
| 462-680  | .680 (17.3) | .070 (1.8) |             |
| 462-700  | .700 (17.8) | .080 (2.0) |             |
| 462-720  | .720 (18.3) | .090 (2.3) |             |
| 462-730  | .730 (18.5) | .095 (2.4) |             |
| 462-740  | .740 (18.8) | .100 (2.5) |             |

| PART NO. | H          | F          | T          |
|----------|------------|------------|------------|
| 465-200  | .200 (5.1) | .025 (.64) | .150 (3.8) |
| 465-210  | .210 (5.3) | .030 (.76) |            |
| 465-220  | .220 (5.6) | .035 (.89) |            |
| 465-230  | .230 (5.8) | .040 (1.0) |            |
| 465-240  | .240 (6.1) | .045 (1.1) |            |
| 465-250  | .250 (6.4) | .050 (1.3) |            |
| 465-260  | .260 (6.6) | .055 (1.4) |            |
| 465-270  | .270 (6.9) | .060 (1.5) |            |
| 465-280  | .280 (7.1) | .065 (1.7) |            |
| 465-290  | .290 (7.4) | .070 (1.8) |            |
| 465-300  | .300 (7.6) | .075 (1.9) |            |
| 465-310  | .310 (7.9) | .080 (2.0) |            |
| 465-320  | .320 (8.1) | .085 (2.2) |            |
| 465-330  | .330 (8.4) | .090 (2.3) |            |
| 465-340  | .340 (8.6) | .095 (2.4) |            |
| 465-350  | .350 (8.9) | .100 (2.5) |            |



2. MATERIAL: NYLON 6/6, 94V-2, NATURAL.

1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

| STANDARD TOLERANCE<br>(UNLESS OTHERWISE SPECIFIED) |                          | BIVAR®   |  |
|--|--------------------------|--|--|
| DECIMALS   | ANGULAR                  | 4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |  |
| .X ± .1  | X° ± 1°                  | <b>TITLE:</b> T-1 (3mm) & T-1 3/4 (5mm)<br>INDIVIDUAL LED MOUNTS       |  |
| .XX ± .01  |                          | <b>PART NO:</b> 46X-XXX  |  |
| .XXX ± .005  |                          | <b>REVISION:</b> E   |  |
| DESIGNED:<br><b>D. Green</b>                       | DATE:<br><b>08/07/03</b> | <b>CAGE CODE :</b> 32559   |  |
| CHECKED:<br><b>M. Chen</b>                         | DATE:<br><b>08/07/03</b> | <b>SHEET # 1 OF 1</b>  |  |
| CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.    |                          |  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## BIVAR:

[460-060](#) [460-100](#) [460-110](#) [460-120](#) [460-150](#) [460-200](#) [461-380](#) [465-250](#) [465-350](#) [460-070](#) [460-080](#) [460-090](#)  
[460-130](#) [460-140](#) [460-160](#) [460-170](#) [460-180](#) [460-190](#) [460-210](#) [461-360](#) [461-400](#) [461-420](#) [461-440](#) [461-460](#)  
[461-480](#) [461-500](#) [461-520](#) [461-540](#) [462-560](#) [462-580](#) [462-600](#) [462-620](#) [462-640](#) [462-660](#) [462-680](#) [462-700](#)  
[462-720](#) [462-730](#) [462-740](#) [465-200](#) [465-210](#) [465-220](#) [465-230](#) [465-240](#) [465-260](#) [465-270](#) [465-280](#) [465-290](#)  
[465-300](#) [465-310](#) [465-320](#) [465-330](#) [465-340](#) [460-060 BK](#)