

1W, 11V - 220V Zener Diode

FEATURES

- AEC-Q101 qualified
- Silicon zener diodes
- Low profile surface-mount package
- Zener and surge current specification
- Low leakage current
- Excellent stability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
V_Z	11 - 220	V
Test current I_{ZT}	5 - 50	mA
P_{tot}	1.0	W
T_{JMAX}	175	°C
Package	SOD-123W	
Configuration	Single die	

APPLICATIONS

- Voltage regulating
- Reference voltage
- Protection circuit



MECHANICAL DATA

- Case: SOD-123W
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.016g (approximately)



SOD-123W



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Forward voltage @ $I_F = 0.2\text{A}$	V_F	1.0	V
Power dissipation	P_{tot}	$T_L = 80^\circ\text{C}$	2.3
		$T_A = 25^\circ\text{C}^{(1)}$	1.0
Non-repetitive peak pulse power dissipation 100 μs square pulse ⁽²⁾	P_{ZSM}	300	W
Non-repetitive peak pulse power dissipation 10/1000 μs waveform (BZD27C11PWH to BZD27C100PWH)	P_{RSM}	150	W
Non-repetitive peak pulse power dissipation 10/1000 μs waveform (BZD27C110PWH to BZD27C220PWH)	P_{RSM}	100	W
Junction temperature	T_J	- 55 to +175	°C
Storage temperature	T_{STG}	- 55 to +175	°C

Notes:

1. Mounted on Cu-Pad size 5mm x 5mm
2. $T_J = 25^\circ\text{C}$ prior to surge

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	22	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	85	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	24	°C/W

ORDERING INFORMATION		
ORDERING CODE⁽¹⁾	PACKAGE	PACKING
BZD27CxPWH	SOD-123W	10,000 / Tape & Reel

Notes:

1. “x” defines voltage from 11V (BZD27C11PWH) to 220V (BZD27C220PWH)

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)								
Part number	Marking code	Zener voltage			Test current	Regulator impedance		Test current
		$V_Z @ I_{ZT}^{(1)}$			I_{ZT}	$Z_{ZT} @ I_{ZT}$	$Z_{ZK} @ I_{ZK}$	I_{ZK}
		V			mA	Ω	Ω	mA
		Min	Nom	Max		Max	Max	
BZD27C11PWH	N2	10.5	11	11.6	50	7	700	0.25
BZD27C12PWH	N3	11.4	12	12.6	50	7	700	0.25
BZD27C13PWH	N4	12.4	13	13.7	50	10	700	0.25
BZD27C15PWH	N5	14.3	15	15.8	50	10	700	0.25
BZD27C16PWH	N6	15.2	16	16.8	25	15	700	0.25
BZD27C18PWH	N7	17.1	18	18.9	25	15	750	0.25
BZD27C20PWH	P0	19	20	21	25	15	750	0.25
BZD27C22PWH	P1	20.9	22	23.1	25	15	750	0.25
BZD27C24PWH	P3	22.8	24	25.2	25	15	750	0.25
BZD27C27PWH	P4	25.7	27	28.4	25	15	1000	0.25
BZD27C30PWH	P5	28.5	30	31.5	25	15	1000	0.25
BZD27C33PWH	P6	31.4	33	34.7	25	15	1000	0.25
BZD27C36PWH	P7	34.2	36	37.8	10	40	1000	0.25
BZD27C39PWH	P8	37.1	39	41	10	40	1000	0.25
BZD27C43PWH	Q0	40.9	43	45.2	10	45	1500	0.25
BZD27C47PWH	Q1	44.7	47	49.4	10	45	1500	0.25
BZD27C51PWH	Q2	48.5	51	53.6	10	60	1500	0.25
BZD27C56PWH	Q5	53.2	56	58.8	10	60	2000	0.25
BZD27C62PWH	Q7	58.9	62	65.1	10	80	2000	0.25
BZD27C68PWH	R1	64.6	68	71.4	10	80	2000	0.25
BZD27C75PWH	R2	71.3	75	78.8	10	100	2000	0.25
BZD27C82PWH	R3	77.9	82	86.1	10	200	3000	0.25
BZD27C91PWH	R4	86.5	91	95.6	5	200	3000	0.25
BZD27C100PWH	R5	95	100	105	5	200	3000	0.25
BZD27C110PWH	R6	104.5	110	115.5	5	250	4000	0.25
BZD27C120PWH	R7	114	120	126	5	300	4500	0.25
BZD27C130PWH	R8	123.5	130	136.5	5	300	5000	0.25
BZD27C150PWH	R9	142.5	150	157.5	5	300	6000	0.25
BZD27C160PWH	R10	152	160	168	5	350	6500	0.25
BZD27C180PWH	R11	171	180	189	5	450	7000	0.25
BZD27C200PWH	R12	190	200	210	5	750	8000	0.25
BZD27C220PWH	R13	209	220	231	5	900	8500	0.25

Notes:

1. Pulse test with PW = 30ms

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Part number	Marking code	Zener voltage			Test current	Clamping Voltage		Leakage current		Temperature coefficient of Zener voltage	
		$V_Z @ I_{ZT}^{(1)}$			I_{ZT}	V_C	$@ I_{RSM}^{(2)}$	$I_R @ V_R^{(1)}$		$\alpha V_Z @ I_{ZT}$	
		V			mA	V	A	μA	V	% / $^\circ\text{C}$	
		Min	Nom	Max		Max		Max		Min	Max
BZD27C11PWH	N2	10.5	11	11.6	50	15.7	9.6	4.0	8.2	0.05	0.10
BZD27C12PWH	N3	11.4	12	12.6	50	17.0	8.8	3.0	9.1	0.05	0.10
BZD27C13PWH	N4	12.4	13	13.7	50	18.9	7.9	2.0	10	0.05	0.10
BZD27C15PWH	N5	14.3	15	15.8	50	20.9	7.2	1.0	11	0.05	0.10
BZD27C16PWH	N6	15.2	16	16.8	25	22.9	6.6	1.0	12	0.06	0.11
BZD27C18PWH	N7	17.1	18	18.9	25	25.6	5.9	1.0	13	0.06	0.11
BZD27C20PWH	P0	19	20	21	25	28.4	5.3	1.0	15	0.06	0.11
BZD27C22PWH	P1	20.9	22	23.1	25	31.0	4.8	1.0	16	0.06	0.11
BZD27C24PWH	P3	22.8	24	25.2	25	33.8	4.4	1.0	18	0.06	0.11
BZD27C27PWH	P4	25.7	27	28.4	25	38.1	3.9	1.0	20	0.06	0.11
BZD27C30PWH	P5	28.5	30	31.5	25	42.2	3.6	1.0	22	0.06	0.11
BZD27C33PWH	P6	31.4	33	34.7	25	46.2	3.2	1.0	24	0.07	0.12
BZD27C36PWH	P7	34.2	36	37.8	10	50.1	3.0	1.0	27	0.07	0.12
BZD27C39PWH	P8	37.1	39	41	10	54.1	2.8	1.0	30	0.07	0.12
BZD27C43PWH	Q0	40.9	43	45.2	10	60.7	2.5	1.0	33	0.08	0.13
BZD27C47PWH	Q1	44.7	47	49.4	10	65.5	2.3	1.0	36	0.08	0.13
BZD27C51PWH	Q2	48.5	51	53.6	10	70.8	2.1	1.0	39	0.08	0.13
BZD27C56PWH	Q5	53.2	56	58.8	10	78.6	1.9	1.0	43	0.09	0.13
BZD27C62PWH	Q7	58.9	62	65.1	10	86.5	1.7	1.0	47	0.09	0.13
BZD27C68PWH	R1	64.6	68	71.4	10	94.4	1.6	1.0	51	0.09	0.13
BZD27C75PWH	R2	71.3	75	78.8	10	103.5	1.5	1.0	56	0.09	0.13
BZD27C82PWH	R3	77.9	82	86.1	10	114	1.3	1.0	62	0.09	0.13
BZD27C91PWH	R4	86.5	91	95.6	5	126	1.2	1.0	68	0.09	0.13
BZD27C100PWH	R5	95	100	105	5	139	1.1	1.0	75	0.09	0.13
BZD27C110PWH	R6	104.5	110	115.5	5	150	1.0	1.0	82	0.09	0.13
BZD27C120PWH	R7	114	120	126	5	152	0.65	1.0	91	0.09	0.13
BZD27C130PWH	R8	123.5	130	136.5	5	185	0.81	1.0	100	0.09	0.13
BZD27C150PWH	R9	142.5	150	157.5	5	205	0.73	1.0	110	0.09	0.13
BZD27C160PWH	R10	152	160	168	5	224	0.67	1.0	120	0.09	0.13
BZD27C180PWH	R11	171	180	189	5	229	0.43	1.0	130	0.09	0.13
BZD27C200PWH	R12	190	200	210	5	254	0.39	1.0	150	0.09	0.13
BZD27C220PWH	R13	209	220	231	5	279	0.35	1.0	160	0.09	0.13

Notes :

1. Pulse test with $PW = 30\text{ms}$
2. 10/1000 μs waveform

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Steady State Power Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Forward Characteristics






Fig.4 Typical Zener Impedance




PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	0.90	1.02	0.035	0.040
A1	0.00	0.10	0.000	0.004
b	0.90	1.05	0.035	0.041
c	0.10	0.22	0.004	0.009
D	1.70	1.90	0.067	0.075
E	3.60	3.80	0.142	0.150
E1	2.60	2.90	0.102	0.114
L	0.50	0.85	0.020	0.033

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	1.40	0.055
B	1.20	0.047
C	3.10	0.122
D	1.90	0.075
E	4.30	0.169

MARKING DIAGRAM



P/N = Marking Code
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.