

- 3"x2" compact size
- · Medical safety approved (2 x MOPP) according to ANSI/AAMI ES60601-1 and IEC/BS EN/EN60601-1
- Suitable for BF application with appropriate system consideration
- · Cooling by free air convection
- EMI class B for class

 configuration
- No load power consumption<0.1W
- Extremely low leakage current
- · Protections: Short circuit / Overload / Over voltage
- · Lifetime > 50K hours
- Operating altitude up to 4000 meters
- 3 years warranty









Applications

- · Oral irrigator
- Hemodialysis machine
- Medical computer monitors
- · Sleep apnea devices


GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

Description

RPS-45 is a 45W highly reliable green PCB type medical power supply with a high power density on the 3" by 2" footprint. It accepts 80~264VAC input and offers various output voltages between 3.3V and 48V. The working efficiency is up to 91% and the extremely low no load power consumption is down below 0.1W. RPS-45 is able to be used for Class II (no FG) system design. The extremely low leakage current is less than 100μA. In addition, it conforms to international medical regulations (2*MOPP) and EMC BS EN/EN55011, perfectly fitting all kinds of BF rated "patient contact" medical system equipment.

■ Model Encoding






45W Reliable Green Medical Power Supply

ORDER NO.		RPS-45-3.3	RPS-45-5	RPS-45-7.5	RPS-45-12	RPS-45-15	RPS-45-24	RPS-45-48
	DC VOLTAGE	3.3V	5V	7.5V	12V	15V	24V	48V
	RATED CURRENT	8A	8A	5.4A	3.8A	3A	1.9A	0.94A
	CURRENT RANGE	0~8.8A	0~8.8A	0 ~ 5.95A	0.07 0 ~ 4.18A	0 ~ 3.3A	0 ~ 2.1A	0.5470 0 ~ 1.03A
	RATED POWER	26.4W	40W	40.5W	45.6W	45W	45.6W	45.1W
UTPUT			44W	44.6W	50.2W	49.5W		
JUIPUI	PEAK LOAD(10sec.) Note.2			1			50.2W	49.4W
	RIPPLE & NOISE (max.) Note.3		60mVp-p	80mVp-p	100mVp-p	100mVp-p	120mVp-p	120mVp-p
	VOLTAGE ADJ.RANGE	3.1~3.6V	4.7~5.5V	7.12~8.3V	11.4~13.2V	13.5~16.5V		45.6~52.8
	VOLTAGE TOLERANCE Note.4		±2.0%	±2.0%	±2.0%	±1.0%	±1.0%	±1.0%
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION	±2.0%	±2.0%	±2.0%	±2.0%	±1.0%	±1.0%	±1.0%
	SETUP, RISE TIME	500ms, 30ms / 20	30VAC 500ms	, 30ms / 115VAC a	t full load			
HOLD UP TIME (Typ.) 30ms / 230VAC 16ms / 115VAC at full load								
	VOLTAGE RANGE Note.5	80 ~ 264VAC						
	FREQUENCY RANGE	47 ~ 63Hz						
NPUT	EFFICIENCY (Typ.)	80.5%	83%	85%	88%	89%	90%	91%
	AC CURRENT (Typ.)	1.2A / 115VAC	1A / 230VAC				·	
	INRUSH CURRENT (Typ.)	COLD STAR 30A/115VAC 60A/230VAC						
	LEAKAGE CURRENT(max.) Note.6							
PROTECTION		115 ~ 150% rated output power						
	OVERLOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed						
	OVER VOLTAGE	3.8~5V	5.7~6.8V	8.6~11.3V	13.8~16.2V	17.2~20.3V	28.4~32.4V	55.2~64.8V
						17.2 20.00	20.4 02.40	00.2 04.00
	WORKING TEMP.	Protection type: Shut down o/p voltage, re-power on to recover -30 ~ +70°C (Refer to "Derating Curve")						
	WORKING HUMIDITY	20% ~ 90% RH non-condensing						
W//DOWNENT		20% ~ 90% RH non-condensing						
NVIRONMENT	STORAGE TEMP., HUMIDITY	· · · · · · · · · · · · · · · · · · ·						
	TEMP. COEFFICIENT	±0.03% / °C (0~50°C)						
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes						
	OPERATING ALTITUDE Note.7	IEC60601-1, TUV BS EN/EN60601-1, EAC TP TC 004,UL ANSI / AAMI ES60601-1 (3.1 version),						
	SAFETY STANDARDS							
	IOOL ATION LEVEL	CAN/CSA-C22.2 No. 60601-1:14 - Edition 3 approved; Design refer to BS EN/EN60335-1						
	ISOLATION LEVEL	Primary-Secondary: 2xMOPP						
	WITHSTAND VOLTAGE	I/P-O/P: 4KVAC						
	ISOLATION RESISTANCE		nms / 500VDC / 25°					
	EMC EMISSION EMC IMMUNITY	Parameter		Standard			est Level / Note	
CAFFTV 0		Conducted emission BS EN/EN55011 (CISPR11)			Class B Class B			
SAFETY &			Radiated emission BS EN/EN55011 (CISPR11) Class B Harmonic current BS EN/EN61000-3-2 Class A					
EMC (Note. 8)		Voltage flicker BS EN/EN61000-3-2 Class A						
14016.0)		Voltage flicker						
				est Level / Note				
		ESD		BS EN/EN	BS EN/EN61000-4-2		Level 4, 15KV air ; Level 4, 8KV contact	
		DE field quagentibility		DO ENI/ENI	BS EN/EN61000-4-3		Level 3, 10V/m(80MHz~2.7GHz)	
		RF field susceptibility					Table 9, 9~28V/m(385MHz~5.78GHz)	
		EFT bursts			BS EN/EN61000-4-4		Level 3, 2KV	
		Surge susceptibility			BS EN/EN61000-4-5		Level 4, 2KV/Line-Line	
		Conducted susc			BS EN/EN61000-4-6		Level 3, 10V	
		Magnetic field immunity BS EN/EN61000-4-8			Level 4, 30A/m			
		Voltage dip, interruption BS EN/EN61000-4-11 100% dip 1 periods, 30% dip 25 per 100% interruptions 250 periods						
OTHERS	MTBF	3334.3K hrs min. Telcordia SR-332 (Bellcore) ; 726.2K hrs min. MIL-HDBK-217F (25°C)						
	DIMENSION (L*W*H)		or 3" * 2" *0.945" i	,	, . =		(/	
, , , , , LINU	PACKING	0.11Kg; 120pcs/14.2Kg/0.94CUFT						
OTE	All parameters NOT specially 33% Duty cycle maximum wit Ripple & noise are measured Tolerance: includes set up to Derating may be needed und Touch current was measured	mentioned are me hin every 30 secon at 20MHz of band erance, line regula er low input voltago from primary input	asured at 230VAC inds. Average output width by using a 12 tion and load regulates. Please check the to DC output.	power should not e " twisted pair-wire to ation. e derating curve for	exceed the rated poerminated with a 0.7 more details.	wer. Iµf & 47µf parall	·	
VIL	7. The ambient temperature der 8. The power supply is consider the unit on a 360mm*360mm For guidance on how to perfo (as available on http://www.m 2. Product Liability Disclaimer 3. The product Liability Disclaimer 3. The product Liability Disclaimer 3. The product Liability Disclaimer 4. The product Liability Disclaimer 4. The product Liability Disclaimer 5. The product Liability Disclaimer 6. The product Liability Disclaimer 6. The product Liability Disclaimer 7. The product Liability Disclaimer 8. The power supply is consider 8. The power supply is consider 8. The power supply is consider 9. The product Liability Disclaimer 9. The power supply is consider 9. The power supply is consider 10. The power supply is consider 10	ating of 3.5°C/1000 ed a component w metal plate with 1 rm these EMC tes eanwell.com)	Om with fanless mod hich will be installed mm of thickness." T ts, please refer to "E	I into a final equipment in the final equipment in EMI testing of complete.	ent. "All the EMC to must be re-confirme onent power suppli	ests are been exe ed that it still mee es."	ecuted by mounting	m(6500ft).

% Product Liability Disclaimer : For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx









■ Mechanical Specification

Case No. Unit:mm





AC Input Connector (CN1): JST B3P-VH or equivalent

	•	,	•	
Pin No.	Assignment	Mating Housing	Terminal	
1	AC/N	ICTVIID	IOT OVILLOAT DA A	
2	No Pin	JST VHR or equivalent	JST SVH-21T-P1.1 or equivalent	
3	AC/L	or oquivalone	or oquivalent	

DC Output Connector (CN2): JST B4P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal	
1	+V			
2	+V	JST VHR	JST SVH-21T-P1.1	
3	-V	or equivalent	or equivalent	
4	-V			

■ Installation Manual

Please refer to : http://www.meanwell.com/manual.html