



### **GTIN CODE**

**SPECIFICATION** 

MW Search: https://www.meanwell.com/serviceGTIN.aspx


### Features :

- 2:1 wide input range
- 4:1 wide input range(option)
- 1000VDC I/O isolation
- 3000VDC I/O isolation(option)
- · Built-in EMI filter
- Protections: Short circuit / Overload
- Cooling by free air convection
- Six-sided shield metal case
- 100% burn-in test
- · Low cost / High reliability
- Approvals: FCC / EAC / CE / UKCA
- 2 years warranty

# FC [H[ C E EK

ORDER NO.				DKE10C-				1					
		05	05	05	12	12	12	15	15	15	24	24	24
ОИТРИТ	DC VOLTAGE	±5V			±12V			±15V			±24V		
	CURRENT RANGE	±100 ~ ±1000mA			±42 ~ ±420mA			±33.3 ~ ±333mA			±21 ~ ±210mA		
	RATED POWER	10W											
	RIPPLE & NOISE (max.) Note.2				60mVp-p			60mVp-p			80mVp-p		
	LINE REGULATION Note.3	±0.3%											
	LOAD REGULATION Note.4	±0.5%											
	VOLTAGE ACCURACY	±2.0%											
	SWITCHING FREQUENCY	250KHz min.											
INPUT	VOLTAGE RANGE	A: 9 ~ 18VDC B: 18 ~ 36VDC C: 36 ~ 72VDC											
	EFFICIENCY (Typ.)	78%	81%	82%	80%	80%	83%	80%	80%	82%	82%	81%	85%
	DO CURRENT	Full load A: 1100mA B: 530mA C: 270mA											
	DC CURRENT	No load A: 30mA B: 16mA C: 8mA											
	FILTER	Pi network											
	PROTECTION	Fuse recommended											
PROTECTION (Note. 5)	OVER CURRENT	160% ~ 250% rated output power											
	OVER CURRENT	Protection type: Hiccup mode, recovers automatically after fault condition is removed											
	OLIOPE OIDOUE	All output equipped with short circuit											
	SHORT CIRCUIT	Protection type: Hiccup mode, recovers automatically after fault condition is removed											
ENVIRONMENT	WORKING TEMP.	-25 ~ +71°C (Refer to "Derating Curve")											
	WORKING HUMIDITY	20% ~ 90% RH non-condensing											
	STORAGE TEMP., HUMIDITY	-25 ~ +105°C, 10 ~ 95% RH											
	TEMP. COEFFICIENT	±0.03% / °C (0 ~ 50°C)											
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes											
SAFETY & EMC	SAFETY STANDARDS	EAC TP TC 020/2011 approved											
	WITHSTAND VOLTAGE	I/P-O/P:1.5KVDC											
	ISOLATION RESISTANCE	I/P-O/P: 100M Ohms / 500VDC / 25°C / 70% RH											
	EMC EMISSION	Compliance to BS EN/EN55032 Class A, FCC part 15 Class A, EAC TP TC 020											
	EMC IMMUNITY	Compliance to BS EN/EN61000-4-2,3,4,5,6,8, light industry level, criteria A, EAC TP TC 020											
OTHERS	MTBF	500Khrs n	500Khrs min. MIL-HDBK-217F(25℃)										
	DIMENSION	50.8*25.4*11.2mm or 2"*1"*0.44" inch (L*W*H)											
	WEIGHT	32g	32g										


# ■ Mechanical Specification



## **■** Pin Configuration

Pin No.	Output					
1	+Vin					
2	-Vin					
3	+Vout					
4	COM					
5	-Vout					

## ■ Derating Curve



#### NOTE

- 1.All parameters are specified at normal input, rated load, 25°C 70% RH ambient.
  2.Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uf & 47uf capacitor.
  3.Line regulation is measured from low line to high line at rated load.
- 4.Load regulation is measured from 10% to 100% rated load.
- 5.Please prevent the converter from operating in overload or short circuit condition for more than 30 seconds.
- Product Liability Disclaimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx