

## LT3505EDD: PMIC High Voltage Adaptor Board with 5 Volt Adaptor Inputs

### DESCRIPTION

Demonstration Circuit 1395A is a 1.2A, Step-Down Switching Regulator in a 3mm × 3mm DFN. The LT3505EDD is available in an 8-pin (3mm × 3mm) DFN surface mount package.

LT, LTC, LTM, LT, Burst Mode, OPTI-LOOP, Over-The-Top and PolyPhase are registered trademarks of Linear Technology Corporation. Adaptive Power, C-Load, DirectSense, Easy Drive, FilterCAD, Hot Swap, LinearView, µModule, Micropower SwitcherCAD, Multimode Dimming, No Latency ΔΣ, No Latency Delta-Sigma, No R<sub>SENSE</sub>, Operational Filter, PanelProtect, PowerPath, PowerSOT, SmartStart, SoftSpan, Stage Shedding, SwitcherCAD, ThinSOT, UltraFast and VLDO are trademarks of Linear Technology Corporation. Other product names may be trademarks of the companies that manufacture the products.

### PERFORMANCE SUMMARY Specifications are at T<sub>A</sub> = 25°C

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
HVIN	High Voltage Input Voltage Range	Input disabled from 36-40V	8		40	V
5V ADAPTOR	5V Adaptor Input Voltage Range		4.5		5.5	V
HVBUCK	Output Voltage Range	Range is mode and load dependant	3.5		5.5	V
I <sub>HVBUCK</sub>	Output Current				2	A

### QUICK START PROCEDURE

Using short twisted pair leads for any power connections, with all loads and power supplies off, refer to Figures 1 & 2 for the proper measurement and equipment setup.

A companion PMIC demo board is required for this check out procedure. The DC1303A (LTC4098EPDC) board is recommended, and will be used for the following procedure. Please refer to the DC1303A Quick Start Guide for further information.

Follow the procedure below:

1. Set PS1 to 8V, PS2 to 0V, and PS3 to 3.6V. Set Load1 to 0A. Ensure that jumpers are configured as per Figure 1, except the “D2” jumper (JP3) on the DC1303A should be set to “1”.
2. Observe that 4.50V < V<sub>OUT</sub> (VM3) < 4.70V. The LT3480 HV Buck regulator is running with its control loop closed locally. The nominal HVBUCK voltage is 4.75V, and the


LTC4098EPDC on the DC1303A board has connected HVBUCK to V<sub>OUT</sub>.

3. Set Load1 to 1A. Observe that 4.35V < V<sub>OUT</sub> (VM3) < 4.55V. Set Load1 to 0A. The 1A load on V<sub>OUT</sub> loads HVBUCK, so the LT3505EDD is supplying 1A.
4. Set PS1 to 36V. Observe that 4.50V < V<sub>OUT</sub> (VM3) < 4.70V. The LT3505 is designed to operate from HVIN = 8V to 36V.
5. Set Load1 to 1A. Observe that 4.20V < V<sub>OUT</sub> (VM3) < 4.55V. Set Load1 to 0A. The LT3505 is now supplying 1A, while operating from 38V.
6. Set “COMP” jumper (JP2) to “REMOTE”. Observe that 3.80V < V<sub>OUT</sub> (VM3) < 4.10V. The LTC4098EPDC is now controlling the LT3505 output voltage to approximately V(BAT) + 0.3V.
7. Set Load1 to 1A. Observe that 3.70V < V<sub>OUT</sub> (VM3) < 3.90V. Set Load1 to 0A. LT3505 is supplying 1A, while under LTC4098 control.
8. Set PS1 to 8V. Observe that 3.80V < V<sub>OUT</sub> (VM3) < 4.10V.

## LT3505EDD

---

9. Set Load1 to 1A. Observe that  $3.70V < (VM3) < 3.90V$ . Set Load1 to 0A.
10. Set PS2 to 4.5V, and “WALL” jumper (JP3) to “5V ADAPTOR”. Observe that  $4.40 < VOUT (VM3) < 4.50V$ . The LT3505 is not supplying power to VOUT. This verifies that the LTC4098 recognizes the 5V Adaptor input, and connects it to VOUT.
11. Set Load1 to 1A. Observe that  $4.10V < VOUT (VM3) < 4.40V$ . Set Load1 to 0A.
12. Set PS2 to 5.5V. Observe that  $5.40V < VOUT (VM3) < 5.50V$ .
13. Set Load1 to 1A. Observe that  $5.10V < VOUT (VM3) < 5.50V$ .



Note: All connections from equipment should be Kelvin connected directly to the Board PINS which they are connected to on this diagram and any input, or output, leads should be twisted pair

Figure 1. Proper Measurement Equipment Setup for DC1395A





Figure 2. Measuring Input or Output Ripple



Note: \* Move JP2 to REMOTE when connected to PMIC board.

<b>CUSTOMER NOTICE</b>		<b>CONTRACT NO.</b>	
LINEAR TECHNOLOGY HAS MADE A BEST EFFORT TO DESIGN A CIRCUIT THAT MEETS CUSTOMER-SUPPLIED SPECIFICATIONS; HOWEVER, IT REMAINS THE CUSTOMER'S RESPONSIBILITY TO VERIFY PROPER AND RELIABLE OPERATION IN THE ACTUAL APPLICATION. COMPONENT SUBSTITUTION AND PRINTED CIRCUIT BOARD LAYOUT MAY SIGNIFICANTLY AFFECT CIRCUIT PERFORMANCE OR RELIABILITY. CONTACT LINEAR TECHNOLOGY APPLICATIONS ENGINEERING FOR ASSISTANCE SUPPLIED FOR USE WITH LINEAR TECHNOLOGY PARTS.		APPROVALS	
Unless noted: Resistors: Ohms 0402 1% 1/16W Capacitors: uF 0402 10% 25V		DRAWN: G. Hubbard CHECKED: G. Hubbard APPROVED: ENGINEER: G. Hubbard DESIGNER:	
THIS CIRCUIT IS PROPRIETARY TO LINEAR TECHNOLOGY AND SUPPLIED FOR USE WITH LINEAR TECHNOLOGY PARTS.		TITLE: <b>LT3505EDD, PMIC High Voltage Adaptor Board with 5V Adaptor Inputs</b>	
SIZE	DWG NO.	REV	DATE:
C	DC1395A	A	Thursday, August 26, 2008
			SHEET 0 OF 1

1630 McCarthy Blvd.  
Milpitas, CA 95035  
Phone: (408)432-1900  
Fax: (408)434-0907  
LTC Confidential For Customer Use Only

**LINEAR TECHNOLOGY**

1630 McCarthy Blvd.  
Milpitas, CA 95035  
Phone: (408)432-1900  
Fax: (408)434-0907  
LTC Confidential For Customer Use Only

Figure 3. DC1395A Schematic

Qty	Reference	Part Description	Manufacture / Part #
<b>REQUIRED CIRCUIT COMPONENTS:</b>			
1	C1	CAP, CHIP, X7R, 4.7µF, ±10%, 50V, 1206	MURATA, GRM31CR71H475KA12L
2	C2	CAP, CHIP, X7R, 0.068µF, ±10%, 50V, 0603	MURATA, GRM188R71H683K
3	C4	CAP, CHIP, BX, 330pF, 50V, 5%, 0402	VISHAY, VJ0402X331JXAA
4	C7	CAP, CHIP, X5R, 22µF, ±20%, 6.3V, 0805	TAIYO-YUDEN, JMK212BJ226MG
5	C8	CAP, CHIP, X7R, 0.47µF, ±10%, 25V, 0603	MURATA, GRM188R71E474K
6	D1	DIODE, ZENER, 16V, ±7%, 150mW, SOD-523	DIODES INC., BZT52C16T
7	D2	DIODE, SCHOTTKY, 2A, 40V, SMB	DIODES INC., DFLS240L
8	D3	DIODE, SILICON, 200mA, 100V, SOD-323	ON SEMICONDUCTOR, MMDL914T1G
9	D4	DIODE, SCHOTTKY, 200mA, 30V, SOD-523	DIODES INC., SDM20U30
10	L1	IND, SMT, 6.8µH, 0.122Ω, ±30%, 1.11A, 5mmX5mm	TDK, VLCF5020T-6R8N1R3
11	Q1	MOSFET, -12V, 35mΩ, -5.3A, SOT-23	VISHAY, Si2333DS
12	R1	RES, CHIP, 150kΩ, 1/16W, ±1%, 0402	VISHAY, CRCW0402150KFKED
13	R2	RES, CHIP, 1.13MΩ, 1/16W, ±1%, 0402	VISHAY, CRCW04021M13FKED
14	R3	RES, CHIP, 25.5kΩ, 1/16W, ±1%, 0402	VISHAY, CRCW040225K5FKED
15	R5	RES, CHIP, 20kΩ, 1/16W, ±1%, 0402	VISHAY, CRCW040220K0FKED
16	R6	RES, CHIP, 100kΩ, 1/16W, ±1%, 0402	VISHAY, CRCW0402100KFKED
17	R7	RES, CHIP, 499kΩ, 1/16W, ±1%, 0402	VISHAY, CRCW0402499KFKED
18	U1	LT3505EDD, PMIC High Voltage Adaptor Board with 5V Adaptor Inputs	LINEAR TECH., LT3505EDD
<b>ADDITIONAL DEMO BOARD CIRCUIT COMPONENTS:</b>			
1	C3	CAP, CHIP, X5R, 10µF, ±10%, 6.3V, 0603	TDK, C1608X5R0J106K
2	C5-OPT, C6-OPT	None	User determined
3	R4	RES, CHIP, 1.0Ω, 1/16W, 5%, 0402	VISHAY, CRCW04021R00JNED
4	R8	RES,CHIP, 20Ω, 1/16W, ±5%, 0402	VISHAY, CRCW040220R0JNED
<b>HARDWARE FOR DEMO BOARD ONLY:</b>			
1	E1,E2,E3,E4,E5,E6	Turret, 0.09"	MILL-MAX, 2501-2
2	J1	CONN, HV interface	SAMTEC, TSH-108-01-T-RA
3	JP1,JP2,JP3	3 Pin Jumper, 2mm	SAMTEC, TMM-103-02-L-S
4	JP1,JP2,JP3	2mm SHUNT	SAMTEC, 2SN-BK-G
5		STAND-OFF, NYLON 0.375" tall (SNAP ON)	KEYSTONE, 8832 (SNAP ON)

Figure 4. DC1395A BOM

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[DC1395A](#)