


AccelePort® Xem

Multiport Serial Cards & Expansion Ports

The AccelePort Xem system enables your business to reap all the benefits of high-performance serial computing at the lowest price per port.



Features/Benefits

- > Expandable up to 64 ports from a single host slot
- > Universal PCI bus slot supports 3.3v & 5v
- > Low profile PCI option
- > ISA bus product available
- > Eight- and 16-port concentrator boxes provide incremental expansion
- > Delivers data speeds up to 115.2 Kbps
- > RS-232 and RS-422 solutions
- Ideal for connecting modems, terminals, printers, instruments and other serial devices
- > 1U 19-inch rack mount 16-port option

Overview

The AccelePort Xem asynchronous system is an expandable, modular and intelligent serial communication solution designed specifically for small to mid-size multiuser installations. This product is especially well-suited for applications that are expected to start small and grow over time to as many as 64 ports.

This flexible system enables you to connect up to 64 RS-232 or RS-422 serial ports to a Universal PCI (3.3v & 5v) or ISA-based computer. The result is a fast, reliable way to connect terminals, printers, modems, instruments and other serial peripheral devices, making it ideal for applications such as data acquisition, office/factory automation and industrial process control.

The AccelePort Xem system features a host adapter card with an on-board RISC-based processor that delivers up to 115.2 Kbps performance per port. The system also includes a compact Digi PORTS module that provides access to eight or 16 serial ports. PORTS modules can also be Ethernet-enabled using the PortServer® II.

The AccelePort Xem has driver support for a wide array of popular operating systems. It features the same quality, reliability and after-sales technical support that has made Digi the leader in serial connectivity.

Digi International, the leader in Connectware, makes device networking easy by developing products and technologies that are cost-effective and easy to use. With over 20 million ports shipped worldwide, Digi has been offering the highest levels of performance, flexibility, and quality since 1985.

DICI®

Connectware™

www.digi.com





FEATURES

AccelePort Xem Host Card

- Supports both Universal PCI (3.3v & 5v) and ISA platforms
- PCI 2.3/PCI-X compatible
- Low profile PCI option
- Data transfer rates up to 115.2 Kbps per port
- One host card supports up to four Digi PORTS modules for a maximum of 64 ports
- Auxiliary power supply package (PN 76000109 in North America or 76000321 for International) required when using more than two PORTS modules on modules 3 & 4
- On-board IDT 3081 RISC processor with patented Front End Processor/Operating System (FEP/OS)

Digi PORTS Modules

- Interchangeable between ISA and PCI platforms & PortServer II
- Eight or 16 RS-232 asynchronous serial ports (RJ-45 or DB-25)
- 1U 19-inch rack mount PORTS/16em for RS-232
- 16 RS-422 asynchronous serial ports (DB-25)
- Modules can connect to Digi EPC/CON concentrators or PortServer II
- External Bus Interface (EBI) technology uses HD44 female connectors on PORTS modules to daisy-chain additional ports via 16-inch (40.6 cm) cable
- Surge protection on all signals
- Supports full modem control and full hardware handshaking (CTS, RTS, DSR, DTR and DCD) on all channels



POWER REQUIREMENTS

PCI Host Card

 +5v +/-5% 0.43 Amps typical, plus module power drain

ISA Host Card

• +5v +/-5% 1.75 Amps typical, plus module power drain

OPERATING SYSTEMS

- AIX
- Compaq Tru64 UNIX, OpenVMS[†]
- HP-UX
- Windows® 95/98/ME
- Windows NT[®]
- Windows 2000/XP
- Windows Server[™] 2003
- Linux
- Novell NetWare[†]
- OS/2[†]
- QNX[†]
- SCO OpenServer, UnixWare
- Solaris[™] SPARC, Intel
- * Driver updates available at www.digi.com/drivers.

†Legacy driver only

SYSTEM

REQUIREMENTS

ISA Host Card

- One full-length 16-bit slot
- 32K unused memory address space for static RAM
- One unused I/O port address

PCI Host Card

- One full-length 32-bit or 64-bit slot
 - One 3.3v or 5v slot

- Ambient temperature: 50° F to 131° F (10° C to 55° C)
- Storage temperature:
 -13° F to +125° F
 (-25° C to +85° C)
- Relative humidity:5% to 90% (non-condensing)
- Altitude: 0 to 12,000 feet (0 to 3,600 meters)
- Air movement: 30 CFM forced



- FCC Part 15, Class B
- ICES-003 Class B
- EN55022, Class B
- EN50082-2
- UL 1950
- CSA 22.2 No 950
- EN60950



| · | | |
|---|------------------|-----------------|
| RS-232 Solutions (Kit includes card, 5'(1.5m) EBI cable and PORTS module) | High Profile PCI | Low Profile PCI |
| AccelePort 8em-PCI RJ-45 | 70001206 | 70002009 |
| AccelePort 8em-PCI DB-25 | 70001208 | 70002008 |
| AccelePort 16em-PCI RJ-45 | 70001201 | 70002011 |
| AccelePort 16em-PCI DB-25 | 70001203 | 70002010 |
| AccelePort 16em-PCI RJ-45 rack (1U 19-inch rack) | 70001757 | 70002012 |
| RS-422 Solutions (Kit includes card, 5'(1.5m) EBI cable and PORTS module) | | |
| AccelePort 16em-PCI RS-422 DB-25 | 70001559 | 70002017 |
| Expansion Modules | | |
| PORTS/8em module DB-25 † | 76000120 | 76000120 |
| PORTS/8em module RJ-45 † | 76000122 | 76000122 |
| PORTS/16em module DB-25 † | 76000073 | 76000073 |
| PORTS/16em module RJ-45 † | 76000074 | 76000074 |
| PORTS/16em rack RJ-45 † (1U 19-inch rack) | 76000617 | 76000617 |
| PORTS/16em module RS-422 DB-25 † (NA version ships w/ power supply & power cord) | 76000535 | 76000535 |
| PORTS/16em module RS-422 DB-25 (International version ships with external 43 W, 100-250v 50/60 Hz power supply)† | 76000548 | 76000548 |
| Optional Accessories | | |
| Xem 120v Power Supply Package | 76000109 | 76000109 |
| Xem International Power Supply Package (100-250v) | 76000321 | 76000321 |
| 19" Rack Mount Chassis (2U) | 76000611 | 76000611 |
| 48" Cable RJ-45 to DB-25M straight-through (One adapter cable needed per port) | 76000195 | 76000195 |
| 48" Cable RJ-45 to DB-9M straight-through (One adapter cable needed per port) | 76000240 | 76000240 |
| 48" Cable RJ-45 to DB-25M crossover (One adapter cable needed per port) | 76000238 | 76000238 |
| 48" Cable RJ-45 to DB-9M crossover (One adapter cable needed per port) \dagger 16" (40.64cm) daisy-chain cable included | 76000264 | 76000264 |
| | | |

DIGI SERVICE AND SUPPORT

You can purchase with confidence knowing that Digi is here to support you with expert technical support and a strong five-year warranty. http://support.digi.com

Digi International

11001 Bren Road E. Minnetonka, MN 55343 USA PH: 877-912-3444 952-912-3444 FX: 952-912-4952 Email: info@digi.com

Digi International GmbH

Joseph-von-Fraunhofer Str. 23 D-44227 Dortmund Germany PH: +49-231-9747-0 FX: +49-231-9747-111

www.digi.de

Digi International (HK) Limited

For ISA bus part numbers, visit www.digi.com.

Suite 1703-05, 17/F. K Wah Centre 191 Java Road North Point, Hong Kong PH: +852-2833-1008 FX: +852-2572-989 www.digi.cn

www.digi.com

email: info@digi.com



© 2001-2004 Digi International Inc.

Digi, Digi International, the Digi logo, the Digi Connectware logo, the Making Device Networking Easy logo, PortServer and AccelePort are trademarks or registered trademarks of Digi International, Inc. in the United States and other countries worldwide. All other trademarks are the

91000151 E4/804

www.digi.com