



EE-SX671A

Photo micro sensor, slot type, L-shaped, L-ON/D-ON selectable, NPN, connector

Specifications

Shape	L-shaped
Sensing method	Through-beam with slot
Sensing distance	5 mm
Setting method	Fixed
Connection method	System connector
Output type	NPN
Operation mode	Dark-ON, Light-ON
Response time	0.17 ms
Material housing	PBT
Thread size	Other
Product Width (unpacked)	26.2 mm
Product Height (unpacked)	15.5 mm
Product Depth (unpacked)	18.3 mm
Type of light	Infrared light
Power supply voltage	5-24 V

Accessories



EE-1001

Accessory Connector for Photomicrosensors, 4-pin , solder terminals



EE-1001-1

Connector for Photomicrosensors, 4-pin , solder terminals, bridge between L and +



EE-1006 1M

Accessory Photomicro sensor connector with cable 1 m



EE-1006 2M

Accessory Photomicro sensor connector with cable 2 m



EE-1006 3M

Accessory Photomicro sensor connector with cable 3m



EE-1010 2M

Accessory Photomicro sensor EE-SPX_03, cable connector, PVC, 2m



EE-1010-R 2M

Accessory photomicro sensor EE-SPX_03, cable connector, robotic PVC, 2 m

Downloads

CAD Library



EE-series
Photomicrosensors
Datasheet

EN PDF 9.35 MB

