

You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK
TR ZH

Detailed information for: 260-1600

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

260-1600

General Information

Extended Product Type:	260-1600
Product ID:	7TCA296230R0072
EAN:	5016947003566
Catalog Description:	M25 INDEX EMC CABLE GLAND
Long Description:	Cable Gland, M32 Thread, 13mm Thread Length, 43.5mm Gland Diameter, 40mm Across Flats Diameter, 19-23mm Cable Diameter Range, Nickel Plated Brass, Stainless Steel Spring, Rubber Seal, IP68

Categories

Products » [Low Voltage Products and Systems](#) » [Installation Products](#) » [Cable Protection, Explosion Proof and Lighting](#) » [Flexible Cable Protection Systems](#)

Additional Information

Application:	Provide Strain Relief and Connection for Conduit Systems
Product Type:	Index EMC Type A Cable Gland

Ordering

EAN:	5016947003566
UPC:	786210271606
Customs Tariff Number:	8547200000

Technical

Number of Batteries:	0
Color:	Brass
Material:	Nickel Plated Brass, Stainless Steel Spring, Rubber Seal (TPE-V)
Size:	M32

Environmental

WEEE Category:	Product Not in WEEE Scope
-----------------------	---------------------------

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Height:	1 in 25 mm
Package Level 1 Depth / Length:	1 in 25 mm
Package Level 1 Width:	1 in 25 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	260-1600
---	--------------------------

Instructions and Manuals: [260-1600](#)

Declaration of Conformity - CE: [9AKK107492A9618](#)

RoHS Information: [9AKK107992A8994](#)

REACH Declaration: [9AKK107992A8994](#)

Classifications

UNSPSC: 39121431



© Copyright 2022 ABB