


# CG/CG2 Series









#### **Agency Approvals**

AGENCY	AGENCY FILE NUMBER	
<b>71</b>	E1286621	
c <b>'71</b> 2 us	E320116 <sup>2</sup>	

#### NOTES:

- 1. Certified to UL 497B.
- 2. Only CG2300, CG2470, CG2600, CG2800 and CG221000. Certified to UL 1449.

#### 2 Electrode GDT Graphical Symbol



#### **Additional Information**







Resources



Samples

#### **Description**

Littelfuse's highly reliable CG/CG2 Series GDTs provide a high degree of surge protection in a small size ideal for board level circuit protection.

GDTs function as switches which dissipate a minimum amount of energy and therefore handle currents that far surpass other types of transient voltage protection. Their gas-filled, rugged ceramic metal construction make them well suited to adverse environments.

The CG/CG2 series comes in a variety of forms including surface mount, core, straight and shaped leads, to serve a variety of mounting methods.

The CG Series (75V-110V) is ideal for protection of test and communication equipment and other devices in which low voltage limits and extremely low arc voltages are required.

The CG2 Series (145V-1000V) is ideal for protecting equipment where higher voltage limits and holdover voltages are necessary.

#### **Features**

- RoHS and Lead-free compliant
- Rugged Ceramic-Metal construction
- Low Capacitance (< 1.5pf)
- Meets REA PE-80
- Available in surface mount, and a variety of lead options options
- RoHS Compliant and Lead-Free

#### **Applications**

- Communication lines and equipment
- CATV equipment
- Test equipment
- Data lines
- Power supplies

- Instrumentation circuits
- Medical electronics
- ADSL equipment
- Telecom SLIC protection

# Gas Discharge Tubes CG/CG2 Series

#### **Electrical Characteristics**

	Device Specifications (at 25°C)					Life Ratings								
Part		Breakd in Volts @100V/s	s	Impulse Break- down in Volts (@100V/µs)	Impulse Break- down In Volts (@1 Kv/µsec)	Insulation Resistance	Capaci- tance (@1MHz)	Arc Voltage (on state Voltage) @1Amp Min	Surge Life (@500A 10/1000µs)	Nominal Impulse Discharge Current (8/20µs)	Nominal AC Discharge Current (10x1sec @50-60Hz)	AC Dischage Current (9 cycle @50Hz)	DC Holdover Voltage <sup>2</sup>	Max Impulse Discharge Current (1 Application @ 10/350µs)
Number	MIN	TYP	MAX	MAX		MIN	MAX	TYP					TYP	
CG75	60	75	90	400	650			1.5 pf 15 V	400 shots	5 shots (@20kA)	20 A	100 A		
CG90	72	90	108	400	600	10 <sup>10</sup> Ω							52 V	4kA
CG90 SN	72	90	108	400	600	(at 50V)								
CG110	88	110	132	450	600									
CG2145	116	145	174	500	600								80 V	
CG2145 SN	120	145	174	500	600									
CG2230 <sup>1</sup>	195	230	265	600	700								135 V	2.5kA
CG2230 SN <sup>1</sup>	184	230	276	600	700									
CG2250	213	250	288	625	725									
CG2250 SN	200	250	300	625	725		Ω							
CG2300	255	300	345	700	800									
CG2300 SN	240	300	360	700	800	10¹0 Ω								
CG2350	297	350	403	750	900	(at 100V)								
CG2350 SN	280	350	420	750	900									
CG2420	357	420	483	800	1000									
CG2470 <sup>1</sup>	400	470	540	850	1200									
CG2470 SN <sup>1</sup>	376	470	564	850	1200									
CG2600 <sup>1</sup>	510	600	690	1000	1400									
CG2600 SN <sup>1</sup>	480	600	720	1000	1400									
CG2800 <sup>1</sup>	680	800	920	1200	1500					10 shots	10 A			
CG21000 <sup>1</sup>	850	1000	1150	1500	1600					(@10kA)	10 A	65 A		

- NOTES:

  1. Certified to UL 1449.

  2. Reference REA PE-80, 0.2A. Tested to ITU-T Rec K.12 and REA PE 80 < 150 mSec.

  2. Tested to ITU-T Rec K.12 and REA PE 80 < 150 mSec.

  3. Tested to ITU-T Rec K.12 and REA PE 80 < 150 mSec.
- 3.  $5 \times [5 (+) \text{ or } 5 (+)]$  applications 20kA 8/20 $\mu$ Sec. (75 to 600 volt devices.) 10  $\times [5 (+) \text{ and } 5 (+)]$  applications 10kA 8/20 $\mu$ Sec. (800 and 100 volt devices.)

#### **Product Characteristics**


Materials	LS, Axial: Device: Tin Plated 2–5 Microns Lead Wires: Tin Plated 17.5 ± 12.5 Microns Construction: Ceramic Insulator Core: Device: Tin Plated 17.5 ± 12.5 Microns. Construction: Ceramic Insulator MS: Device: Dull Tin Plated 7–9 Microns Construction: Ceramic Insulator
Product Marking	LF Logo, Voltage and date code; Black in positive print

Glow to arc transition current	< 0.5Amps		
Glow Voltage	60-160 Volts		
Storage and Operational Temperature	-40 to +90		
Maximum Follow On Current <sup>1</sup>	230 Volts r.m.s, 200 Amps. (800V and 1000V devices tested to UL1449 3rd edition)		




#### **Device Dimensions**


#### Leaded 'L' Type Straight Axial Devices




#### **Core Devices**



#### Leaded 'LS' Type Shaped Lead Devices




#### 'MS' Type Devices






#### **Soldering Parameters - Reflow Soldering (Surface Mount Devices)**

Reflow Co	ndition	Pb – Free assembly		
Pre Heat	-Temperature Min (T <sub>s(min)</sub> )	150°C		
	-Temperature Max (T <sub>s(max)</sub> )	200°C		
	-Time (Min to Max) (t <sub>s</sub> )	60 – 180 secs		
Average ra	amp up rate (Liquidus Temp k	3°C/second max		
T <sub>S(max)</sub> to T <sub>L</sub>	- Ramp-up Rate	5°C/second max		
Reflow	-Temperature (T <sub>L</sub> ) (Liquidus)	217°C		
	-Temperature (t <sub>L</sub> )	60 – 150 seconds		
PeakTemp	erature (T <sub>P</sub> )	260 <sup>+0/-5</sup> °C		
Time with Temperatu	in 5°C of actual peak ıre (t <sub>p</sub> )	10 – 30 seconds		
Ramp-dov	vn Rate	6°C/second max		
Time 25°C	to peakTemperature (T <sub>P</sub> )	8 minutes Max.		
Do not exc	ceed	260°C		



#### **Soldering Parameters - Wave Soldering (Thru-Hole Devices)**



### **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100° C
Temperature Maximum:	150° C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	280° C Maximum
Solder DwellTime:	2-5 seconds

# **Soldering Parameters - Hand Soldering**


Solder Iron Temperature: 350° C +/- 5°C


Heating Time: 5 seconds max.




#### **Packaging Dimensions**


#### For 'L' Type Axial Lead Items







#### Core and 'MS' Type Items






### For 'LS' Type Shaped Lead Items








# **Gas Discharge Tubes** CG/CG2 Series

#### **Part Numbering System and Ordering Information**



#### **Examples:**

CG75 - A non-leaded 75V device CG2230L -- A leaded 230V device

CG2800LTR - A leaded 800V device, tape-and-reel (per EIA standard RS-296-D)

#### Notes:

CG/CG2 devices with other breakdown voltages in the 75-1000 V range are available upon request.

#### **Packaging Option Code**

(Blank) = No Leads / Core, Bulk Bag - 400 pcs L(Blank) = Straight Lead, Tray - 50 pcs

LTR = Straight Lead, Tape & Reel per EIA RS-296-E - 500 per reel

LS(Blank) = Shaped Lead (see LS dimensions), Tape & Reel - 500 per reel

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Littelfuse:

CG2230LSN CG2145SN CG110L CG2250LSN CG2350LSN CG21000LTR CG75MSTR CG2250MS CG2300LS

CG2350MS CG110LTR CG2800LS CG2470L-07 CG75LTR CG2350LSTR CG2350LSNTR CG2600LSN

CG2230LSNTR CG2470MS CG90LTR CG75 CG21000LSTR CG2230LS CG110 CG2230MS CG2145LS

CG2800 CG2300LSN CG75L CG90L CG2800MS CG2800L CG2470LSTR CG2145LSTR CG90LSTR CG2600LS

CG2300LSTR CG2250MSTR CG2300MS CG22000MSTR CG2145 CG90SN CG75LSN CG2250 CG2470SN

CG75MS CG90 CG75LS CG2470 CG2145L CG2600L CG90LSN CG2250SN CG21000MSTR CG2250LSSN

CG75LSTR CG2470L CG2230SN CG21000 CG2350 CG2350L CG2600MS CG2300L CG90MS CG2230LSTR

CG2470LSN CG21000LTE CG2145LSSNTR CG2250L CG2350SN CG2470LTR CG2145LSN CG2350LS

CG2300LSNTR CG2145MS CG110LSTR CG2470LSNTE CG2145LTR CG2600LTR CG2350LTR

CG2470LSSNTR CG2230 CG2470LS CG110MSTR CG21000MS CG2470LSNTR CG21000L CG2250LTR

CG90LSNTR CG2250LSNTR CG2230LSSNTR CG2230L CG90MSTR CG2800LTR CG2300LTR

CG2350LSNTR CG2250LSNTR CG2230LSSNTR CG2230L CG90MSTR CG2800LTR CG2300LTR

CG2350LSNTR CG2250LSNTR CG2230LSSNTR CG2230LSSN