



3175 - MALE STUD COUPLING HEXAGONAL BSPT AND NPT THREAD



| | |
|---------------------------------|---|
| maximum working pressure | 20 bar 2 MPa 290 psi |
| working temperature | -20 to 80 °C -4 to 176 °F 253 to 353 °K |
| vacuum capability | 755 mm Hg |
| body | NICKEL PLATED BRASS |
| 'O'-rings | NBR |
| gripping ring | STAINLESS STEEL |
| surface treatment | PTFE |

| Part Nb | ØD (MM) | C | (mm) | F2 (mm) | H (mm) | (kg) |
|------------|---------|-------|-------|---------|--------|-------|
| | All ▾ | All ▾ | All ▾ | All ▾ | All ▾ | All ▾ |
| 3175 04 10 | 4 | R1/8 | 10 | 3 | 9.5 | .005 |
| 3175 04 13 | 4 | R1/4 | 14 | 3 | 6.5 | .012 |
| 3175 04 17 | 4 | R3/8 | 17 | 3 | 8 | .024 |
| 3175 06 10 | 6 | R1/8 | 11 | 4 | 11.5 | .005 |
| 3175 06 13 | 6 | R1/4 | 14 | 4 | 8.5 | .011 |
| 3175 06 17 | 6 | R3/8 | 17 | 4 | 8.5 | .021 |
| 3175 06 21 | 6 | R1/2 | 21 | 4 | 9 | .043 |
| 3175 08 10 | 8 | R1/8 | 13 | 5 | 20 | .011 |
| 3175 08 13 | 8 | R1/4 | 14 | 6 | 17 | .015 |
| 3175 08 17 | 8 | R3/8 | 17 | 6 | 13 | .021 |
| 3175 08 21 | 8 | R1/2 | 21 | 6 | 12 | .039 |
| 3175 10 10 | 10 | R1/8 | 16 | 5 | 22.5 | .017 |
| 3175 10 13 | 10 | R1/4 | 16 | 7 | 20 | .017 |
| 3175 10 17 | 10 | R3/8 | 17 | 8 | 16.5 | .019 |
| 3175 10 21 | 10 | R1/2 | 21 | 8 | 14 | .036 |
| 3175 12 13 | 12 | R1/4 | 19 | 7 | 26.5 | .028 |
| 3175 12 17 | 12 | R3/8 | 19 | 9 | 24 | .028 |
| 3175 12 21 | 12 | R1/2 | 21 | 10 | 19.5 | .036 |
| 3175 14 17 | 14 | R3/8 | 22 | 9 | 28.5 | .043 |
| 3175 14 21 | 14 | R1/2 | 24 | 10 | 23.5 | .046 |
| 3175 16 17 | 16 | R3/8 | 27 | 9 | 32.5 | .068 |
| 3175 16 21 | 16 | R1/2 | 27 | 12 | 32.5 | .079 |