



SECTION A-A

MATERIALS:

- BUSHING AND FLANGE - COPPER ALLOY, NICKEL PLATED
- SPRING - SPECIAL COPPER ALLOY
- CLAMP TERMINAL - COPPER ALLOY, TIN PLATED
- INSULATORS - PHENOLIC AND MYLAR
- HANDLE - COPPER ALLOY, NICKEL PLATED

NOTES:

1. SAME AS 88 JACK EXCEPT SHIELDED HANDLE AND INSULATOR.
2. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M	TEMPER
					1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	FINISH			MATERIAL	
					2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	SPEC No.			SPEC No.	
					3. REMOVE ALL BURRS	FIRST USED ON		SCALE		Switchcraft®
					DO NOT SCALE DRAWING	DATE DRAWN	BY	CHKD	APVD	
B	23532	4-4-01	JL	JF		06-Jun-01	JL	JF 6-6-01	JF 6-6-01	SHEET OF
REV	ECO NUMBER	DATE	BY	APVD		NAME			PART No.	REV
REVISIONS						2 CONDUCTOR EXTENSION JACK, RoHS			128	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[128](#)